Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A

Supplier Information							
Company Name	TE Connectivity	**Request Document ID**		**Contact Name**	Benfer, David W	**Contact Title**	Staff Mfg & Process Dvl Engineer, Eng Proc Opt/LEANPD
Company Unique ID	TE Connectivity	**Response Date**	2017-01-25	**Contact Email**	dave.benfer@te.com		
Contact Phone Number		+1-717-986-3725					

Legal Statement	
Supplier Acceptance	true

Legal Statement

The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

Product							
Manufacturer Item number	499786-6	**Amount**	7056.98702	**Version**	-	**Identity**	
Manufacturer Item Name	026 UNIV HDR RA 4S 15DP STD L1	**Weight Uom**	mg	**Mfr Site**		**Authority**	
Date		**UOM**	Each				
EURoHS-0508	Product(s) does not meet EU RoHS requirements and is not under exemptions						
ChinaRoHS-0508	Product(s) is NOT eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products						
EUREACH-1215	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH						

Product Disclosure

Sub-Item/Material/ Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	UNIVERSAL HEADER LATCH				2.0	449.0	mg	
Material	2	PBT-I-GF30-FR(17)				2.0	449.0	mg	
Substance	3	Dolomite (CaMg(CO3)2)	Supplier	16389-88-1	0.5	2.0	2.245	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	35.0	2.0	157.15	mg	
Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	2.0	0.898	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.2	2.0	0.898	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	3.0	2.0	13.47	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	2.0	2.0	8.98	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	1.0	2.0	4.49	mg	
Substance	3	Chlorite-group minerals	Supplier	1318-59-8	0.5	2.0	2.245	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	2.0	4.49	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	36.6	2.0	164.334	mg	

Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.5	2.0	2.245	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	18.0	2.0	80.82	mg	
Substance	3	Quartz (SiO2)	Supplier	14808-60-7	0.5	2.0	2.245	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	1.0	2.0	4.49	mg	
Sub-Item	1	UNV AMP-LATCH HDR HSG 26P W/MT				1.0	4593.0	mg	
Material	2	PBT-I-GF30-FR(17)				1.0	4593.0	mg	
Substance	3	Dolomite (CaMg(CO3)2)	Supplier	16389-88-1	0.5	1.0	22.965	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	35.0	1.0	1607.55	mg	
Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	1.0	9.186	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.2	1.0	9.186	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	3.0	1.0	137.79	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	2.0	1.0	91.86	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	1.0	1.0	45.93	mg	
Substance	3	Chlorite-group minerals	Supplier	1318-59-8	0.5	1.0	22.965	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	45.93	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	36.6	1.0	1681.038	mg	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.5	1.0	22.965	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	18.0	1.0	826.74	mg	
Substance	3	Quartz (SiO2)	Supplier	14808-60-7	0.5	1.0	22.965	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	1.0	1.0	45.93	mg	
Sub-Item	1	A/L UNIV HDR CONT 15 DPLX				13.0	52.18077	mg	
Material	2	Brass				13.0	50.891	mg	
Substance	3	Tin	Supplier	7440-31-5	0.1	13.0	0.050891	mg	
Substance	3	Copper	Supplier	7440-50-8	64.0	13.0	32.57024	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	13.0	0.0254455	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	13.0	5.0891E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	13.0	0.0050891	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	13.0	0.050891	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.1	13.0	0.050891	mg	
Substance	3	Zinc	Supplier	7440-66-6	35.2085	13.0	17.91796	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	13.0	0.0050891	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	13.0	0.0050891	mg	

Substance	3	Aluminum	Supplier	7429-90-5	0.05	13.0	0.0254455	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.3	13.0	0.15267	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	13.0	0.0050891	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	13.0	2.5446E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	13.0	0.0254455	mg	
Material	2	Tin-Lead Plate				13.0	0.26997	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	13.0	13.0	0.0350961	mg	
Substance	3	Tin	Supplier	7440-31-5	86.5	13.0	0.23352	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.5	13.0	0.00134985	mg	
Material	2	Gold Plate				13.0	0.045	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	13.0	0.044865	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	13.0	1.35E-4	mg	
Material	2	Nickel Plate				13.0	0.92	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	13.0	0.00184	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	13.0	9.2E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	13.0	0.91724	mg	
Material	2	Gold Plate				13.0	0.0548	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	13.0	1.644E-4	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	13.0	0.0546356	mg	
Sub-Item	1	A/L UNIV HDR CONT 15 DPLX				13.0	68.27977	mg	
Material	2	Brass				13.0	66.79	mg	
Substance	3	Tin	Supplier	7440-31-5	0.1	13.0	0.06679	mg	
Substance	3	Copper	Supplier	7440-50-8	64.0	13.0	42.7456	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	13.0	0.033395	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	13.0	6.679E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	13.0	0.006679	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	13.0	0.06679	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.1	13.0	0.06679	mg	
Substance	3	Zinc	Supplier	7440-66-6	35.2085	13.0	23.51576	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	13.0	0.006679	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	13.0	0.006679	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.05	13.0	0.033395	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.3	13.0	0.20037	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	13.0	0.006679	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	13.0	3.3395E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	13.0	0.033395	mg	
Material	2	Tin-Lead Plate				13.0	0.26997	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	13.0	13.0	0.0350961	mg	
Substance	3	Tin	Supplier	7440-31-5	86.5	13.0	0.23352	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.5	13.0	0.00134985	mg	
Material	2	Gold Plate				13.0	0.045	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	13.0	0.044865	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	13.0	1.35E-4	mg	
Material	2	Nickel Plate				13.0	1.12	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	13.0	0.00224	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	13.0	0.00112	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	13.0	1.11664	mg	

Material	2	Gold Plate				13.0	0.0548	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	13.0	1.644E-4	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	13.0	0.0546356	mg	