Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A

Supplier Information

Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Prod Compliance Engineer
Company Unique ID	TE Connectivity	Response Date	2018-04-16	Contact Email	dave.benfer@te.com		
Contact Phone Number		717-986-3725					

Legal Statement

Supplier Acceptance	true

Legal Statement

The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

Product

Manufacturer Item number	499786-8	Amount	10337.208	Version	-	Identity	
Manufacturer Item Name	034 UNIV HDR RA 4S 15DP STD L1	Weight Uom	mg	Mfr Site		Authority	
Date		UOM	Each				
EURoHS-0508	Product(s) does not meet EU RoHS requirements and is not under exemptions						
ChinaRoHS-0508	Product(s) is NOT eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products						
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed						
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed						

Product Disclosure

Sub-Item/Material/ Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	UNV AMP-LATCH HDR HSG 34P W/MT				1.0	5280.6	mg	
Material	2	PBT-I-GF30-FR(17)				1.0	5280.6	mg	
Substance	3	Dolomite (CaMg(CO3)2)	Supplier	16389-88-1	0.5	1.0	26.403	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	35.0	1.0	1848.21	mg	
Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	1.0	10.5612	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.2	1.0	10.5612	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	3.0	1.0	158.418	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	2.0	1.0	105.612	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	1.0	1.0	52.806	mg	
Substance	3	Chlorite-group minerals	Supplier	1318-59-8	0.5	1.0	26.403	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	52.806	mg	

Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	36.6	1.0	1932.6996	mg	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.5	1.0	26.403	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	18.0	1.0	950.508	mg	
Substance	3	Quartz (SiO2)	Supplier	14808-60-7	0.5	1.0	26.403	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	1.0	1.0	52.806	mg	
Sub-Item	1	A/L POST .607" 15 PD-NI/SN-PB				17.0	110.1119	mg	
Material	2	Gold Plate				17.0	0.0105	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	17.0	0.0104685	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	17.0	3.15E-5	mg	
Material	2	Nickel Plate				17.0	0.919	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	17.0	0.001838	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	17.0	9.19E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	17.0	0.91624	mg	
Material	2	Palladium-Nickel Plate				17.0	0.0216	mg	
Substance	3	Palladium	Supplier	7440-05-3	80.0	17.0	0.01728	mg	
Substance	3	Nickel	Nickel	7440-02-0	20.0	17.0	0.00432	mg	
Material	2	Tin-Lead Plate				17.0	0.2608	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	13.0	17.0	0.033904	mg	
Substance	3	Tin	Supplier	7440-31-5	86.5	17.0	0.22559	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.5	17.0	0.001304	mg	
Material	2	Brass				17.0	108.9	mg	
Substance	3	Tin	Supplier	7440-31-5	0.1	17.0	0.1089	mg	
Substance	3	Copper	Supplier	7440-50-8	64.0	17.0	69.696	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	17.0	0.05445	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	17.0	0.001089	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	17.0	0.01089	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	17.0	0.1089	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.1	17.0	0.1089	mg	
Substance	3	Zinc	Supplier	7440-66-6	35.2085	17.0	38.34206	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	17.0	0.01089	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	17.0	0.01089	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.05	17.0	0.05445	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.3	17.0	0.3267	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	17.0	0.01089	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	17.0	5.445E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	17.0	0.05445	mg	
Sub-Item	1	A/L POST .789" 15 PD-NI/SN-PB				17.0	134.5121	mg	
Material	2	Gold Plate				17.0	0.0105	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	17.0	0.0104685	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	17.0	3.15E-5	mg	
Material	2	Nickel Plate				17.0	1.12	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	17.0	0.00224	mg	

Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	17.0	0.00112	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	17.0	1.11664	mg	
Material	2	Palladium-Nickel Plate				17.0	0.0216	mg	
Substance	3	Palladium	Supplier	7440-05-3	80.0	17.0	0.01728	mg	
Substance	3	Nickel	Nickel	7440-02-0	20.0	17.0	0.00432	mg	
Material	2	Tin-Lead Plate				17.0	0.26	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	13.0	17.0	0.0338	mg	
Substance	3	Tin	Supplier	7440-31-5	86.5	17.0	0.2249	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.5	17.0	0.0013	mg	
Material	2	Brass				17.0	133.1	mg	
Substance	3	Tin	Supplier	7440-31-5	0.1	17.0	0.1331	mg	
Substance	3	Copper	Supplier	7440-50-8	64.0	17.0	85.184	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	17.0	0.06655	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	17.0	0.001331	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	17.0	0.01331	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	17.0	0.1331	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.1	17.0	0.1331	mg	
Substance	3	Zinc	Supplier	7440-66-6	35.2085	17.0	46.86251	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	17.0	0.01331	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	17.0	0.01331	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.05	17.0	0.06655	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.3	17.0	0.3993	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	17.0	0.01331	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	17.0	6.655E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	17.0	0.06655	mg	
Sub-Item	1	UNIVERSAL HEADER LATCH				2.0	449.0	mg	
Material	2	PBT-I-GF30-FR(17)				2.0	449.0	mg	
Substance	3	Dolomite (CaMg(CO3)2)	Supplier	16389-88-1	0.5	2.0	2.245	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	35.0	2.0	157.15	mg	
Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	2.0	0.898	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.2	2.0	0.898	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	3.0	2.0	13.47	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	2.0	2.0	8.98	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	1.0	2.0	4.49	mg	
Substance	3	Chlorite-group minerals	Supplier	1318-59-8	0.5	2.0	2.245	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	2.0	4.49	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	36.6	2.0	164.334	mg	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.5	2.0	2.245	mg	

Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	18.0	2.0	80.82	mg	
Substance	3	Quartz (SiO2)	Supplier	14808-60-7	0.5	2.0	2.245	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	1.0	2.0	4.49	mg	