

OPERATION MANUAL MODEL 805 ACCELEROMETER



WARRANTY

Measurement Specialties, Inc. accelerometers are warranted during a period of one year from date of shipment to original purchaser to be free from defects in material and workmanship. The liability of Seller under this warranty is limited to replacing or repairing any instrument or component thereof which is returned by Buyer, at his expense, during such period and which has not been subjected to misuse, neglect, improper installation, repair, alteration, or accident. Seller shall have the right to final determination as to the existence and cause of a defect. In no event shall Seller be liable for collateral or consequential damages. This warrant is in lieu of any other warranty, expressed, implied, or statutory; and no agreement extending or modifying it will be binding upon Seller unless in writing and signed by a duly authorized officer.

RECEIVING INSPECTION

Every Measurement Specialties, Inc. accelerometer is carefully inspected and is in perfect working condition at the time of shipment. Each accelerometer should be checked as soon as it is received. If the unit is damaged in any way, or fails to operate, a claim should immediately be filed with the transportation company.

SERVICE CONCERNS

If a Measurement Specialties, Inc. instrument requires service, first contact the nearest Measurement Specialties, Inc. representative. They may be able to solve the problem without returning the unit to the factory. If it is determined that factory service is required, call Customer Service at the regional headquarters for an RMA number before return.

RETURNS

All units being returned to the factory require an RMA (Return Material Authorization) number before they will be accepted. This number may be obtained by calling Customer Service at the regional headquarters with the following information; model number(s), quantity, serial number(s), and symptoms of the problem, if being returned for service. You must include the original purchase order number if under warranty.

RECALIBRATION SERVICES

The Vibration Sensors Design Center and its two manufacturing facilities in China and France offer factory re-calibration services for Piezoresistive, Piezoelectric and Integrated Electronics Piezoelectric (IEPE, ISOTRON, ICP, etc.) accelerometers. NIST (US), DKD (Germany), COFRAC (France) traceable calibration services on sensitivity at 100 Hz (102 or 120 Hz in Europe) and full frequency sweeps are offered. Contact the regional headquarters for pricing information.

MODEL 805 ACCELEROMETER

DESCRIPTION

The Model 805 is a miniature IEPE accelerometer designed for OEM embedded applications. Packaged in a 3-Pin TO-5 header, the accelerometer is available in ranges from $\pm 50g$ to $\pm 500g$ and offers a flat frequency response to 15kHz. The accelerometer is offered in two configurations; one for adhesive mounting and one for stud mounting.


INSTALLATION

The model 805 accelerometers are offered in adhesive mount and stud mount configurations. For stud mount option the -01 suffix is added to end of part number.

Stud Mounting (model 805-GGGG-01 stud mount option)

For stud mounting the following guidelines should be followed:

- The mounting surface should be clean and free of any residue or foreign material.
- The mounting surface should be smooth, flat, and with a maximum surface roughness of 32 micro-inches rms.
- Apply a light coating of coupling fluid (machine oil or silicone grease) on the mating surface to maximize the usable frequency range.
- Torque mounting stud to 5.3 in-lbs (0.6 N-m)



Adhesive Mounting (805-GGGG standard)

For adhesively mounting of accelerometers the following guidelines should be followed:


- The mounting surface should be clean and free of any residue or foreign material.
- The mounting surface should be smooth, flat, and with a maximum surface roughness of 64 micro-inches rms.
- For best high frequency performance a cyanoacrylate adhesive is recommend. A thin layer offers best frequency response.
- Soften adhesive cured adhesive with a chemical debonder (eg. acetone) prior to removal. Gently shear accelerometer loose from the mounting surface after waiting a few minutes for the debonding agent to penetrate the epoxy. Make sure not to use excessive force as this may damage the accelerometer.
- Note that the outer casing of the 805 accelerometer is connected to circuit ground. If ground isolation is required then a layer of adhesive or epoxy encapsulant should isolate the sensor casing from mounting surface.

EXCITATION

The model 805 is an IEPE type accelerometer that is designed for constant current excitation. The operator can connect the accelerometers to standard IEPE signal conditioners or construct their own constant current excitation circuitry. Consult with Measurement Specialties application support to confirm that the user selected signal conditioner is compatible with the 805 series accelerometers.

IEPE (Integral Electronics Piezoelectric) Accelerometer Schematic

IEPE accelerometers can be operated into readout devices (i.e. oscilloscope), or into the voltage input stage of a signal conditioner without the use of a conventional charge converter/amplifier. Below is the schematic for the basic setup. There are several ways to supply a constant current. The simplest set-up consists of a current regulating diode or diodes in parallel with a battery.




Constant Current

Most IEPE accelerometers can be operated from as low as 2 mA of constant current. Higher current levels (up to 10 mA for model 805) may be required depending on the load and the desired frequency response. In normal applications, 4 mA is recommended. The model 805 series accelerometers can operate at a compliance voltage from 18 to 30 Vdc with an excitation current of 2 to 10 mA.

Compliance Voltage and Bias Voltage

Compliance voltage is defined as the maximum DC voltage available from the constant current source. Bias voltage is the quiescent DC voltage appearing at the output of the IEPE accelerometer in static condition (no vibration). Together they determine the signal transfer characteristic of the IEPE accelerometer. Below shows the typical transfer characteristics of a unity gain IEPE internal preamplifier.



MODEL 805 ACCELEROMETER

In reference to the illustration above, the compliance voltage is available at 22 Vdc. The bias voltage is set by the accelerometer internal preamplifier at 11 Vdc, and the sensor produces an 18V pk-pk input signal. Under these conditions, the internal preamplifier can produce a distortion-free 18V pk-pk output. However, distortion (otherwise known as clipping) may occur with one or more of the following conditions:

1. Input signal exceeds 20V pk-pk.
2. Compliance voltage drops below 20 Vdc.
3. The bias level of the accelerometer shifts significantly with temperature change.

Most IEPE accelerometers are capable of producing linear output up to 18V pk-pk under ideal conditions (conservatively, a maximum full scale output of 10 V pk-pk).

Constructing a Constant Current Supply



Many data acquisition systems on the market today has the ability to supply a constant current supply. There are also many small stand alone constant current supply's available (1 channel boxes up to 16 channel 19 inch rack mount modules as well). Measurement Specialties offers the single channel model 160 and the 4-channel model 161 current supplies.

However, for those that want to construct their own constant current supply, polarity of the power supply voltage must be correctly connected to the constant current diode. If the polarity of the voltage source is reversed, an unlimited amount of current may be going to the IEPE accelerometer and cause permanent damage to the internal electronics of the accelerometer. It is therefore recommended to put a regulating diode (polarity reversal protection) in series with the constant current diode as depicted in the IEPE schematic above.

WIRING

For attaching wires to the header pins of the model 805, the following guidelines should be followed.

- Solder small lead wires to the header pins. The gage should be no larger than #32 AWG.
- Encapsulate the header pins with an encapsulant or silicon RTV to protect the pins from damage during operational usage.



NORTH AMERICA

Measurement Specialties, Inc.,
a TE Connectivity Company
1000 Lucas Way
Hampton, VA 23666
United States
Tel: +1 757 766 1500
Email: customercare.hmpt@te.com

Measurement Specialties, Inc.,
a TE Connectivity Company
Vibration Sensors Design Center
32 Journey, Suite 150
Aliso Viejo, CA 92656, USA
Tel: +1 949 716 7324

EUROPE

MEAS Deutschland GmbH
a TE Connectivity Company
105 av. du Général Eisenhower
BP 1036, 31023 Toulouse Cedex, France
Tel: +33 (0) 561 194 543
Email: customercare.tlse@te.com

ASIA

Measurement Specialties China Ltd.,
a TE Connectivity Company
F1.6-4D, Tian An Development Compound
Shenzhen, China 518057
Tel: +86 755 8330 1004
Email: customercare.shzn@te.com

te.com/sensorsolutions

Measurement Specialties, Inc., a TE Connectivity company.

Measurement Specialties (MEAS), American Sensor Technologies (AST), TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2016 TE Connectivity Ltd. family of companies All Rights Reserved.