Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A

Supplier Information

Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Staff Mfg & Process Dvl Engineer, Eng Proc Opt/LEANPD
Company Unique ID	TE Connectivity	Response Date	2017-01-18	Contact Email	dave.benfer@te.com		
Contact Phone Number		+1-717-986-3725					

Legal Statement

Supplier Acceptance	true

Legal Statement

The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

Product

Manufacturer Item number	499910-5	Amount	6204.035133	Version	-	Identity	
Manufacturer Item Name	024 UNIV HDR SP 4S 15DP STD L2	Weight Uom	mg	Mfr Site		Authority	
Date		UOM	Each				
EURoHS-0508	Product(s) does not meet EU RoHS requirements and is not under exemptions						
ChinaRoHS-0508	Product(s) is NOT eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products						
EUREACH-1215	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH						

Product Disclosure

Sub-Item/Material/ Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	UNV AMP-LATCH HDR HSG 24P W/MTG EARS				1.0	4165.0	mg	
Material	2	PBT-I-GF30-FR(17)				1.0	4165.0	mg	
Substance	3	Dolomite (CaMg(CO3)2)	Supplier	16389-88-1	0.5	1.0	20.825	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	35.0	1.0	1457.75	mg	
Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	1.0	8.33	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.2	1.0	8.33	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	3.0	1.0	124.95	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	2.0	1.0	83.3	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	1.0	1.0	41.65	mg	
Substance	3	Chlorite-group minerals	Supplier	1318-59-8	0.5	1.0	20.825	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	41.65	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	36.6	1.0	1524.39	mg	

Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.5	1.0	20.825	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	18.0	1.0	749.7	mg	
Substance	3	Quartz (SiO2)	Supplier	14808-60-7	0.5	1.0	20.825	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	1.0	1.0	41.65	mg	
Sub-Item	1	A/L UNIV HDR CONT 15 DPLX				24.0	51.8597972	mg	
Material	2	Gold Plate				24.0	0.043016	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	24.0	0.04288695	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	24.0	1.2905E-4	mg	
Material	2	Nickel Plate				24.0	1.03	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	24.0	0.00206	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	24.0	0.00103	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	24.0	1.02691	mg	
Material	2	Tin-Lead Plate				24.0	0.27	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	13.0	24.0	0.0351	mg	
Substance	3	Tin	Supplier	7440-31-5	86.5	24.0	0.23355	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.5	24.0	0.00135	mg	
Material	2	Gold Plate				24.0	0.0567812	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	24.0	1.7034E-4	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	24.0	0.05661086	mg	
Material	2	Brass				24.0	50.46	mg	
Substance	3	Tin	Supplier	7440-31-5	0.1	24.0	0.05046	mg	
Substance	3	Copper	Supplier	7440-50-8	64.0	24.0	32.2944	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	24.0	0.02523	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	24.0	5.046E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	24.0	0.005046	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	24.0	0.05046	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.1	24.0	0.05046	mg	
Substance	3	Zinc	Supplier	7440-66-6	35.2085	24.0	17.76621	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	24.0	0.005046	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	24.0	0.005046	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.05	24.0	0.02523	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.3	24.0	0.15138	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	24.0	0.005046	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	24.0	2.523E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	24.0	0.02523	mg	
Sub-Item	1	UNIVERSAL HEADER LATCH				2.0	397.2	mg	
Material	2	PBT-I-GF30-FR(17)				2.0	397.2	mg	
Substance	3	Dolomite (CaMg(CO3)2)	Supplier	16389-88-1	0.5	2.0	1.986	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	35.0	2.0	139.02	mg	

Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	2.0	0.7944	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.2	2.0	0.7944	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	3.0	2.0	11.916	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	2.0	2.0	7.944	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	1.0	2.0	3.972	mg	
Substance	3	Chlorite-group minerals	Supplier	1318-59-8	0.5	2.0	1.986	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	2.0	3.972	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	36.6	2.0	145.3752	mg	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.5	2.0	1.986	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	18.0	2.0	71.496	mg	
Substance	3	Quartz (SiO2)	Supplier	14808-60-7	0.5	2.0	1.986	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	1.0	2.0	3.972	mg	