Form Type	Distribute	Version	2.0	Sectionals	Material Info	Subsectionals	D, A
Supplier Information							
Company Name	TE Connectivity	Request Document ID		Contact Name	Vincent M Pascucci	Contact Title	Compliance Engineer
Company Unique ID	-	Response Date	2013-02-27	Contact Email	vincent.pascucci@te.com		
Contact Phone Number		717-986-7822					
Legal Statement							
Supplier Acceptance	true						
Legal Statement							
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.							
Product							
Manufacturer Item number	5-102694-5	Amount	2582.255364	Version	-	Identity	
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority	
Date		UOM	Each				
EURoHS-0508	Product(s) meets EU RoHS requierement without any exemptions						
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products						
REACH-0209	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH						

Product Disclosure

Sub-Item/Material/ Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	102642-6				14.0	115.282526	mg	
Material	2	Nickel Plate				14.0	2.102526	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	14.0	0.00210253	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	14.0	2.09622	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	14.0	0.00420505	mg	
Material	2	Phos Bronze				14.0	111.5	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	14.0	105.5721	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	14.0	0.0223	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	14.0	0.01115	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	14.0	5.0175	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	14.0	0.016725	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	14.0	0.01115	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	14.0	0.1115	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	14.0	0.001115	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	14.0	0.3345	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	14.0	0.1115	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	14.0	0.1115	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	14.0	0.01115	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	14.0	0.05575	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	14.0	0.1115	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	14.0	5.575E-4	mg	
Material	2	Tin Plate				14.0	0.9	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	14.0	8.991E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	14.0	0.8991	mg	
Material	2	Gold Plate				14.0	0.78	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.1	14.0	7.8E-4	mg	
Substance	3	Gold	Supplier	7440-57-5	99.9	14.0	0.77922	mg	
Sub-Item	1	102394-5				1.0	968.3	mg	
Material	2	PBT-GF30FR(17)				1.0	968.3	mg	

Substance	3	Carbonic dichloride, polymer with 4,4'-(1-methylethylidene)bis[2,6-dibromophenol] and phenol	Brominated Flame Retardants (other than PBBs or PBDEs)	94334-64-2	30.0	1.0	290.49	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	33.0	1.0	319.539	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	1.0	1.0	9.683	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	9.683	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	48.415	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	290.49	mg	