SAFETY ORGANIZATIONS

THIS FILTER HAS BEEN FORMALLY RECOGNIZED, CERTIFIED OR APPROVED BY THE LISTED AGENCY. THEREFORE, ALL TEST/REQUIREMENTS SPECIFIED IN THE LATEST REVISION OF THE FOLLOWING AGENCY STANDARDS HAVE BEEN MET:

UL RECOGNIZED: UL 1283 VDE APPROVED: EN 60939-2

OPERATING SPECIFICATIONS

LINE CURRENT/VOLTAGE: 10 AMP, 120/250 VAC, 10 AMP/40°C, 250 VAC

LINE FREQUENCY: 50-60Hz

MAXIMUM LEAKAGE CURRENT,

DIFF

dB

SHEET SI

10 20 20 35 67

0

75

70

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUSSIDIANIES AND AFFILIATES. IT MAY NOT BE DISCUSSED TO ANYONE OTHER THAN TYCO ELECTRONICS PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION.

WRITEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION.

60

EACH LINE TO GROUND:

2 µA @ 120V 60Hz 5 µA @ 250V 50Hz

OPERATING AMBIENT TEMP. RANGE: -10°C TO +40°C @ RATED CURRENT, Ir. IN AN AMBIENT, T_0 , HIGHER THAN 40°C, THE MAXIMUM OPERATING CURRENT, I_0 , IS AS FOLLOWS: $I_1 = I_2 - I_3 - I_4 - I_5 - I_5 - I_6$ <u>85 - Τα</u> $I_0 = I_r - /$

RELIABILITY SPECIFICATIONS:

STORAGE TEMPERATURE: -40°C TO +85°C HUMIDITY: 21 DAYS € 40°C 95% RH. CURRENT OVERLOAD TEST: 6 TIMES In FOR 8 SECONDS

CUSTOMER DRAWING		
CATALOG # PEOSODLXC		
ECN #	APPRVD.	
22-185505	JB	30N0V22

TEST SPECIFICATIONS:

INDUCTANCE: 4.0 mH NOMINAL CAPACITANCE: (MEASURED @ 1KHz, 0.250VAC MAX., 25°C±1°C)

LINE TO GROUND: N/A μF±20% LINE TO LINE: 2.0 μF±20%

DISCHARGE RESISTOR: 165 K ∩

L/G AND L/L I.R.

NO DISCHARGE RESISTOR: 6000M ∩ (MIN.) @ 100VDC.

20°C AND 50% RH

TYCO ELECTRONICS PART NO.

DATE: NTS

28APR00

MAC

6609109-4

PEOSODLXC

 \mathbf{C}


DRAWING NUMBER

RECOMMENDED RECEIVING INSPECTION HIPOT:

LINE TO GROUND: 1500 VAC FOR 1 MINUTE 1450 VDC FOR 1 MINUTE LINE TO LINE:

FILTER APPROVAL:

THE BEST WAY TO SELECT AND QUALIFY A FILTER IS FOR YOUR ENGINEERING TO TEST THE UNIT IN YOUR EQUIPMENT.



PEOSODLXC-C.ckd