Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A

Supplier Information

Company Name	TE Connectivity	Request Document ID		Contact Name	John R. Penica	Contact Title	M. Global Product Compliance
Company Unique ID	485203835	Response Date	2013-12-10	Contact Email	jrpenica@te.com		
Contact Phone Number		717-592-3266					

Legal Statement

Supplier Acceptance	true

Legal Statement

The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

Product

Manufacturer Item number	5-103169-1	Amount	1142.226	Version	-	Identity	
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority	
Date		UOM	Each				
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true						
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true						

Product Disclosure

Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	5-104012-7				6.0	55.371	mg	
Material	2	Nickel Plate				6.0	0.596	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	6.0	0.001192	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	6.0	5.96E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	6.0	0.59421	mg	
Material	2	Gold Plate				6.0	0.168	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	6.0	0.1675	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	6.0	5.04E-4	mg	
Material	2	Tin Plate				6.0	0.215	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	6.0	2.1478E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	6.0	0.21479	mg	
Material	2	Phos Bronze				6.0	54.392	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	6.0	51.50025	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	6.0	0.0108784	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	6.0	0.0054392	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	6.0	2.44764	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	6.0	0.0081588	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	6.0	0.054392	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	6.0	0.0054392	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	6.0	5.4392E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	6.0	0.16318	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	6.0	0.054392	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	6.0	0.054392	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	6.0	0.0054392	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	6.0	0.027196	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	6.0	0.054392	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	6.0	2.7196E-4	mg	
Sub-Item	1	3-87472-3				1.0	810.0	mg	
Material	2	PA66-GF25				1.0	810.0	mg	

Substance	3	Benzenamine, reaction products with aniline hydrochloride and nitrobenzene	Supplier	101357-15-7	4.0	1.0	32.4	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	6.0	1.0	48.6	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.5	1.0	28.35	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	61.5	1.0	498.15	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	25.0	1.0	202.5	mg	