SAFETY ORGANIZATIONS

THIS FILTER HAS BEEN FORMALLY RECOGNIZED, CERTIFIED OR APPROVED BY THE LISTED AGENCY. THEREFORE, ALL TEST/REGUIREMENTS SPECIFIED IN THE LATEST REVISION OF THE FOLLOWING AGENCY STANDARDS HAVE BEEN MET:

UL RECDGNIZED: UL 1283 VDE APPROVED: EN 60939-2

OPERATING SPECIFICATIONS

LINE CURRENT/VOLTAGE: 6 AMP, 120/250 VAC, 6 AMP/40°C, 250 VAC

LINE FREQUENCY: 50-60Hz

MAXIMUM LEAKAGE CURRENT,

0.25mA @ 120V 60Hz EACH LINE TO GROUND: 0.50mA @ 250V 50Hz

DPERATING AMBIENT TEMP. RANGE: -10°C TO +40°C @ RATED CURRENT, Ir. IN AN AMBIENT, T_0 , HIGHER THAN 40°C, THE MAXIMUM OPERATING CURRENT, I_0 , IS AS FOLLOWS: $I_0 = I_0 - \sqrt{85 - T_0}$ $I_0 = I_r - \sqrt{85 - \overline{I_0}}$

RELIABILITY SPECIFICATIONS:

STORAGE TEMPERATURE: -40°C TO +85°C HUMIDITY: 21 DAYS @ 40°C 95% RH. CURRENT DVERLDAD TEST: 6 TIMES In FOR 8 SECONDS

CUSTOM	IER DI	RAWING
CATALOG	# PM	OSOSZ6C
ECN #	APPRVD	. DATE
22-185505	JB	30NDV22

TEST SPECIFICATIONS:

INDUCTANCE: 6.2 mH NDMINAL

CAPACITANCE: (MEASURED @ 1KHz, 0.250VAC MAX., 25°C±1°C)

LINE TO GROUND: LINE TO LINE: 0.006µF ±20% 2.0µF ±20% 165K ∩

DISCHARGE RESISTOR:

L/G AND L/L I.R.

ND DISCHARGE RESISTOR: 6000M₁ (MIN.) @ 100VDC,

20°C AND 50% RH


RECOMMENDED RECEIVING INSPECTION HIPOT:

LINE TO GROUND: 1500VAC OR 2250VDC FOR 1 MINUTE

1450VDC FOR 1 MINUTE LINE TO LINE:

FILTER APPROVAL:

THE BEST WAY TO SELECT AND QUALIFY A FILTER IS FOR YOUR ENGINEERING TO TEST THE UNIT IN YOUR EQUIPMENT.



50 <u> </u>	50a-50a(MINIMUM) INSERTION LOSS								
FREQUENCY MHz	. 01	. 05	. 10	. 15	.50	1.0	5.0	10.0	30.0
COMMON dB	8	21	27	30	37	43	49	52	42
DIFF. dB	10	15	34	44	75	75	75	70	60

THIRD ANGLE PROJECTION
UNLESS DTHERWISE SPECIFIED, TOLERANCE TO BE ±.025 MATERIAL & FINISH: AS SUPPLIED
THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO YCO ELECTRONICS CORPORATION AND ITS MORLOWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE OTHER THAN YCO ELECTRONICS PERSONEL, WITHOUT WRITTEN AUTHORIZATION FROM YCO ELECTRONICS CORPORATION. HARRISBURG, PENNSYLVANIA USA



POWER LINE FIL	TER
----------------	-----

IYLU ELELIKUN	IICS PART NU.	3-1003103-0	
SCALE: NITS		CATALOG NO.	REV.
N12	28MAY08	BUGGGGGGG	_
	DRIG:	PMOSOSZ6C	I C
CD	ELC	10.00.0.000	_