Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Manufacturing Info/ Material Info	Subsectionals	D, A

Supplier Information							
Company Name	TE Connectivity	**Request Document ID**		**Contact Name**	Chan, Nelson	**Contact Title**	Mgr Global Accounts, HKG SELL DIR-EMS
Company Unique ID	TE Connectivity	**Response Date**	2017-07-18	**Contact Email**	nelson.chan@te.com		
Contact Phone Number		+852-2738-8751					

Legal Statement	
Supplier Acceptance	true

Legal Statement

The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

Product							
Manufacturer Item number	5-103669-3	**Amount**	933.305314	**Version**	-	**Identity**	
Manufacturer Item Name	04 MTE HDR SRST LATCH W/HLDWN	**Weight Uom**	mg	**Mfr Site**		**Authority**	
Date		**UOM**	Each				
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions						
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products						
EUREACH-0616	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH						
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed						

Manufacturing Information							
J-STD-020 MSL Rating		**Max Total a Wave Time**		**Ramp Rate**		**Wave Additional Info**	
Classification Temp		**Max Wave Solder Time**	20.0	**Ramp Down Rate**		**Psl Rating Reflow**	
Max Time Within 5		**Psl Rating Wave**		**Package Designator**		**Size**	0.0
Time Above 217		**Reflow Additional Info**		**Preheat Max Temp**		**Terminal Base Alloy**	Not Applicable
Preheat Duration		**bulk Solder Termination**	Not Applicable	**Nbr or Reflow Cycles**		**Terminal Plating**	Not Applicable
Preheat Min Temp		**Nbr of Instances**	0	**Component Temp Spike**		**Shape**	Not Applicable

Product Disclosure

Sub-Item/Material/ Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	MTE POST PLTD SN				4.0	50.8983285	mg	
Material	2	Tin Plate				4.0	1.0806	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	4.0	0.0021612	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	4.0	1.07768	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	4.0	7.5642E-4	mg	
Material	2	Nickel Plate				4.0	0.6577285	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	4.0	0.00131546	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	4.0	6.5773E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	4.0	0.65576	mg	
Material	2	Brass				4.0	49.16	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	4.0	4.916E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	4.0	13.77586	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	4.0	0.02458	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	4.0	0.004916	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	4.0	0.02458	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	4.0	0.04916	mg	

Substance	3	Copper	Supplier	7440-50-8	71.5	4.0	35.1494	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	4.0	4.916E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	4.0	0.004916	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	4.0	2.458E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	4.0	0.09832	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	4.0	0.002458	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	4.0	0.02458	mg	
Sub-Item	1	04 MODII HDR DRRA SHRD .100 C/L				1.0	729.712	mg	
Material	2	LCP-GF35				1.0	729.712	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	2.0	1.0	14.59424	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	34.3	1.0	250.29122	mg	
Substance	3	1,3-Benzenedicarboxylic acid, polymer with 1,4-benzenedicarboxylic acid, [1,1-biphenyl]-4,4-diol and 4-hydroxybenzoic acid	Supplier	60088-52-0	62.7	1.0	457.52942	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	7.29712	mg	