



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Manufacturing Info/ Material Info	<b>Subsectionals</b>	D, A																									
<b>Supplier Information</b>																																		
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Chan, Nelson	<b>Contact Title</b>	Manager Sales, HKG SELL DIR-EMS																											
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2015-12-12	<b>Contact Email</b>	nelson.chan@te.com																													
<b>Contact Phone Number</b>		+852-2738-8751																																
<b>Legal Statement</b>																																		
<b>Supplier Acceptance</b>	true																																	
<b>Legal Statement</b>																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
<b>Product</b>																																		
<b>Manufacturer Item number</b>	532828-2	<b>Amount</b>	1226.822892	<b>Version</b>	-	<b>Identity</b>																												
<b>Manufacturer Item Name</b>	HDI STATIC CHRG GDE PIN PLTD	<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>																												
<b>Date</b>		<b>UOM</b>	Each																															
<b>EUROHS-0508</b>	Product(s) meets EU RoHS requirements by application of the selected exemption(s)																																	
<b>ChinaRoHS-0508</b>	Product(s) is NOT eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
<b>EUREACH-1214</b>	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH																																	
<b>Manufacturing Information</b>																																		
<b>J-STD-020 MSL Rating</b>		<b>Max Total a Wave Time</b>		<b>Ramp Rate</b>		<b>Wave Additional Info</b>																												
<b>Classification Temp</b>		<b>Max Wave Solder Time</b>	0.0	<b>Ramp Down Rate</b>		<b>Psi Rating Reflow</b>																												
<b>Max Time Within 5</b>		<b>Psi Rating Wave</b>		<b>Package Designator</b>		<b>Size</b>	0.0																											
<b>Time Above 217</b>		<b>Reflow Additional Info</b>		<b>Preheat Max Temp</b>		<b>Terminal Base Alloy</b>	NAC																											
<b>Preheat Duration</b>		<b>bulk Solder Termination</b>	NAC	<b>Nbr or Reflow Cycles</b>		<b>Terminal Plating</b>	NAC																											
<b>Preheat Min Temp</b>		<b>Nbr of Instances</b>	0	<b>Component Temp Spike</b>		<b>Shape</b>	NAC																											
<b>Product Disclosure</b>																																		
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>																									
Material	1	Brass				1.0	1215.3	mg																										
Substance	2	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.012153	mg																										
Substance	2	Antimony	Supplier	7440-36-0	0.01	1.0	0.12153	mg																										
Substance	2	Cobalt	Supplier	7440-48-4	0.1	1.0	1.2153	mg																										
Substance	2	Arsenic	Supplier	7440-38-2	0.01	1.0	0.12153	mg																										
Substance	2	Manganese	Supplier	7439-96-5	0.02	1.0	0.24306	mg																										
Substance	2	Chromium	Supplier	7440-47-3	0.0010	1.0	0.012153	mg																										
Substance	2	Iron	Supplier	7439-89-6	0.35	1.0	4.25355	mg																										
Substance	2	Zinc	Supplier	7440-66-6	32.7475	1.0	397.98037	mg																										
Substance	2	Copper	Supplier	7440-50-8	63.0	1.0	765.639	mg																										
Substance	2	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0060765	mg																										
Substance	2	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.12153	mg																										
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	3.7	1.0	44.9661	mg	6(c) Lead as an alloying element in copper containing up to 4% lead by weight																									
Substance	2	Nickel	Nickel	7440-02-0	0.05	1.0	0.60765	mg																										
Material	1	Nickel Plate				1.0	6.82554	mg																										
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.01365108	mg																										
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.00682554	mg																										
Substance	2	Nickel	Nickel	7440-02-0	99.7	1.0	6.80506	mg																										

Material	1	Gold Plate				1.0	4.697352	mg	
Substance	2	Gold	Supplier	7440-57-5	99.7	1.0	4.68326	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	1.0	0.01409206	mg	