Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A

Supplier Information

Company Name	TE Connectivity	Request Document ID		Contact Name	David W Benfer	Contact Title	PROD COMPLIANCE ENGINEER
Company Unique ID	-	Response Date	2013-08-12	Contact Email	dave.benfer@te.com		
Contact Phone Number		717-986-3725					

Legal Statement

Supplier Acceptance	true

Legal Statement

The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

Product

Manufacturer Item number	5646492-1	Amount	16628.143	Version	-	Identity	
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority	
Date		UOM	Each				
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true						
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true						

Product Disclosure

Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	646443-1				1.0	3293.0	mg	
Material	2	PBT-GF20				1.0	3293.0	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	56.5	1.0	1860.545	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.0	1.0	98.79	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	20.0	1.0	658.6	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	164.65	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.5	1.0	16.465	mg	
Substance	3	2-Propenoic acid, (2,3,4,5,6-pentabromophenyl)methyl ester, homopolymer	Brominated Flame Retardants (other than PBBs or PBDEs)	59447-57-3	15.0	1.0	493.95	mg	
Sub-Item	1	5646437-2				11.0	768.613	mg	
Material	2	PBT-GF20				11.0	450.0	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	56.5	11.0	254.25	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.0	11.0	13.5	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	20.0	11.0	90.0	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	11.0	22.5	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.5	11.0	2.25	mg	

Substance	3	2-Propenoic acid, (2,3,4,5,6-pentabromophenyl)methyl ester, homopolymer	Brominated Flame Retardants (other than PBBs or PBDEs)	59447-57-3	15.0	11.0	67.5	mg	
Material	2	Nickel Plate				11.0	3.04	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	11.0	0.00608	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	11.0	0.00304	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	11.0	3.03088	mg	
Material	2	Phos Bronze				11.0	315.0	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	11.0	298.25303	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	11.0	0.063	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	11.0	0.0315	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	11.0	14.175	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	11.0	0.04725	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	11.0	0.315	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	11.0	0.0315	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	11.0	0.00315	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	11.0	0.945	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	11.0	0.315	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	11.0	0.315	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	11.0	0.0315	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	11.0	0.1575	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	11.0	0.315	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	11.0	0.001575	mg	
Material	2	Gold Plate				11.0	0.023	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	11.0	0.022931	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	11.0	6.9E-5	mg	
Material	2	Tin Plate				11.0	0.55	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	11.0	5.4945E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	11.0	0.54945	mg	
Sub-Item	1	5646494-1				1.0	4880.4	mg	
Material	2	Phos Bronze				1.0	4840.0	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	1.0	4582.6814	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.968	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	0.484	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	1.0	217.8	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	1.0	0.726	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	4.84	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.484	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.0484	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	1.0	14.52	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	1.0	4.84	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	4.84	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.484	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	2.42	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	4.84	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0242	mg	
Material	2	Nickel Plate				1.0	33.9	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	1.0	0.0678	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.0339	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	33.7983	mg	
Material	2	Gold Plate				1.0	5.3	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	5.2841	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	1.0	0.0159	mg	

Material	2	Tin Plate				1.0	1.2	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	1.0	0.0011988	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	1.0	1.1988	mg	