



## TRUBLUE 575 BARO DATA LOGGER

- ♦ Barometric Pressure Accuracy of  $\pm 0.05\%$  FS TEB
- ♦ Five year permanent battery
- ♦ 8 MB internal memory
- ♦ New user-friendly TruWare software for PC or Mobile

The TruBlue 575 BARO Data Logger is an absolute non-submersible pressure transducer. This unit provides local atmospheric pressure data that can be used to compensate one or more submerged, non-vented water level transducers. An absolute format measures all pressure applied to it including atmospheric. If submerged, it measures the atmospheric pressure plus pressure exerted by the column of water above the sensor. A level value can be arrived at using two absolute transducers—one submerged and one at ground level—subtracting atmospheric pressure from the submerged transducer measuring water pressure.

The TruBlue 575 BARO is the perfect choice to measure barometric pressure when reliability, accuracy and precision matter.

### Features

- ♦ Calibration Report included with each instrument
- ♦ New fully sealed design
- ♦ Two Year Warranty
- ♦ Easier set-up and data retrieval
- ♦ Displays real-time instrument status and data graphs
- ♦ RS-485 or SDI-12 communication interface


### Applications

- ♦ Barometric Pressure Measurement
- ♦ Correction for Non-vented Transducers
- ♦ Remediation
- ♦ Surface Water Monitoring
- ♦ Groundwater Monitoring
- ♦ Oceanographic Research

## Specifications

<b>SENSORS – LEVEL</b>		
Sensor Type		Oil-filled Piezoresistive
Sensor Material		316 SS or Titanium
Range (psia)	Low	8
	High	16
Accuracy	0 – 50°C	±0.05% FS TEB
Resolution		0.01% FS or better
Burst		3 x FS (600 psi max)
Accuracy is stated as total error band (TEB). This includes the combined errors due to non-linearity, hysteresis, non-repeatability and thermal effects.		
<b>SENSORS – TEMPERATURE</b>		
Sensor Type		Embedded NTC Thermistor
Range (°C)	Low	0
	High	50
Accuracy		±0.2°C
Resolution		0.01°C
<b>PHYSICAL</b>		
Diameter	inches	0.75
Length	inches	13.26
Weight	oz.	12
<b>OPERATING CONDITIONS</b>		
Pressure (psia)	Low	8
	High	16
Temperature (°C)	Low	0
	High	50
<b>ELECTRICAL</b>		
Internal Battery Type		3.6V lithium
Battery Life		5 years
On-Board Surge Protection		✓
External Power		6-16 VDC (1 mA sleep, 15 mA active)
Communication Interface		RS-485 (half duplex), SDI-12
<b>DATA LOGGING</b>		
Memory		8 MB
Data Points		550,000
Clock Accuracy		2 min/year
Reading	Linear	1 per 5 seconds
	Linear Average	programmable
	Event	programmable
Fastest Logging Rate	Linear	5 per second
	Linear Average	programmable
	Event	programmable
Methods	Linear	✓
	Linear Average	✓
	Event	✓

### Dimensions



### Software

Each unit comes with user-friendly TruWare software at no charge.

- ♦ View, graph, and export test data
- ♦ Manage transducers by site
- ♦ Easy to use in the field or office



### Ordering Information

#### 1. Pick your transducer

PART NUMBER	REFERENCE	MATERIAL
575-00020	Absolute	S
575-00030	Absolute	T

#### 2. Communication cable options

MODEL	DESCRIPTION
850-00857	USB to Backshell Communication Cable

#### 3. Other cabling options can be found in the TruBlue Accessories Catalog

#### NORTH AMERICA

Measurement Specialties, Inc.  
a TE Connectivity Company  
Tel 800-522-6752  
[customercare.hmp@te.com](mailto:customercare.hmp@te.com)

#### EUROPE

Measurement Specialties (Europe), Ltd.,  
A TE Connectivity Company  
Tel 800-440-5100  
[customercare.dtm@te.com](mailto:customercare.dtm@te.com)

#### ASIA

Measurement Specialties (China), Ltd.,  
a TE Connectivity Company  
Tel 0400-820-6049  
[customercare.shzn@te.com](mailto:customercare.shzn@te.com)

#### TE.com/sensorsolutions

Measurement Specialties, Inc., a TE Connectivity company.

Measurement Specialties (MEAS), American Sensor Technologies (AST), TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2017 TE Connectivity Ltd. family of companies All Rights Reserved.