Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A

Supplier Information

Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Prod Compliance Engineer
Company Unique ID	TE Connectivity	Response Date	2015-01-15	Contact Email	dave.benfer@te.com		
Contact Phone Number		717-986-3725					

Legal Statement

Supplier Acceptance	true

Legal Statement

The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

Product

Manufacturer Item number	5748677-5	Amount	47975.79952	Version	-	Identity	
Manufacturer Item Name	PLTD PLST CBL CLMP KIT,SZ 5	Weight Uom	mg	Mfr Site		Authority	
Date		UOM	Each				

EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products
EUREACH-1213	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed

Product Disclosure

Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	MOUNTING SCREW, ZN PLTD				2.0	522.158	mg	
Material	2	Carbon Steel				2.0	522.0	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.04	2.0	0.2088	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	0.0522	mg	
Substance	3	Iron	Supplier	7439-89-6	98.2485	2.0	512.85717	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.0522	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.522	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.05	2.0	0.261	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	0.00522	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.23	2.0	1.2006	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.15	2.0	0.783	mg	
Substance	3	Manganese	Supplier	7439-96-5	1.0	2.0	5.22	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	2.0	0.0522	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	0.00261	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	0.522	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	2.0	0.261	mg	
Material	2	Zinc Plate				2.0	0.14	mg	
Substance	3	Zinc	Supplier	7440-66-6	100.0	2.0	0.14	mg	
Material	2	Tri Chrome Film				2.0	0.018	mg	
Substance	3	Silicate(2-), hexafluoro-, hydrogen (1:2)	Supplier	16961-83-4	30.0	2.0	0.0054	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	10.0	2.0	0.0018	mg	
Substance	3	Chromium chloride (CrCl3), hydrate (1:6)	Supplier	10060-12-5	60.0	2.0	0.0108	mg	
Sub-Item	1	SCREW, MACHINE, FILLISTER HEAD, SLOT				2.0	334.64	mg	
Material	2	Carbon Steel				2.0	330.98	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	0.0016549	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.033098	mg	

Substance	3	Manganese	Supplier	7439-96-5	0.6	2.0	1.98588	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.13	2.0	0.43027	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.04	2.0	0.13239	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.15	2.0	0.49647	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	0.0033098	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.02	2.0	0.066196	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.1	2.0	0.33098	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.33098	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	0.033098	mg	
Substance	3	Iron	Supplier	7439-89-6	98.6785	2.0	326.6061	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	0.33098	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	2.0	0.033098	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	2.0	0.16549	mg	
Material	2	Zinc Plate				2.0	2.88	mg	
Substance	3	Zinc	Supplier	7440-66-6	100.0	2.0	2.88	mg	
Material	2	Tri Chrome Film				2.0	0.78	mg	
Substance	3	Silicate(2-), hexafluoro-, hydrogen (1:2)	Supplier	16961-83-4	30.0	2.0	0.234	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	10.0	2.0	0.078	mg	
Substance	3	Chromium chloride (CrCl3), hydrate (1:6)	Supplier	10060-12-5	60.0	2.0	0.468	mg	
Sub-Item	1	NUT,4-40,PLATED				2.0	190.65876	mg	
Material	2	Carbon Steel				2.0	189.0	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.2	2.0	0.378	mg	
Substance	3	Iron	Supplier	7439-89-6	97.5175	2.0	184.30807	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	2.0	0.00189	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.4	2.0	0.756	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.3	2.0	0.567	mg	
Substance	3	Manganese	Supplier	7439-96-5	1.3	2.0	2.457	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	0.0189	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.0189	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.189	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	0.00189	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	9.45E-4	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	2.0	0.0189	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	0.189	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	2.0	0.0945	mg	
Material	2	Zinc Plate				2.0	1.65	mg	
Substance	3	Zinc	Supplier	7440-66-6	100.0	2.0	1.65	mg	
Material	2	Tri Chrome Film				2.0	0.00876	mg	
Substance	3	Silicate(2-), hexafluoro-, hydrogen (1:2)	Supplier	16961-83-4	30.0	2.0	0.002628	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	10.0	2.0	8.76E-4	mg	
Substance	3	Chromium chloride (CrCl3), hydrate (1:6)	Supplier	10060-12-5	60.0	2.0	0.005256	mg	
Sub-Item	1	CABLE CLAMP SIZE 5-PLATED				2.0	19324.193	mg	
Material	2	Nickel Plate				2.0	358.702	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	2.0	0.7174	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	0.3587	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	2.0	357.62589	mg	
Material	2	ABS MOLDING COMPOUND				2.0	18407.01	mg	

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	10.0	2.0	1840.701	mg	
Substance	3	2-Propenenitrile, polymer with 1,3-butadiene and ethenylbenzene	Supplier	9003-56-9	65.0	2.0	11964.5565	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	2.0	920.3505	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	20.0	2.0	3681.402	mg	
Material	2	Copper Plate				2.0	558.481	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	0.55848	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	2.0	557.92252	mg	
Sub-Item	1	GROMMET ASSORTMENT, SZ 3,4 & 5				1.0	7232.5	mg	
Material	2	POLYVINYL CHLORIDE				1.0	7232.5	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	3.3	1.0	238.6725	mg	
Substance	3	Ethene, chloro-, homopolymer	Supplier	9002-86-2	41.4	1.0	2994.255	mg	
Substance	3	Magnesium carbonate hydroxide	Supplier	12125-28-9	5.6	1.0	405.02	mg	
Substance	3	Huntite (CaMg3(CO3)4) (9CI)	Supplier	19569-21-2	5.6	1.0	405.02	mg	
Substance	3	Barium	Supplier	7440-39-3	0.2	1.0	14.465	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	1.8	1.0	130.185	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.1	1.0	7.2325	mg	
Substance	3	1,2-Benzenedicarboxylic acid, di-C8-10-branched alkyl esters, C9-rich	Phthalates (DINP, DIDP, DNOP)	68515-48-0	17.3	1.0	1251.2225	mg	
Substance	3	1,2-Benzenedicarboxylic acid, 3,4,5,6-tetrabromo-, 1,2-bis(2-ethylhexyl) ester	Brominated Flame Retardants (other than PBBs or PBDEs)	26040-51-7	7.4	1.0	535.205	mg	
Substance	3	1,2-Benzenedicarboxylic acid, di-C6-8-branched alkyl esters, C7-rich	1,2-Benzenedicarboxylic acid, di-C6-8-branched alkyl esters, C7-rich	71888-89-6	17.3	1.0	1251.2225	mg	