File E28476 Vol. 68 Sec. 29 Page 1 Issued: 2010-06-15 and Report Revised: 2011-04-07

DESCRIPTION

PRODUCT COVERED:

*USR - 4 Pos. Low Voltage Free Hanging Connector, Cat. Nos. 293702-1, 293702-2, 293702-3, 293703-1, 293703-2 and 293703-3

GENERAL:

These devices are multi-pole connectors intended for factory assembly on printed wiring boards where the acceptability of combinations is determined by Underwriters Laboratories Inc. The devices are identified as follows:

USR indicates investigation to United States Standards, UL 1977.

RATINGS: 30 V ac/dc, 2 A

File E28476

Vol. 68

Sec. 29 and Report Page 2

Issued: 2010-06-15

TECHNICAL CONSIDERATIONS (NOT FOR FIELD REPRESENTATIVE'S USE):

Use - For use only in or with complete equipment where the acceptability of the combination is determined by Underwriters Laboratories Inc.

Conditions of Acceptability - The following are among the considerations to be made when evaluating the device in the end-use product.

Interruption of Current

These devices are not suitable for interrupting the flow of current by connecting or disconnecting the mating connector.

Current-Carrying Capability and Current Ratings

These devices have been subjected to the Temperature test with the rated currents and maximum temperature rise values tabulated below.

Cat No.	Current, A	Maximum Temperature Rise, °C		
293702-2 and 293703-2	2	5.7		

Insulating Materials

These devices employ insulating materials with properties as tabulated below at the minimum thickness employed in the connector housing, the suitability of the insulating materials based on the documented values shall be determined in the end-use application. Please note the values specified in the table when multiple materials are indicated represent the minimum values for the group of materials.

Cat. No.	Insulating Material (#)	Measured Minimum Thickness	Flame Class	HWI	HAI	RTI Elec	RTI Str	Max Operating Temp, ⁰ C
293702-1, 293702-2, 293702-3, 293703-1, 293703-2, 293703-3	A	0.4 mm	V-0	4	3	130	130	130

(#) - Code for Insulating Body Material.

- 1. Dielectric strength (kV/mm):-
- 2. CTI: 2