Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A

Supplier Information							
Company Name	TE Connectivity	**Request Document ID**		**Contact Name**	Benfer David W	**Contact Title**	Product Compliance Engineer for DND
Company Unique ID	TE Connectivity	**Response Date**	2017-12-28	**Contact Email**	dave.benfer@te.com		
Contact Phone Number		1-717-986-3725					

Legal Statement	
Supplier Acceptance	true

Legal Statement

The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

Product							
Manufacturer Item number	5786554-5	**Amount**	10472.0275	**Version**	-	**Identity**	
Manufacturer Item Name	50 50SR VRT RCPT,L,R,ACT PIN	**Weight Uom**	mg	**Mfr Site**		**Authority**	
Date		**UOM**	Each				
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions						
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products						
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed						
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed						

Product Disclosure

Sub-Item/Material/ Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	50 50SR VRT ACTION PIN S-A,L/F				1.0	3271.7275	mg	
Material	2	PPA-GF33				1.0	1221.7	mg	
Substance	3	Benzene, ethenyl-, homopolymer, brominated	Supplier	88497-56-7	23.3	1.0	284.6561	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.5	1.0	18.3255	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	35.2	1.0	430.0384	mg	
Substance	3	Antimonate (SbO31-), sodium (1:1)	Supplier	15432-85-6	3.9	1.0	47.6463	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	0.3	1.0	3.6651	mg	
Substance	3	1,4-Benzenedicarboxylic acid, polymer with 1,6-hexanediamine and hexanedioic acid	Supplier	25776-72-1	34.5	1.0	421.4865	mg	
Substance	3	Calcium oxide (CaO)	Supplier	1305-78-8	0.4	1.0	4.8868	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.9	1.0	10.9953	mg	
Material	2	Gold Plate				1.0	0.6275	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	0.62562	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	1.0	0.0018825	mg	
Material	2	Nickel Plate				1.0	40.75	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.0815	mg	

Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.04075	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	40.62775	mg	
Material	2	Tin Plate				1.0	8.65	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.0173	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	8.62665	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	0.006055	mg	
Material	2	Phos Bronze				1.0	2000.0	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6985	1.0	1893.97	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.4	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	0.2	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	1.0	90.0	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	1.0	0.1	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	2.0	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.2	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.02	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	1.0	6.0	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	1.0	2.0	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	2.0	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.1	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	1.0	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	2.0	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.01	mg	
Sub-Item	1	50 50SR BD RCPT SHELL,PLTD,LP				1.0	872.1	mg	
Material	2	Nickel Plate				1.0	73.8	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.0738	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	73.5786	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.1476	mg	
Material	2	Copper Plate				1.0	18.5	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.0185	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	1.0	18.4815	mg	
Material	2	Carbon Steel				1.0	779.8	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.08	1.0	0.62384	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.007798	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.5	1.0	3.899	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.07798	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.2	1.0	1.5596	mg	
Substance	3	Iron	Supplier	7439-89-6	98.8875	1.0	771.12473	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.025	1.0	0.19495	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.025	1.0	0.19495	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.007798	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.07798	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.7798	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.3899	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.07798	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.7798	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.003899	mg	
Sub-Item	1	50 50SR BRKT,VRT RCPT,PLTD				1.0	6328.2	mg	
Material	2	Zinc Alloy				1.0	6206.5	mg	
Substance	3	Iron	Supplier	7439-89-6	0.08	1.0	4.9652	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.035	1.0	2.17228	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.62065	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.062065	mg	
Substance	3	Tin	Supplier	7440-31-5	0.0020	1.0	0.12413	mg	
Substance	3	Magnesium	Supplier	7439-95-4	0.05	1.0	3.10325	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.02	1.0	1.2413	mg	

Substance	3	Copper	Supplier	7440-50-8	0.1	1.0	6.2065	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	6.2065	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	1.0	3.10325	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.62065	mg	
Substance	3	Zinc	Supplier	7440-66-6	95.2145	1.0	5909.48794	mg	
Substance	3	Aluminum	Supplier	7429-90-5	4.3	1.0	266.8795	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.02	1.0	1.2413	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0030	1.0	0.1862	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0310325	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0040	1.0	0.24826	mg	
Material	2	Copper Plate				1.0	81.1	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.0811	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	1.0	81.0189	mg	
Material	2	Nickel Plate				1.0	40.6	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.0406	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.0812	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	40.4782	mg	