Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A

Supplier Information							
Company Name	TE Connectivity	**Request Document ID**		**Contact Name**	Benfer, David W	**Contact Title**	Prod Compliance Engineer
Company Unique ID	TE Connectivity	**Response Date**	2016-06-22	**Contact Email**	dave.benfer@te.com		
Contact Phone Number		717-986-3725					

Legal Statement	
Supplier Acceptance	true

Legal Statement

The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

Product							
Manufacturer Item number	650912-5	**Amount**	10822.384347	**Version**	-	**Identity**	
Manufacturer Item Name	064 EURO TYPE R PIN AP ASSY	**Weight Uom**	mg	**Mfr Site**		**Authority**	
Date		**UOM**	Each				
EURoHS-0508	Product(s) does not meet EU RoHS requirements and is not under exemptions						
ChinaRoHS-0508	Product(s) is NOT eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products						
EUREACH-0615	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH						

Product Disclosure

Sub-Item/Material/ Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	EURO LC A/P CONT PLTD, PDNI				64.0	66.673702	mg	
Material	2	Gold Plate				64.0	0.003871	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	64.0	0.00385939	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	64.0	1.1613E-5	mg	
Material	2	Palladium-Nickel Plate				64.0	0.03515	mg	
Substance	3	Palladium	Supplier	7440-05-3	80.0	64.0	0.02812	mg	
Substance	3	Nickel	Nickel	7440-02-0	20.0	64.0	0.00703	mg	
Material	2	Phos Bronze				64.0	65.3	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6985	64.0	61.83812	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	64.0	0.01306	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	64.0	0.00653	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	64.0	2.9385	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	64.0	0.003265	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	64.0	0.0653	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	64.0	0.00653	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	64.0	6.53E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	64.0	0.1959	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	64.0	0.0653	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	64.0	0.0653	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	64.0	0.003265	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	64.0	0.03265	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	64.0	0.0653	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	64.0	3.265E-4	mg	
Material	2	Tin-Lead Plate				64.0	0.534284	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	13.0	64.0	0.06945692	mg	
Substance	3	Tin	Supplier	7440-31-5	86.5	64.0	0.46216	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.5	64.0	0.00267142	mg	
Material	2	Nickel Plate				64.0	0.800397	mg	

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	64.0	0.00160079	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	64.0	8.004E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	64.0	0.798	mg	
Sub-Item	1	096 EURO LCP HSG				1.0	6555.267419	mg	
Material	2	PBT-I-GF30FR(17)				1.0	6555.267419	mg	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.5	1.0	32.77634	mg	
Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.1	1.0	6.55527	mg	
Substance	3	Aluminum oxide (Al2O3)	Supplier	1344-28-1	0.1	1.0	6.55527	mg	
Substance	3	Copper oxide (CuO)	Supplier	1317-38-0	0.1	1.0	6.55527	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	1.0	1.0	65.55267	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	45.895	1.0	3008.53998	mg	
Substance	3	Zinc oxide (ZnO)	Supplier	1314-13-2	0.1	1.0	6.55527	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	1.0	1.0	65.55267	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	4.0	1.0	262.2107	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	2.0	1.0	131.10535	mg	
Substance	3	Carbon black	Supplier	1333-86-4	0.01	1.0	0.65553	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	1966.58023	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.18	1.0	11.79948	mg	
Substance	3	Zinc sulfide (ZnS)	Supplier	1314-98-3	2.0	1.0	131.10535	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	10.0	1.0	655.52674	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	3.0	1.0	196.65802	mg	
Substance	3	1H-Isoindole-1,3(2H)-dione, 4,5,6,7-tetrachloro-2-[2-(4,5,6,7-tetrachloro-2,3-dihydro-1,3-dioxo-1H-inden-2-yl)-8-quinolinyl]-	Supplier	30125-47-4	0.01	1.0	0.65553	mg	
Substance	3	Methane, dichloro-	Supplier	75-09-2	0.0050	1.0	0.32776	mg	