Form Type	Distribute	Version	2.0	Sectionals	Material Info	Subsectionals	D, A
Supplier Information							
Company Name	TE Connectivity	Request Document ID		Contact Name	David Benfer	Contact Title	Product Compliance Engineer for DTC
Company Unique ID	-	Response Date	2013-03-24	Contact Email	dave.benfer@te.com		
Contact Phone Number		717-986-3725					
Legal Statement							
Supplier Acceptance	true						
Legal Statement							
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.							
Product							
Manufacturer Item number	6658293-1	Amount	12111.64784756	Version	-	Identity	
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority	
Date		UOM	Each				
EURoHS-0508	Product(s) meets EU RoHS requirements by application of the selected exemption(s)						
ChinaRoHS-0508	Product(s) requires marking for the presence of restricted substances and must be marked with an Environmental Protection Use Period under China's Measures for Administration of the control of pollution by Electronic Information Products						
REACH-0209	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH						

Product Disclosure

Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	1-745120-6				1.0	4829.161837	mg	
Material	2	Tin Plate				1.0	131.277097	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	0.4	1.0	0.52511	mg	
Substance	3	Tin	Supplier	7440-31-5	99.5	1.0	130.62071	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.13128	mg	
Material	2	Carbon Steel				1.0	4617.5	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.05	1.0	2.30875	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.46175	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.02	1.0	0.9235	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.15	1.0	6.92625	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.1	1.0	4.6175	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.046175	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.46175	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	4.6175	mg	
Substance	3	Iron	Supplier	7439-89-6	97.9335	1.0	4522.07936	mg	
Substance	3	Molybdenum	Supplier	7439-98-7	0.75	1.0	34.63125	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.035	1.0	1.61612	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.6	1.0	27.705	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.08	1.0	3.694	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0230875	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	4.6175	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	2.30875	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.46175	mg	
Material	2	Copper Plate				1.0	80.38474	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.08038474	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	1.0	80.30436	mg	
Sub-Item	1	1-204570-8				1.0	2626.072284	mg	
Material	2	Tin Plate				1.0	119.505942	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	0.4	1.0	0.47802	mg	
Substance	3	Tin	Supplier	7440-31-5	99.5	1.0	118.90841	mg	

Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.11951	mg	
Material	2	Carbon Steel				1.0	2458.0	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.08	1.0	1.9664	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.02	1.0	0.4916	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.02	1.0	0.4916	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.2458	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.02	1.0	0.4916	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.15	1.0	3.687	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	2.458	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.2458	mg	
Substance	3	Molybdenum	Supplier	7439-98-7	0.75	1.0	18.435	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.4	1.0	9.832	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.1	1.0	2.458	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.02458	mg	
Substance	3	Iron	Supplier	7439-89-6	98.1785	1.0	2413.22753	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	1.229	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.2458	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.01229	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	2.458	mg	
Material	2	Copper Plate				1.0	48.566342	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.04856634	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	1.0	48.51778	mg	
Sub-Item	1	788604-1				2.0	301.70686328	mg	
Material	2	Tri Chrome Film				2.0	0.00686328	mg	
Substance	3	Silicate(2-), hexafluoro-, hydrogen (1:2)	Supplier	16961-83-4	30.0	2.0	0.00205898	mg	
Substance	3	Unspecified ROHS Compliant Substance	Supplier	Unspecified Compliant Substance	10.0	2.0	6.8633E-4	mg	
Substance	3	Chromium chloride (CrCl3), hydrate (1:6)	Supplier	10060-12-5	60.0	2.0	0.00411797	mg	
Material	2	Carbon Steel				2.0	299.1	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	2.0	0.002991	mg	
Substance	3	Manganese	Supplier	7439-96-5	1.15	2.0	3.43965	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.35	2.0	1.04685	mg	
Substance	3	Iron	Supplier	7439-89-6	97.727501	2.0	292.30296	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.15	2.0	0.44865	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.02991	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.09	2.0	0.26919	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	0.02991	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	0.002991	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.2991	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	2.0	0.02991	mg	N/A
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	0.0014955	mg	N/A
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.349999	2.0	1.04685	mg	6(a) Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0.35% lead by weight
Substance	3	Nickel	Nickel	7440-02-0	0.05	2.0	0.14955	mg	
Material	2	Zinc Plate				2.0	2.6	mg	
Substance	3	Zinc	Supplier	7440-66-6	100.0	2.0	2.6	mg	
Sub-Item	1	787727-1				1.0	2032.0	mg	
Material	2	PA66-GF25				1.0	2032.0	mg	
Substance	3	Benzenamine, reaction products with aniline hydrochloride and nitrobenzene	Supplier	101357-15-7	4.0	1.0	81.28	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	6.0	1.0	121.92	mg	

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.5	1.0	71.12	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	61.5	1.0	1249.68	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	25.0	1.0	508.0	mg	
Sub-Item	1	787731-1				1.0	2021.0	mg	
Material	2	PA66-GF25				1.0	2021.0	mg	
Substance	3	Benzenamine, reaction products with aniline hydrochloride and nitrobenzene	Supplier	101357-15-7	4.0	1.0	80.84	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	6.0	1.0	121.26	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.5	1.0	70.735	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	61.5	1.0	1242.915	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	25.0	1.0	505.25	mg	