

REV. 1 1/22/93


COIL: @ 25°C	
RESISTANCE	330 OHMS ± 10%
NOMINAL VOLTAGE	12.0 VDC
MUST OPERATE	6.1 VDC
MUST RELEASE	.61 VDC

ENVIRONMENT:

VIBRATION	10	CPS TO	2000	CPS @	20	g's
SHOCK	100	g's	6 ± 1	MS. DURATION		
TEMPERATURE	-65	°C TO	+125	°C		

NOTES: _____

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO
1 AMP 28 VDC RESISTIVE
100,000 OPERATIONS

DR. J.P. 10/19/87 CK. V2495 JMS



CUST. C. I. I. STD.
 CUST. NO. _____

TYPE "MFW" RELAY

MFW1201K00