

REV. 1 9/12/97

COIL: @ 25°C


RESISTANCE	2500 OHMS ± 10%
NOMINAL VOLTAGE	30.0 VDC
MUST OPERATE	17.7 VDC
MUST RELEASE	1.50 VDC

ENVIRONMENT:

VIBRATION	10	CPS TO	3000	CPS @	30	g's
SHOCK	75	g's	6	MS. DURATION		
TEMPERATURE	-65	°C TO	+125	°C		

NOTES: OPERATE TIME 2.0 MS MAX; RELEASE TIME 4.0 MS MAX; CONTACT BOUNCE 1.5 MS MAX  
 TERMINAL FINISH SOLDER DIPPED. BUILT IN ACCORDANCE WITH MIL-R-39016

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1 AMP  
 28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 10/16/95 *CK* 9/12/97

**COMMUNICATIONS**  
**INSTRUMENTS, INC.**

CUST. C. I. I. STD.  
 CUST. NO. \_\_\_\_\_

TYPE MGAD RELAY

**MGAPD-30**