




COIL: @ 25°C

RESISTANCE 1560 OHMS

NOMINAL VOLTAGE 26.5 VDC

MUST OPERATE 14.2 VDC

MUST RELEASE 1.37 VDC

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's

SHOCK 75 g's 6 MS. DURATION


TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 2.0 MS MAX

RELEASE TIME 4.0 MS MAX

CONTACT BOUNCE 1.5 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1 AMP
28 VDC RESISTIVE 100,000 OPERATIONS MIN.

DR. R.B. 9/11/95

CK. 9/11/95



COMMUNICATIONS
INSTRUMENTS, INC.

CUST. C.I.I. STD.

CUST. NO.

TYPE "MGAD" RELAY

MGAPDF-26W