


COIL: @ 25°C
 RESISTANCE 3300 OHMS \pm 10%
 NOMINAL VOLTAGE 26.0 VDC
 MUST OPERATE 14.0 VDC
 MUST RELEASE 1.4 VDC

ENVIRONMENT:
 VIBRATION 10 CPS TO 3000 CPS @ 30 g's
 SHOCK 75 g's 6 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 4 MS MAX
RELEASE TIME 2 MS MAX
CONTACT BOUNCE 1.5 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 3/10/98 | PK ERRV 3/10/98

COMMUNICATIONS INSTRUMENTS, INC.

CUST. C. I. I.
 CUST. NO. STD. TYPE "MS" RELAY

MSWG-26