



100P1381-17-1-C-L35

SERIES
SHELL SIZE (SEE TABLE 1)
MATERIAL AND
PLATING/FINISH (SEE TABLE 2)
LENGTH

TABLE 1

SHELL SIZE	A THREAD	B MAX	C +0/-0,15	D MAX	T
09	M12 x 1.0	18,0	10,57	8,80	6,8
11	M15 x 1.0	21,0	13,56	12,07	10,3
13	M18 x 1.0	24,5	16,58	14,96	13,6
15	M22 x 1.0	29,0	20,57	18,14	16,3
17	M25 x 1.0	32,5	23,57	21,31	19,5
19	M28 x 1.0	35,5	26,57	24,00	21,9
21	M31 x 1.0	37,0	29,57	27,18	25,2
23	M34 x 1.0	40,0	32,56	30,35	28,3
25	M37 x 1.0	43,5	35,56	33,53	31,5

TABLE 2

CODE	MATERIAL / PLATING
1-C	ALUMINIUM / ELECTROLESS NICKEL
1-B	ALUMINIUM / CADMIUM OLIVE DRAB OVER ELECTROLESS NICKEL
1-ZB	ALUMINIUM / ZINC COBALT OLIVE DRAB OVER ELECTROLESS NICKEL
4-J	STAINLESS STEEL / PASSIVATE
2-Z	NICKEL ALUMINIUM BRONZE / SHOT BLAST NON REFLECTIVE

LIST NOT EXHAUSTIVE - FOR COMPREHENSIVE LIST AND SPECS SEE WEBSITE

DRAWN	DIW	DATE 12/02/2001	3RD ANGLE PROJECTION NOT TO SCALE	POLAMCO LTD WESTON LOCK LOWER BRISTOL ROAD BATH BA2 1EP	PAGE 1	UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES
SALES APPR						
DESIGN APPR			THIS DRAWING IS COPYRIGHT AND THE PROPERTY OF POLAMCO LTD. IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.	ASSY USED ON: MIL-DTL-38999 SERIES III & IV	MATERIAL	
QUAL APPR					NCAGE CODE U5792	
ISSUE 2	DCR 4180				TITLE: EXTENDER ADAPTOR	DRAWING NO: P3779
WEIGHT	GENERAL TOL LINEAR +/-0.1MM ANGULAR +/- 1°		PART NUMBER: 100P1381-**-1-C-L35			