

REV. 1 8/25/98

COIL: @ 25°C

RESISTANCE 800 OHMS \pm 10%

NOMINAL VOLTAGE 12.0 VDC

MUST OPERATE 7.0 VDC

MUST RELEASE 0.64 VDC

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's

SHOCK 75 g's 6 MS. DURATION


TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 4.0 MS MAX

RELEASE TIME 2.0 MS MAX

CONTACT BOUNCE 1.5 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1 AMP
28 VDC RESISTIVE 100,000 OPERATIONS MIN

DR. R.B. 11/11/97 *CK* *11/25/98*

COMMUNICATIONS
INSTRUMENTS, INC.

CUST. TELEDYNE

CUST. NO. ER134M4-12A

TYPE PRMGS RELAY

PRMGSC-12XW