




REV. 0
DCO 143221

COIL: @ 25°C

RESISTANCE 100 OHMS $\pm 10\%$

NOMINAL VOLTAGE 5.0 VDC

MUST OPERATE 2.6 VDC

MUST RELEASE 0.23 VDC

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's

SHOCK 75 g's 6 MS. DURATION


TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 4.0 MS MAX

RELEASE TIME 2.0 MS MAX

CONTACT BOUNCE 1.5 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 1 AMP

28 VDC RESISTIVE 100,000 OPERATIONS MIN

DR. ASB 9/20/01

Handwritten signature and date: 9/20/01

CII Technologies
advanced control electronic solutions

CUST: CII

CUST. NO. STANDARD REV.

"PRMGS" RELAY

PRMGSCG-5XW