<b>tyco</b> Electronics	Tyco Electroni 300 Constitutio Menlo Park, C	cs Corporation on Drive A 94025 USA	Raychem	Specification This Issue: Date: Replaces:	<b>RT-1370</b> Issue 2 September 12, 1995 Issue 1		
Rayaten Polyolefin Molded Components Electrically Shielded, Flame Retarded, Semi-Rigid, Heat-Shrinkable							
1.	<b>SCOPE</b> This specification covers the requirements for one type of semi-rigid, electrical insulating and shielded molded component which, when used with S-1184 or S-1185 adhesives, is designed to control electromagnetic interference (EMI). The dimensions of these molded components will reduce to a predetermined size upon the application of heat in excess of $121^{\circ}C$ (250°F).						
2.	<b>APPLICABLE DOCUMENTS</b> This specification takes precedence over documents referenced herein. Unless otherwise specified, the latest issue of referenced documents applies. The following documents form a part of this specification to the extent specified herein.						
2.1	GOVERNMEN <u>Military</u> MIL-I-81765 MIL-T-5624 MIL-L-23699	JT-FURNISHED DOCUMENTS Insulated Components, Molded Electrical, Heat- Shrinkable, General Specification for Turbine Fuel, Aviation, Grades JP-4 and JP-5 Lubricating Oil, Aircraft Turbine Engine, Synthetic Base					
2.2	OTHER PUBLICATIONS						
	American Socie	ty for Testing and Materials (ASTM)					
	D 412	Standard Method of T	Test for Rubber Prope	rties in Tension			
	(Copies of ASTM publications may be obtained from the American Society for Testing and Materials, 1916 Race, Philadelphia, Pennsylvania 19103.)						
	Raychem Corporation						
	RT-301	Specification for The Heat-Shrinkable	rmofit* Polyolefin Mo	olded Components, Flam	e Retarded, Semi-Rigid,		
	RT-1011 RT-1084 RT-1085 202S152-3S	Specification for The Specification for The Specification for The Specification Control	rmofit Adhesive S-11 rmofit S-1184 Conduc rmofit S-1185 Conduc Drawing for Boot, St	25, Epoxy, Flexible ctive Epoxy Adhesive ctive Hot Melt Adhesive raight, Heat-Shrinkable,	with Lip, Shielded		
	*Trademark of Raychem Corporation						

# 3. **REQUIREMENTS**

# 3.1 MATERIAL

The molded components shall be fabricated from a crosslinked, thermally stabilized, flame-retarded, modified polyolefin composition. They shall be internally metal plated to form a composite structure which shall provide an electrical shield.

# 3.2 APPEARANCE

The molded components shall be homogeneous and essentially free from pinholes, bubbles, and inclusions.

## 3.3 COLOR

The molded components shall be black.

### 3.4 PROPERTIES

The molded polyolefin components shall have met the requirements of RT-301, and MIL-I-81765/1 Type 1 before plating. The composite components shall meet the requirements of Table I.

# 4. QUALITY ASSURANCE PROVISIONS

# 4.1 CLASSIFICATION OF TESTS

# 4.1.1 Qualification Tests

Qualification tests are those performed on plated molded slabs and plated components submitted for qualification as satisfactory products and shall consist of all tests listed in this specification.

## 4.1.2 <u>Acceptance Tests</u>

Acceptance tests are those performed on plated molded slabs and plated components submitted for acceptance under contract. Acceptance tests shall consist of the following: visual examination, dimensions, dimensional recovery, tensile strength, ultimate elongation and heat shock.

## 4.2 SAMPLING INSTRUCTIONS

# 4.2.1 <u>Preparation of Test Samples</u>

Molded slabs and molded components shall be prepared as follows: unless otherwise specified, tests shall be carried out on a molded test slab of material  $6 \ge 6 \ge .010$  inches

 $(152 \times 152 \times 1.9 \pm .25 \text{ mm})$ . The test slab shall be electroplated with metal on one face. The thickness of metal shall be representative of the thickness deposited on the molded component. The standard molded component for qualification testing shall be 202S152-3S, unless otherwise specified.

### 4.2.2 Qualification Test Samples

Qualification test samples shall consist of six plated molded slabs as described in Section 4.2.1, and the number of plated molded components specified by the test program. The molded slabs shall be fabricated from the same lot of material and shall be subject to the same degree of crosslinking as the molded components.

# 4.2.3 Acceptance Test Samples

Acceptance test samples shall consist of specimens cut from a plated molded slab as described in Section 4.2.1, and plated molded components selected at random. The plated molded slab shall be fabricated from the same lot of material and shall be subjected to the same degree of crosslinking as the molded components. A lot of components shall consist of all plated molded components of the same part number from the same lot of material, from the same production run, and offered for inspection at the same time.

# 4.3 TEST PROCEDURES

# 4.3.1 <u>Dimensional Recovery</u>

Three samples of plated molded components, as supplied, shall be measured for dimensions. The samples then shall be conditioned for 15 minutes in a  $200 \pm 2^{\circ}C$  ( $392 \pm 4^{\circ}F$ ) oven, or equivalent, cooled to room temperature, and remeasured.

### 4.3.2 <u>Tensile Strength and Ultimate Elongation</u>

Three specimens cut from a plated molded slab using Die D of ASTM D 412 shall be tested for tensile strength and ultimate elongation in accordance with ASTM D 412, Method A. Jaw separation rate shall be  $4 \pm 0.4$  inches (100  $\pm 10$  mm) per minute. Test shall be conducted at room temperature.

# 4.3.3 <u>Metal Adhesion</u>

The metal surface of a plated test slab shall be wiped clean with 1,1,1 trichloroethane. Five  $6 \times 3/8$ -inch (150 x 10 mm) strips shall be cut from the clean test slab. A strip of aluminum foil, approximately .006 inches (.15 mm) thick, shall be bonded to the plated side of each strip of the test slab with S-1110\* adhesive (or equivalent) to form a T-peel assembly. Leave 3 inches (75 mm) of the assembly unbonded. Bond the assembly using a roller and applying four firm rolling strokes.

The five specimens shall be subjected to 180 degree peel by clamping the unbonded end of the test specimen into one jaw of a tensile machine and the unbonded end of the aluminum strip into the other jaw. The rate of jaw separation shall be  $2 \pm .2$  inches  $(50 \pm 5 \text{ mm})$  per minute. The mean peel force (calculated by averaging the loads found from several equispaced points along the length, omitting the first and last 10% of the peel) for each specimen shall be recorded and the mean of the five recorded measurements reported as the peel strength.

# 4.3.4 <u>Shielding Efficiency</u>

All shielding tests are performed on Rayaten components recovered onto triaxial aerial test fixtures similar to those shown in Figure 1A or 1B as appropriate. The test method uses the current injection principle on a Rayaten specimen fixtured on a triaxial test circuit. Instruments are used to detect electrical variations in the circuit caused by the penetration of given potential through the shield causing an induced voltage on the center conductor of the fixture. This induced voltage is to be measured at various frequencies up to and including 100 MHz. A minimum level of shielding efficiency is specified for each type of Rayaten part (boot or transition) as defined in Table 1.

# 4.3.4.1 <u>Preparation of Test Specimens</u><sup>(1)</sup>

- a) Select the appropriate test aerial fixture for the component under test.
- b) Clean all bond interfaces with 1,1,1 trichloroethane or other suitable cleaning solvent and allow to dry.
- c) Apply Raychem type S-1185 conductive adhesive to the aerial for acceptance test. For qualifications tests, apply Raychem type S-1184 and S-1125. (See Figure 1A.)
- d) Position the component on the aerial fixture and begin shrinking at the "H" end, using Raychem CV 5000 Hot Air Gun or equivalent, and continuing to the "J" end. Allow the component to conform freely to the aerial without manual manipulation. Allow the assembly to cool to room temperature.
- e) Install the aerial test assembly (with component) in the properly sized metal test box. Installation is accomplished by means of soldering the resistor wire of the aerial fixture to one connector and fixing the other end by means of the special

fitting and brass clamping nut as shown in Figure 1A or 1B as appropriate.

f) Connect the metal box containing the test aerial to the test circuit as shown in Figure 2. Allow the component to cool to room temperature prior to testing.

\*Mastic Tape, Tackified Rubber, obtainable from Raychem Corporation

#### 4.3.4.2 <u>Test Procedure</u>

The suggested test circuit is shown in Figure 2. Approved equivalent circuits may be used.

#### Sequence 1

Terminate the measurement circuit at the variable attenuator using a 50 ohm 12 watt load. Connect the triaxial test fixture to the circuit and inject a signal from the function generator onto the triaxial leakage test box over the range of frequencies specified in Sequence 2. The resultant induced voltage on the center conductor is received and stored in the spectrum analyzer.

#### Sequence 2

Terminate the triaxial test fixture using a 50 ohm 12 watt load. Connect the variable attenuator in circuit with the function generator.

Pass a signal from the function generator through the variable attenuator and adjust it until it matches the stored voltage signal from the test specimen.

Take measurements at frequencies from 3 kHz through 100 MHz.

(1) Related Standards

BS 2316 Radio Frequency Cables IEC 96 Radio Frequency Cables VG95373Screening Test Methods

Record the readings from the variable attenuator at the selected frequencies as the shielding efficiency.

#### 4.3.5 Heat Shock

Six specimens, five prepared in accordance with 4.3.3, and one prepared in accordance with 4.3.4.1 a-d shall be conditioned for  $30 \pm 5$  minutes in a  $200 \pm 5^{\circ}C$  ( $392 \pm 9^{\circ}F$ ) mechanical convection oven with an air velocity of from 100 to 200 feet (30.5 to 61.0 m) per minute past the specimens. They shall be tested for metal adhesion for acceptance tests plus shielding efficiency for qualification testing.

### 4.3.6 Heat Aging

Eleven specimens, three prepared in accordance with 4.3.2 for ultimate elongation, five prepared in accordance with 4.3.3 for metal adhesion, and three plated molded components prepared in accordance with 4.3.4.1 a-d, shall be conditioned for  $168 \pm 2$  hours in a  $160 \pm 3^{\circ}$ C ( $320 \pm 5^{\circ}$ F) mechanical convection oven with an air velocity of from 100 to 200 feet per minute past the specimens. After conditioning, the specimens shall be removed from the oven and cooled to

 $23 \pm 3^{\circ}$ C ( $73 \pm 5^{\circ}$ F). The specimens shall then be tested for ultimate elongation, metal adhesion, and shielding efficiency.

### 4.3.7 <u>Thermal Cycling</u>

Three molded components prepared in accordance with 4.3.4.1 a-d and three strip specimens prepared in accordance with 4.3.3 shall be subjected to thermal cycling as follows:  $4 \pm 1/4$  hours. at  $150 \pm 3^{\circ}C$  ( $302 \pm 5^{\circ}F$ ),  $1 \pm 1/4$  hr at  $23 \pm 3^{\circ}C$  ( $73 \pm 5^{\circ}F$ ),  $4 \pm 1/4$  hours. at  $-55 \pm 3^{\circ}C$  ( $-67 \pm 5^{\circ}F$ ) and  $1 \pm 1/4$  hr at  $23 \pm 3^{\circ}C$  ( $73 \pm 5^{\circ}F$ ). After completion of three cycles the shielding efficiency and metal

 $1 \pm 1/4$  hr at  $23 \pm 3^{\circ}$ C ( $73 \pm 5^{\circ}$ F). After completion of three cycles the shielding efficiency and meta adhesion of the molded components shall be measured.

#### 4.3.8 Fluid Resistance

Three specimens prepared in accordance with 4.3.2 and three plated molded components prepared in accordance with 4.3.4.1 a-d shall be completely immersed in each of the fluids listed in Table 1 for 24 hours at  $23 \pm 3^{\circ}$ C ( $73 \pm 5^{\circ}F$ ). The volume of the fluids shall be not less than 20 times that of the specimens. After immersion the plated molded components shall be allowed to air dry for

18 to 24 hours at room temperature and shall then be tested for shielding efficiency in accordance with 4.3.4. The tensile test specimens cut from molded slabs shall be lightly wiped and then air dried for 30 to 60 minutes at room temperature, visually examined for delamination of the metal from the polymer and then tested for tensile strength and ultimate elongation in accordance with 4.3.2.

# 4.4 REJECTION AND RETEST

Failure of any sample to comply with any one of the requirements of this specification shall be cause for rejection of the lot represented. Material which has been rejected may be replaced or reworked to correct the defect and then resubmitted for acceptance. Before resubmitting, full particulars concerning the rejection and the action taken to correct the defect shall be furnished to the inspector.

# 5. PREPARATION FOR DELIVERY

### 5.1 PACKAGING

The molded components shall be packaged in accordance with good commercial practice. The exterior shipping container shall be not less than 125 pound test fiberboard.

# 5.2 MARKING

Each molded component shall be distinctly identified on the part and/or the bag with the manufacturer's name or symbol and the manufacturer's part number, lot number and date of manufacture.







PROPERTY	UNIT	REQUIREMENTS	TEST METHOD
ELECTRICAL			
Shielding Efficiency	dB	Boots, 70 minimum Transitions,	Section 4.3.4
3 kHz through 100 MHz		65 minimum	
PHYSICAL			
Visual Examination		Pass	Section 3.2
Dimensions	Inches (mm)	In accordance with	Section 4.3.1
Dimensional Recovery	Inches (mm)	specification control drawing	
Tensile Strength	psi (MPa)	1500 minimum (10.3)	Section 4.3.2
			ASTM D 412,
Ultimate Elongation	Percent	250 minimum	Method A
Metal Adhesion	lbs/inch (N/cm)	8.5 minimum (15)	Section 4.3.3
Heat Shock		No dripping, flowing or cracking	Section 4.3.5
30 minutes at 200°C ( <i>392°F</i> )			
Followed by test for:			
Metal Adhesion	lbs/inch	8.5 minimum (15)	Section 4.3.3
	(N/cm)		
Shielding Efficiency(1)	dB	Boots, 70 minimum Transitions,	Section 4.3.4
3 kHz through 100 MHz		65 minimum	
Heat Aging			Section 4 3 6
168 hours at 160°C ( $320^{\circ}F$ )			Section 1.5.0
Followed by tests for:			
Ultimate Elongation	Percent	250 minimum	Section 4.3.2
Metal Adhesion	lbs/inch	8.5  minimum  (15)	Section 4.3.3
	(N/cm)		Section 1.5.5
Shielding Efficiency	dB	Boots, 70 minimum Transitions	Section 4.3.4
3 kHz through 100 MHz		65 minimum	
Thermal Cycling Range			Section 4.3.7
-55°C to 150°C			
$(-67^{\circ}F \text{ to } 302^{\circ}F)$			
Followed by tests for:			
Metal Adhesion	lb/inch (N/cm)	8.5 minimum (15)	Section 4.3.3
Shielding Efficiency	dB	Boots, 70 minimum Transitions,	Section 4.3.4
30 Hz through 100 MHz		65 minimum	
CHEMICAL		No delamination	Section 4.3.8
Fluid Resistance			
24 hours at 23°C ( $73^{\circ}F$ )J			
P-4 Fuel (MIL-T-5624)			
Skydrol* 500			
Lubricating Oil (MIL-L-23699)			
Followed by tests for:			
Tensile Strength	psi (MPa)	1150 minimum (8)	Section 4.3.2
Ultimate Elongation	Percent	200 minimum	Section 4.3.2
Shielding Efficiency	dB	Boots, 70 minimum Transitions,	Section 4.3.4
3 kHz through 100 MHz		65 minimum	

# TABLE 1 Requirements

(1)Qualification only\*Trademark of Monsanto Company