File E28476	Vol. 60	Sec. 8	Page 1	Issued:	2011-09-17
		and Report			

DESCRIPTION

PRODUCT COVERED:

USR, CNR Component Connectors, Header, Cat. No. 2029030-2.

GENERAL:

These devices are multi-pole connectors intended for factory assembly on printed wiring boards where the acceptability of combinations is determined by Underwriters Laboratories Inc. The devices are identified as follows:

USR indicates investigation to United States Standards, UL 1977.

 $\ensuremath{\texttt{CNR}}$ indicates investigation to Canadian National Standards, C22.2 No. 182.3.

RATINGS: Flammability - V-0

File E28476	Vol. 60	Sec. 8	Page 2	Issued:	2011-09-17
		and Report			

TECHNICAL CONSIDERATIONS (NOT FOR FIELD REPRESENTATIVE'S USE):

Use - For use only in or with complete equipment where the acceptability of the combination is determined by Underwriters Laboratories Inc.

Conditions of Acceptability - The following are among the considerations to be made when evaluating the device in the end-use product.

Interruption of Current

1. These devices are not suitable for interrupting the flow of current by connecting or disconnecting the mating connector.

Current-Carrying Capability and Current Ratings

- 2. These devices have not been subjected to the Temperature test and as a result do not have an assigned current rating. The device's current carrying capability is to be reviewed in the end-use by measuring temperatures on the connector housing and/or terminals when current is flowing through the connector under conditions of normal use. Insulating Materials
- 3. These devices employ insulating materials with properties as tabulated below at the minimum thickness employed in the connector housing, the suitability of the insulating materials based on the documented values shall be determined in the end-use application. Please note the values specified in the table when multiple materials are indicated represent the minimum values for the group of materials.

Cat Nos.	Insulating	Measured	Flame	HWI	HAI	RTI	RTI	Max
	Material (#)	Minimum	Class			Elec	Str	Operating
		Thickness						Temp, ⁰ C
2029030-2	A	0.36 mm	V-0	0	2	120	120	120

(#) - Code for Insulating Body Material.

A. Tyco Raw Material DSM Engineering Plastics B V (E47960), Type NC1101A(h7). Dielectric strength (kV/mm): -

CTI: 0

Miscellaneous

4. The enclosure of the device has live parts that may be exposed to user contact when the connector is energized. The device is suitable for use only within an acceptable enclosure.