


CUSTOMER DRAWING




Product Name	Mark	Product Dimensions		
		A±1.75 [A±0.070]	øB min	øC min
SO63-1-9036-22	SO631R	16.50 [0.650]	1.90 [0.075]	2.65 [0.105]
SO63-1-9036-20				
SO63-1-9036-18				
SO63-2-9036-22	SO632R	16.50 [0.650]	2.65 [0.105]	3.55 [0.145]
SO63-2-9036-20				
SO63-2-9036-18				
SO63-3-9036-22	SO633R	16.50 [0.650]	4.30 [0.170]	5.00 [0.200]
SO63-3-9036-20				
SO63-3-9036-18				
SO63-4-9036-22	SO634R	19.10 [0.750]	5.95 [0.235]	6.50 [0.255]
SO63-4-9036-20				
SO63-4-9036-18				
SO63-5-9036-22	SO635R	19.10 [0.750]	7.00 [0.275]	7.60 [0.300]
SO63-5-9036-20				
SO63-5-9036-18				

MATERIALS

- INSULATION SLEEVE: Heat-shrinkable, transparent blue, radiation cross-linked modified polyvinylidene fluoride. Marked per table.
- SOLDER PREFORM WITH FLUX AND THERMAL INDICATOR RING:
SOLDER: TYPE Sn63 per ANSI / J-STD-006.
FLUX: TYPE ROL1 per ANSI / J STD-004.
THERMAL INDICATOR RING: Fusible alloy with melt point of 221°C.
- MELTABLE RINGS: Environment resistant fluorocarbon-based thermoplastic
- PRE-INSTALLED LEAD: Raychem 55PC6121-GA. "GA"=size (AWG) of lead, color: white with 2 black stripes.

APPLICATION

- These parts are designed to provide an environment resistant shield termination on cables, rated for 125°C min. having tin or silver-plated shields, and jackets compatible with the insert material. Consult TE Connectivity.
- When properly installed, these parts will meet the performance requirements of Raychem RT-1404.
- Part selection: Measure cable jacket diameter at its maximum point. Select the smallest terminator that has a "B" diameter larger than the cable diameter.
- Cable is to be stripped to expose 6.0 -7.5mm [0.235-0.295] of shield.
- Part may be installed using any TE Connectivity-approved convection or infra-red heating tool. Tools must be equipped with a suitable reflector. For detailed assembly instruction see Raychem RCPS-100-70.

		Raychem Devices	TITLE: SOLDERSLEEVE DEVICE WITH PRE-INSTALLED LEAD, IMMERSION RESISTANT			
Unless otherwise specified dimensions are in millimeters. [Inches dimensions are shown in brackets]			DOCUMENT NO.:			
			SO63-X-9036-GA			
TOLERANCES: 0.00 N/A 0.0 N/A 0 N/A	ANGLES: N/A ROUGHNESS IN MICRON	TE Connectivity reserves the right to amend this drawing at any time. Users should evaluate the suitability of the product for their application.	Revision: C1		Issue Date: 27OCT2023	
PREPARED BY: M. FORONDA	DATE: 17FEB2017	CAGE CODE: 06090	ECN: ECN-23-234831	SCALE: ---	SIZE: A	SHEET: 1 of 1

© 2022 TE Connectivity Ltd. Family of Companies. All Rights Reserved.

*TE Connectivity, TE connectivity (logo), Raychem, Thermofit, SolderSleeve are trademarks