


TOL = $\pm .010$

REV. 0
DCO 64265

COIL: @ 25°C	
RESISTANCE	100 OHMS $\pm 10\%$
NOMINAL VOLTAGE	12.0 VDC
MUST OPERATE	6.5 VDC
MUST RELEASE	4.2 VDC MAX, 0.92 VDC MIN.

ENVIRONMENT:	
VIBRATION	10 Hz TO 2000 Hz @ 15 g's
SHOCK	100 g's 6 MS. DURATION
TEMPERATURE	-65 °C TO +125 °C
NOTES:	OPERATE & RELEASE 7 MS MAX. (INCLUDING BOUNCE)

CUSTOMER DATA SHEET



CONTACT RATING:	LOW LEVEL TO
	2 AMP 28 VDC RESISTIVE
	100,000 OPERATIONS

DR. ASB 6 DEC 02 CK. 2/6/2008



CUST. QPL
CUST. NO. M39016/40-016 REV.

"SR" RELAY

SR-7616