


626 Pneumatic Tool System The Effortless Alternative to Hand Crimping



Fast Facts

Effortless crimping for a broad range of terminals, either bench-mounted or hand-held for working in cramped quarters.

- Lightweight tool eliminates pysical force required by hand tools
- · Hand- or foot-switch operation
- Termination wire range from 26-6 AWG [0.12-13.0mm²], plus coaxial and fiber optic cable
- Works with existing TE-compatible crimp heads and die sets
- Ratchet control option provides complete crimp cycle, eliminating partial crimps
- Use rotating head assembly to reach difficult termination locations
- Engineered and manufactured using processes independently certified to internationally recognized quality standards ISO-9001:2000 and elecommunications Industry Standard TL 9000



The 626 System Works Where and How You Need It

Using 626 adapters, tools previously restricted to prototype or limited production applications can now be used in low to medium bench production and harness assembly operations. Because the 626 crimp head can be rotated to any angle, you can also work on those difficult terminations in confined equipment cabinets or enclosures.

with fewer mistakes.

aligning the wire and terminal. Now you can crimp faster and

Looking for the complete crimp cycle control provided by the mechanical ratchet in premium CERTI-CRIMP hand tools? The available 626 System ratchet tool holders produce a complete crimp cycle by simply pressing a switch. Dies will fully bottom before you can open the jaws to release the crimped product.

Protect Your Investment

The 626 System's power unit works with a variety of adapters and tool holders, so you can continue to work with your existing crimp heads and die sets.

Need More Information?

For information about tooling, call 888-777-5917 or 717-810-2080 or e-mail toolingsales@te.com.

626 Pneumatic System Power Unit



| Outside Diameter | 45 mm [1.8] |
|------------------|---|
| Length | 225 mm [8.88] for foot actuated unit |
| | 230 mm [9.00] for hand actuated unit |
| Grip Span | 55 mm [2.19] over button/handle |
| Mass | 0.60 kg [1.32 lbm] for foot acuated unit |
| 1 1055 | 0.72 kg [1.58 lbm] for hand actuated unit |
| Air Pressure | 6.21-6.89 bar [90-100 psi] |
| Air Displacement | 0.00018 m³ [11.14 in³] |
| Air Supply Hose | 3.05 m [10 ft] long, 4.8 mm [3/16] l.D. |
| All Supply Hose | with 1/8 in NPT fitting |
| Cycle Time | 0.7-0.8 s (for 16-14 AWG [1.3-2 mm²] |
| | PIDG Terminals) |

Micro Pneumatic System Power Unit

| Outside Diameter | 45 mm [1.8] |
|------------------|---|
| Length | 146.5 mm [5.75] |
| Grip Span | 55 mm [2.19] over button/handle |
| Mass | 0.70 kg [1.5 lbm] |
| Air Pressure | 6.21-6.89 bar [90-100 psi] |
| Air Displacement | 0.00018 m³ [11.14 in³] |
| Air Supply Hose | 3.05 m [10 ft] long, 4.8 mm [3/16 in] I.D. with 1/8 in NPT fitting |
| Cycle Time | 0.7-0.8 s (for 16-14 AWG [1.3-2 mm²] PIDG Terminals) |



Big Return in a Micro Package

Does your crimping application demand even more accessibility and flexibility than the 626 System offers? The Micro Pneumatic Tool System terminates wires in the 26–14 AWG [0.12–2 mm²] range,* but with a smaller and lighter power unit. Weighing in at only 0.7 kg [1.5 lb] and just 146.5 mm [5.75 in] long, the hand-actuated Micro System is compatible with three different head systems.

* With the exception of the SOLISTRAND head combination, which crimps 22–10 AWG [0.3–2 mm²] combinations.

Die Interchangeability

For the ability to change dies quickly when needs change, whether from one terminal type to another or from tool to tool when workload and environment change, consider the SDE family of tools and dies. For more information, see Catalog 1773379-1.



| SDE Compatible Kit | | | | | |
|---|---------------|--------------------------|--|--|--|
| Complete tool with hand-held power unit | P/N 1213855-1 | 0.3 - 6.0mm2 (22-10 AWG) | | | |



| Tool and Adapter Holders* | | | | | |
|-----------------------------|--|-------------------|-------------------|--|--|
| | Large Tool Holder Small Tool Holder Adapter Holder | | | | |
| Length (with Head Assembly) | 100 [3.88] | 70 [2.75] | 70 [2.75] | | |
| Weight (with Head Assembly) | 0.76 kg [1.68 lb] | 0.44 kg [0.96 lb] | 0.44 kg [0.96 lb] | | |

^{*}Measurements are averages.



| Bench Mount Assembly* | | | |
|---------------------------|--|--|--|
| Base Size | 200 × 200 [8 × 8] | | |
| Weight | 2.9 kg [6.5 lb] | | |
| Bench Mounting Dimensions | Base has two, 1/4-20 tapped holes on 150 [6] centerlines | | |
| Part No. | 856 4 02-1 | | |

st Not for use in the European Community.


Need More Information?

For information about tooling, call 888-777-5917 or 717-810-2080 or e-mail toolingsales@te.com.

System Configurations and Ordering Information

626 Pneumatic Tool System

A basic 626 Pneumatic Tool System requires a power unit, a tool holder, a head assembly, and a die set, when applicable. Tool holder assemblies (i.e., tool holder and cam) accept the crimping heads, adapters, and die sets listed on pages 6 through 7.




For drawings or technical data, contact your TE Connectivitys sales engineer or call the Technical Support Center: 1-800-522-6752. Dimensions are in millimeters unless specified otherwise. Values in brackets are English equivalents unless specified otherwise. Specifications subject to change. Consult TE for latest specifications.

System Configurations and Ordering Information

Micro Pneumatic Tool System

A basic Micro Pneumatic Tool System requires a power unit, a tool holder, a head assembly, and a die set, when applicable. Tool holder assemblies (i.e., tool holder and cam) accept the crimping heads, adapters, and die sets listed on pages 7 and 8.



Note: Acemark adjacent to a crimping head or adapter indicates it conforms to European Union Directives in hand-held applications.

626 System Crimping Heads and Die Sets





| | Wire Size Range | | | | |
|---|-----------------|---------------|------------------------------|-----------------------------|--|
| Wire Size Range | AWG | mm² | Crimping Head Part Number | Instruction Sheet Number | Die Set Part Number |
| | 22-18 | 0.3-0.9 | | | |
| PIDG FASTON Receptacles (P/N Series 6409 Only) | 16-14 | 1.3-2 | | | |
| (, | 12-10 | 3-6 | 679305-1† | 100, 1000 | _ |
| | 22-16 | 0.3-1.3 | (TETRA-CRIMP) | 408-4099 | |
| PIDG Terminals and Splices, PLASTI-GRIP Terminals | 16-14 | 1.3-2 | | | |
| PLASTI-GRIP Terminals | 12-10 | 3-6 | | | |
| PIDG Terminals and Splices, PLASTI-GRIP Terminals | 16-14 HD, 12-10 | 1.3-2 HD, 3-6 | 679300-1 (€ | 408-4071 | _ |
| | 22-18 | 0.3-0.9 | | | 58079-3 |
| PLASTI-STRIP Terminals, Ultra-Fast Plus FASTON Receptacles | 16-14 | 1.3-2 | 679992-1†† | 408-4098 | 58080-3 |
| Ultra-Fast FASTON Tabs and | 22-18 | 0.3-0.9 | 1 | | 90390-3 |
| Receptacles | 16-14 | 1.3-2 | 1 | | 90391-3 |
| | 22-10 | 0.3-6 | 679301-1 (€ | | |
| SOLISTRAND Uninsulated Terminals and Splices | 8 | 8 | 1338757-1 €€ | 408-4072 | _ |
| and opines | 6 | 13 | 1338758-1 (€ | | |
| Adapter for PRO-CRIMPER III Die Sets | _ | _ | 679304-1 | 408-4070 | Request Catalog 82276 for listing of over 75 die sets. |
| Closed End Splices | ECV 18-8 | 0.9-8 | 189896-1 €€ | 408-4111 | |
| (Insulated) | CES 18-10 | 0.9-6 | 189466-1 € | 408-4175 | |
| STRATO-THERM Terminals and Splices | 22-10 | 0.3-6 | 217206-1 € | 408-4110 | _ |
| | 16-14 | 1.3-2 | 189447-1 (€ | 400.0000 | |
| COPALUM Terminals and Splices | 12-10 | 3-6 | 189444-1 (€ | 408-9989 | _ |
| and Spinces | 8 | 8 | 1320369-1♦€€ | 408-4366 | _ |
| TERMINYL Terminals | 8 | 8 | 904395-1 (€ | 408-4451 | _ |
| TERMI-FOIL Barrel Terminals, Strip Tap Terminals and Splices | 8 | 8 | 217923-1 €€ | 408-4171 | 305956-3 (0.016 [0.40] Max Foil Thk.) |
| | Ŭ | Ü | 21/923-1 (€ 408-41/1 | | 305956-8 (0.030 [0.75] Max Foil Thk.) |

[†] Equivalent to TETRA-CRIMP Hand Tool Part No. 59824-1; die set is NOT interchangeable.

Need More Information?

For information about tooling, call 888-777-5917 or 717-810-2080 or e-mail toolingsales@te.com.

^{††}Uses same die sets as Platform Die Hand Tool Part No. 58078-3.

[♦] Requires Hand Actuated Power Unit Part No. 189721-2 or Foot Actuated Power Unit Part No. 189722-2.

626 System Crimping Heads and Die Sets





| Crimping Heads and Die Sets for Small Tool Holders | | | | | | |
|--|-----------------|---------|--------------------|-----------------------------|--|--|
| | Wire Size Range | | Crimping Head Part | Instruction Sheet Number | | |
| Products Applied | AWG mm² | | Number | | | |
| | 22-14 | 0.3-2 | 354422-1 (€ | 408-9893 | | |
| Closed End Splices (Insulated) | EC 22-10 | 0.3-6 | 354422-2 (€ | 408-9906 | | |
| () | VS 22-16 | 0.3-1.3 | 217205-1 (€ | 408-9761 | | |
| DI ACTI CDID D C. I | 22-16 | 0.3-1.3 | 314868-1 (€ | 408-9775 | | |
| PLASTI-GRIP Butt Splices | 16-14 | 1.3-2 | 314869-1 € | | | |
| PIDG Terminals and Splices and PLASTI-GRIP Terminals | 22-16 | 0.3-1.3 | 314270-3 (€ | 400.0504 | | |
| | 16-14 | 1.3-2 | 314269-1 €€ | 408-9586 | | |
| | 22-16 | 0.3-1.3 | 314516-1 € | | | |
| SOLISTRAND Uninsulated Terminals and Splices | 16-14 | 1.3-2 | 314517-1 (€ | 400 0005 | | |
| | 14-12 | 2-3 | 314518-1 € | 408-9285 | | |
| | 22-10 | 0.3-6 | 189989-1 | | | |

Micro Pneumatic Crimping Heads

| Double Action Crimping Heads | | | | | |
|---|-----------------|---------|------------------------------|--|--|
| | Wire Size Range | | Cuimanina Haad Baut | | |
| Products Applied | AWG | mm² | Crimping Head Part Number | | |
| PLASTI-GRIP Butt | 22-16 | 0.3-1.3 | 314868-1 | | |
| Splices | 16-14 | 1.3-2 | 314869-1 | | |
| PIDG Terminals and Splices and PLASTI-GRIP Terminals | 22-16 | 0.3-1.3 | 314270-3 | | |
| | 16-14 | 1.3-2 | 314269-1 | | |
| SOLISTRAND | 22-16 | 0.3-1.3 | 314516-1 | | |
| Uninsulated Terminals | 16-14 | 1.3-2 | 314517-1 | | |
| and Splices | 14-12 | 2-3 | 314518-1 | | |
| SOLISTRAND | 22-16 | 0.3-1.3 | | | |
| Uninsulated Terminals | 16-14 | 1.3-2 | 189989-1 | | |
| and Splices | 14-12 | 2-3 | | | |

| T-HEAD Crimper | | | | | |
|-----------------------------|---------|----------|-----------------|--|--|
| | Wire Si | ze Range | | | |
| Products Applied | AWG | mm² | T-HEAD Assembly | | |
| PIDG Terminals & Splices | 22-16 | 0.3-1.25 | 217202 1 | | |
| PLASTI-GRIP Terminals | 16-14 | 1.25-2 | 217202-1 | | |

T-HEAD Crimper

Part No. 217202-1

Used to apply 22-14 AWG [0.3-2 mm²] PIDG Terminals and Splices and PLASTI-GRIP Terminals. (Equivalent to T-HEAD Hand Tool Part Nos. 59170 and 59250.)



Micro System Crimping Heads

| | | <u> </u> | , | Adapter Crimping | |
|--------------------------------|--------------------------|-----------------|-----------|------------------|------------|
| Products Applied | | Wire Size Range | | SAHT | |
| Connector/Terminal | Style | AWG | mm² | Tool Assembly* | Head Only |
| Connector/Terrinia | Style | | | 1001 Assembly | Tiead Only |
| | Size 20 DF | 28-24 | 0.08-0.2 | 91503-1 | 91503-3 |
| AMPLIMITE D-Sub. Connectors | Contacts | 24-20 | 0.2-0.5 | | |
| D-sub. Connectors | Size 22 DF Contacts | 28-22 | 0.08-0.3 | 91520-1 | 91520-3 |
| | Mod. IV | 26-22 | 0.12-0.3 | 91517-1 | 91517-3 |
| | Contacts | 24-20 | 0.2-0.5 | 91516-1 | 91516-3 |
| AMPMODU | Locking Clip Contacts | 26-22 | 0.12-0.3 | 91533-1 | 91533-3 |
| Connectors | MTE & Tandem | 32-28 | 0.03-0.08 | 91543-1 | 91543-3 |
| | Spring Contacts | 26-22 | 0.12-0.3 | 91531-1 | 91531-3 |
| | Short Point | 32-22 | 0.03-0.3 | 91518-1 | 91518-3 |
| | Contacts | 24-20 | 0.2-0.5 | 91551-1 | 91551-3 |
| | Type II Contacts | 28-24 | 0.08-0.2 | 01530 1 | 91539-3 |
| | | 24-20 | 0.2-0.5 | 91539-1 | |
| | 30.1.2.2.5 | 18-14 | 0.8-2 | 91539-1 | 91539-3 |
| | | 26-24 | 0.12-0.2 | | 91515-3 |
| CPC Connectors M | | 24-20 | 0.2-0.5 | 91515-1 | |
| series Connectors | | 24-20 | 0.2-0.5 | 01522.1 | 91523-3 |
| | Type III+ Contacts | 18-16 | 0.8-1.25 | 91523-1 | |
| | - | 24-20 | 0.2-0.5 | 0.505 | 01505.3 |
| | | 18-16 | 0.8-1.25 | 91505-1 | 91505-3 |
| | | 18-14 | 0.8-2 | 91519-1 | 91519-3 |
| | | 30-22 | 0.05-0.3 | 91515-1 | 91515-3 |
| | Commercial Contacts | 24-18 | 0.2-0.8 | 91512-1 | 91512-3 |
| | Contacts | 20-14 | 0.5-2 | 91504-1 | 91504-3 |
| | | 24-18 | 0.2-0.8 | 91510-1 | 91510-3 |
| | Universal & | 20-14 | 0.5-2 | 91500-1 | 91500-3 |
| | Universal II Contacts | 20-18 | 0.5-0.8 | 91508-1 | 91508-3 |
| MATE-N-LOK Connectors | Contacts | 16-14 | 1.25-2 | 91506-1 | 91506-3 |
| | Mini-Universal | 20-16 | 0.5-1.25 | 91536-1 | 91536-3 |
| | | 26-22 | 0.12-0.3 | 91529-1 | 91529-3 |
| | Mini-Universal II | 22-18 | 0.3-0.8 | 91522-1 | 91522-3 |
| | Contacts — | 20-16 | 0.5-1.25 | 91594-1 | 91594-3 |
| MR Connectors | Contacts | 26-18 | 0.12-0.8 | 91526-1 | 91526-3 |

 $^{^{}st}$ Head may be disassembled from tool assembly.

Disclaimer: While TE Connectivity has made every reasonable effort to ensure the accuracy of the information in this catalog, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current.

TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

tooling.te.com/europe



