



## HIGH TEMP IMMERSION PROBE

### SPECIFICATIONS

- Precision remote temperature sensing
- Highly stable precision thermistors
- Robust design
- Suitable for applications where sensor is exposed to temperatures up to 300°C
- RoHs Compliant

### Features

- Suitable for use in high temperature applications
- Pipe threaded probes provide excellent seal
- Custom tolerances available on request
- Temperature range -40 °C to +300°C

### Applications

- Domestic hot water generators
- Building automation systems
- Compact heat exchangers
- Closed loop pressurized systems
- Water tank applications

This assembly consists of a NTC thermistor mounted in Stainless Steel screw-in housing. The sensing element is sealed with a ceramic compound. Device is available in a variety of thread and connector types.

**HIGH TEMP IMMERSION PROBE**

Performance Specs

Parameters	Units	Value
Resistance @ +200°C	Ohms	3.6 Meg
Tolerance @ +200°C	%	± 5
Beta Value 150/250	K	5300
Tolerance on Beta Value	%	± 5
Time response in still water	Seconds	<12.5

Mechanical Details




Figure 1: Immersion probe – mechanical drawing

## HIGH TEMP IMMERSION PROBE

### Resistance V Temperature Table

Temp °C	K Ohms	Temp °C	K Ohms	Temp °C	K Ohms	Temp °C	K Ohms
-40	199,959	50	1,097	140	39.81	230	4.077
-35	138,733	55	878.3	145	34.3	235	3.669
-30	97,340	60	706.8	150	29.65	240	3.309
-25	69,031	65	571.8	155	25.7	245	2.989
-20	49,459	70	464.8	160	22.34	250	2.705
-15	35,783	75	379.7	165	19.47	255	2.453
-10	26,131	80	311.6	170	17.02	260	2.228
-5	19,254	85	256.9	175	14.92	265	2.026
0	14,308	90	212.7	180	13.1	270	1.846
5	10,720	95	176.9	185	11.54	275	1.685
10	8,096	100	147.7	190	10.19	280	1.54
15	6,160	105	123.8	195	9.019	285	1.41
20	4,721	110	104.2	200	8	290	1.293
25	3,643	115	87.97	205	7.112	295	1.187
30	2,830	120	74.56	210	6.337	300	1.092
35	2,213	125	53.42	215	5.658		
40	1,741	130	54.1	220	5.062		
45	1,378	135	46.35	225	4.538		

### Ordering Information

Part Number	Description	Ω @200°C	MOQ
11016706-00	Immersion Probe	3.6 Meg	100*

\* For quantities less than Minimum Order Quantity – contact distribution

#### NORTH AMERICA

Measurement Specialties, Inc.,  
a TE Connectivity Company  
1711 139th Lane NW  
Andover, MN 55304  
Tel: +1 763 689 4870  
Fax: +1 763 689 5033  
[customer care.ando@te.com](mailto:customer care.ando@te.com)

#### EUROPE

Measurement Specialties (Europe), Ltd.,  
a TE Connectivity Company  
Ballybrit Business Park  
Galway Ireland  
Tel : +353-91-753238  
Fax : +353-91-770789  
Email: [customer care.glwy@te.com](mailto:customer care.glwy@te.com)

#### ASIA

Measurement Specialties (China), Ltd.,  
a TE Connectivity Company  
No. 368 Wulian 1st Road  
Gongxing Town  
Shuangliu, Chengdu  
Sichuan, 610200  
China  
Tel: +86 (0) 28 8573 9088  
Fax: +86 (0) 28 8573 9070  
Email: [customer care.chdu@te.com](mailto:customer care.chdu@te.com)

### [te.com/sensorsolutions](http://te.com/sensorsolutions)

TE Connectivity, TE, TE Connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2019 TE Connectivity Corporation. All Rights Reserved.

Version # 09/2020

