

Introduction



GET.64 Interconnection System

The GET.64 Interconnection System is used worldwide in various applications for automotive interconnections. It fulfills requirements for passenger and engine compartment.

High packaging density is possible for sealed applications due to mat seal capability.

Technical Features

- Product offering includes wire-to-wire, wire-to-board and wire-to-device configurations
- High range of pin count variants
- Tangle free contact offered as tin, silver and gold plating
- Female terminal accepts blades from 0.64 x 0.64 mm up to 1.2 x 0.64 mm
- Sealed and unsealed connector housings available (straight mate or lever actuated)
- Mat seals allow high packaging density
- Design allows for specific pinout versions, no blind plugs necessary in sealed applications



Engineering Notes

								 															_
			_				_										_						_
							_	 									_						_
								 											_				
			_				_	 	_											_			
																							_
							_																
+++		+++						+			+++					+						\square	
								\square															
		+++						+ + +			+++	+++				+++							
	 	+ + +			$\left \right $			 + + +			 				++-	+++		+ +	++		+		
	 	+ + +					++	 +			 + + + +			\vdash		+ $+$ $+$			+			$ \rightarrow $	
+	+	+++						+			\square	+				+						\square	
			_				_	 	_											_			
																+ + +							
			_				_						_				_						
				Image: Constraint of the sector of						Image:													
				Image: Sector						Image:													
										Image:													
			Image: Section of the sectio																				



Introduction



Features

- CPA capability
 - Assures connector mating
- USCAR & SDS compatibility
 Standard interface for multiple applications
- 2.54 mm x 2.54 mm spacing
 Typically smaller than competition
- 8 keying options
 Maximum design flexibility
- Tang-free contact
 - Easier harness handling/ production
- Good Stress Relaxation performance (70 % remaining after 3000 hr @ 150 °C)
 - Used in USCAR Class III range (-40 °C to +125 °C)

- 0.22 to 0.75 mm² wire range
- Two terminal sizes cover 3–8 amp requirements (20 °C T-rise)
- 10 mating cycles (tin, silver or gold)
- Robust receptacle to handle multiple mates
- Accepts up to 1.0 mm wide blade
 - Large interface flexibility and robustness
- Same shorting bar design for sealed, unsealed, gold and tin systems
 - Economical shorting bar solution

Applications

- Airbag Restraint Modules
- Power Control Modules
- Generic Control Modules
- Unsealed Harness Wiring
 - Inline Connections
 - Instrument Panel
 - Audio
 - Mirror
 - Switches
 - Actuators
 - Overhead Consoles
- Sealed Harness Wiring
 Mass Air Flow
 - Passenger Sensing

Product Offering

- Tin, Silver and Gold Platings
- Wire-to-Wire
- Wire-to-PC Board
- Wire-to-Device
- Unsealed and Sealed
- Hand Mate and Lever Actuated



Receptacle Contacts

Technical Features

Insertion Force:

- Tin Terminals: <4.0 N</p>
- Silver Terminals: <3.5 N
- Gold Terminals: <2.0 N

Terminal Retention Force: >30 N (Preliminary)

>75 N (Permanent)

Temperature Classification (according to USCAR):

Tin Terminals Class II:
 -40 °C to +120 °C max.
 up to +125 °C max.

 Silver and Gold Terminals Class III: -40 °C to +145 °C max.

Vibration (per USCAR):

- Unsealed Applications: Body and Instrument Panel Profile
- Sealed Applications: Engine Compartment Profile

Dielectric Strength: 1,000 V AC min.

Voltage Drop (Initial Interface): 1.0 mV/A max.


Isolation Resistance: 20 MW @ 500 DC 500 V min.

Extraction Tool: Part No. 3-1579007-6

Receptacle Contacts


	Insulation				F	Part Numbers		
Wire Size Range (mm ²)	Diameter (mm)	Material and Finish	Strip Form	Packaging Unit	Loose- Piece	Packaging Unit	Applicator	Hand Tool
		Gold plated	1393364-1	10,000				
0.22-0.35	1.10-1.65	Gold shunted	1393364-2	10,000			x-1528005-x	6-1393462-4
0.22-0.35	1.10-1.05	Tin plated	1393367-1	10,000	-	-	X-1526003-X	0-1393402-4
		Silver plated	1393367-2	10,000				
		Gold plated	1393365-1	10,000				
0.50-0.75	1.40-2.06	Gold shunted	1393365-2	10,000			x-1528268-x	6 1000460 F
0.50-0.75	1.40-2.06	Tin plated	1393366-1	10,000	-	-	x-1528268-X	6-1393462-5
		Silver plated	1393366-2	10,000				

Note: All Part Numbers are RoHS and ELV compliant.






Pin Contacts



Pin Contacts

W. O. D.	Insulation				Р	art Numbers		
Wire Size Range (mm ²)	Diameter (mm)	Material and Finish	Strip Form	Packaging Unit	Loose- Piece	Packaging Unit	Applicator	Hand Tool
		Gold plated	3-1419158-1①	10,000	-	-	N1/A	
0.22-0.35	1.10-1.65	Tin plated	1-1419158-6①	10,000	_	-	N/A	0 1000 400 4
0.22-0.33	1.10-1.05	Gold plated	1438299-12	10,000	_	-	x-1528005-x	6-1393462-4
		Tin plated	1438299-22	10,000	_	-	X-1528005-X	
		Gold plated	2-1419158-3①	10,000	_	-	N/A	
0.50-0.75	1.40-2.06	Tin plated	2-1419158-5①	10,000	_	-	IN/A	0 1000400 5
0.50-0.75	1.40-2.00	Gold plated	1438299-32	10,000	_	-	x-1528268-x	6-1393462-5
		Tin plated	1438299-42	10,000	-	-	X-1020200-X	

Note: All Part Numbers are RoHS and ELV compliant.





Receptacle Contacts

Technical Features

Insertion Force:

– Tin Terminals: <4.0 N

Terminal Retention Force:

>30 N (Preliminary) >75 N (Permanent)

Temperature Classification (according to USCAR):

Tin Terminals Class II:
 -40 °C to +120 °C max.
 up to +125 °C max.

Vibration (per USCAR):

 Unsealed Applications: Body and Instrument Panel Profile


 Sealed Applications: Engine Compartment Profile

Dielectric Strength: 1,000 V AC min.

Voltage Drop (Initial Interface): 1.0 mV/A max.

Isolation Resistance: 20 MW @ 500 DC 500 V min.

Extraction Tool: Part No. 3-1579007-6



Receptacle Contacts

	Insulation				F	Part Numbers		
Wire Size Range (mm²)	Diameter (mm)	Material and Finish	Strip Form	Packaging Unit	Loose- Piece	Packaging Unit	Applicator	Hand Tool
0.13	0.80-1.05	Tin plated	1564880-1	10,000			1157164-6	
0.22-0.35	1.10–1.65	Tin plated	1719957-1	10,000	-	-	1528698-6	-
0.50-0.75	1.40-2.06	Tin plated	1719958-1	10,000	-	-	1528699-6	-

Note: All Part Numbers are RoHS and ELV compliant.



Introduction



Features

- CPA capability
 - Assures connector mating
- USCAR & SDS compatibility
 Standard interface for multiple applications
- 2.54 mm x 2.54 mm spacing
 Typically smaller than competition
- 8 keying options
- Maximum design flexibility
 Tang-free contact
 - Easier harness handling/ production
- Good Stress Relaxation performance (70 % remaining after 3000 hr @ 150 °C)
 - Used in USCAR Class III range (-40 °C to +125 °C)

- 0.22 to 0.75 mm² wire range
- Two terminal sizes cover 3–8 amp requirements (20 °C T-rise)
- 10 mating cycles (tin, silver or gold)
 - Robust receptacle to handle multiple mates
- Accepts up to 1.0 mm wide blade
 Large interface flexibility
 - and robustness
- Same shorting bar design for sealed, unsealed, gold and tin systems
 - Economical shorting bar solution


Applications

- Airbag Restraint Modules
- Power Control Modules
- Generic Control Modules
- Unsealed Harness Wiring
 - Inline Connections
 - Instrument Panel
 - Audio
 - Mirror
 - Switches
 - Actuators
 - Overhead Consoles
- Sealed Harness Wiring
 Mass Air Flow
 - Passenger Sensing

Product Offering

- Tin, Silver and Gold Platings
- Wire-to-Wire
- Wire-to-PC Board
- Wire-to-Device
- Unsealed and Sealed
- Hand Mate and Lever Actuated





No. of	Kouina	Ususian				Part Numbers			
No. of Positions	Keying Options	Housing Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical
2 (1 x 2)	А	Black	1452598-1	-	-	-	1452601-1	1452625-1	1452623-1






No. of Positions: 4 (1 x 4) Position Assy


Housing Material: PA66 GF35


Wire Size Range: 0.22-0.75 mm²

Product Specification: 114-13060

Application Specifications: 408-8955 408-8600







Unsealed Receptacle Housings 1-Row with CPA

No. of	Keying	Housing				Part Numbers			
Positions	Options	Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical
	А	Black	6-1419169-8	-	-	-	6-1419166-1	-	-
4 (1 4)	В	Black	6-1419169-9	-	-	-	6-1419166-2	-	-
4 (1 x 4)	С	Black	6-1419169-2	-	-	-	9-1419157-4	-	-
	D	Black	6-1419169-3	-	-	-	5-1419166-6	-	-

No. of	Kanina					Part Numbers			
No. of Positions	Keying Options	Housing Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical
	А	Black	3-1419158-2	-	-	-	6-1419166-1	_	-
4 (1 × 4)	В	Black	5-1419169-2	-	_	-	6-1419166-2	-	-
4 (1 x 4)	С	Black	4-1419169-6	-	-	-	9-1419157-4	-	-
	D	Black	4-1419169-7	-	-	-	5-1419166-6	-	-



Unsealed Low Profile Latch 1-Row




No. of Positions: 4 (1 x 4) Position Assy


Housing Material: PA66 GF35


Wire Size Range: 0.22-0.75 mm²

Product Specification: 114-13060

Application Specifications: 408-8955 408-8600








Unsealed Low Profile Latch 1-Row with CPA

No. of	Kaulaa	Ususian				Part Numbers			
Positions	Keying Options	Housing Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PCI Right-Angle	B Header Vertical
	А	Black	1456983-2	-	-	-	6-1419166-1	_	-
4 (1 4)	В	Black	1456983-4	-	-	-	6-1419166-2	-	-
4 (1 x 4)	С	Black	1456983-6	-	-	-	9-1419157-4	-	-
	D	Black	1456983-8	-	-	-	5-1419166-6	-	-

Unsealed Low Profile Latch 1-Row without CPA

Ne of	Kanina					Part Numbers			
No. of Positions	Keying Options	Housing Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical
	А	Black	1456983-1	-	-	-	6-1419166-1	-	-
. (1 4)	В	Black	1456983-3	-	-	-	6-1419166-2	-	-
4 (1 x 4)	С	Black	1456983-5	-	-	-	9-1419157-4	-	-
	D	Black	1456983-7	-	-	-	5-1419166-6	-	-





No. of	Kaulina	Ususing				Part Numbers			
No. of Positions	Keying Options	Housing Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PCI Right-Angle	B Header Vertical
4 (1 x 4)	A	Black	1438122-1	-	-	-	6-1419166-1	-	-






No. of Positions: 6 (1 x 6) Position Assy Housing Material:

PA66 GF35 Wire Size Range: 0.22-0.75 mm²

Product Specification: 114-13060

Application Specification:



No. of	Kauina	Ususian				Part Numbers			
No. of Positions	Keying Options	Housing Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical
6 (1 x 6)	-	Yellow	1564003-1	-	-	-	1564004-1	-	-



Technical Features


No. of Positions: 6 (1 x 6) Position Assy Housing Material:


PA66 GF35


Wire Size Range: 0.22-0.75 mm²


Product Specification: 114-13060

Application Specification: 408-8955









Unsealed Receptacle Housings 1-Row with CPA

No. of	Kauina	Heusing				Part Numbers			
No. of Positions	Keying Options	Housing Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical
	В	Black	9-1419169-0						
6 (1 x 6)	С	Black	8-1419169-3	-	-	-	-	-	-
	D	Black	8-1419169-4						

No. of	Keying	Housing	Part Numbers							
No. of Positions	Options	Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical	
	В	Black	1419158-4							
·	С	Black	1419158-1							
6 (1 x 6)	D	Black	1419158-2	-	-	-	-	-	-	
·	E	Black	7-1419169-0							
·	F	Black	7-1419169-1							



Unsealed Low Profile Latch 1-Row

Technical Features


No. of Positions: 6 (1 x 6) Position Assy Housing Material:

PA66 GF35

Wire Size Range: 0.22-0.75 mm²

Product Specification: 114-13060


Application Specification: 408-8955



18.6

XX >PBT+PC-GF30<

2.54 —



Unsealed Low Profile Latch 1-Row with CPA


No. of	Keying	Housing		Part Numbers							
No. of Positions	Options	Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical		
	В	Black	1456985-2								
	С	Black	1456985-4								
6 (1 x 6)	D	Black	1456985-6	-	-	-	-	-	-		
	E	Black	1456985-8								
	F	Black	1-1456985-0								

13.6

Unsealed Low Profile Latch 1-Row without CPA


No. of	Kauina	Housing		Part Numbers							
Positions	Keying Options	Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical		
	В	Black	1456985-1								
- 6 (1 × 6)	С	Black	1456985-3								
	D	Black	1456985-5	-	-	-	-	-	-		
	E	Black	1456985-7								
	F	Black	1456985-9								





No. of	Kauina	Housing		Part Numbers								
No. of Positions	Keying Options	Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical			
6 (1 x 6)	В	Black	1438156-2	_	_	_	_	_	_			
0 (1 × 0)	С	Black	1488752-3	-	-	-	_	_				





No. of	Kaving	Ususian			Part Numbers					
No. of Positions	Keying Options	Housing Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical	
6 (1 x 6)	А	Yellow	1355922-1	_	_	_	_	_	_	
0 (1 × 0)	В	Black	1355922-4	-	-	_	_	_	-	





No. of Positions: 6 (1 x 6) Position Hybrid 4 x GET.64 Terminal 2 x 6.3 mm Terminal


Housing Material: PBT GF30

Wire Size Range: 0.22-0.75 mm²

Product Specification:

_

Application Specification:



30.1

7.62


23.62

8.0

2.54

3.3

1



No. of	Kaulaa	Hausian				Part Numbers			
No. of Positions	Keying Options	Housing Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical
6 (1 x 6)	A	Black	1452203-1	-	-	-	-	-	-






No. of Positions: 10 (1 x 10) Position Assy without CPA

Housing Material: PA66 GF35

Wire Size Range: 0.22-0.75 mm²


Product Specification: 114-13060

Application Specification: 408-8955



No. of	Keying Options	Heusing	Part Numbers								
No. of Positions		Housing Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical		
	А	Black	1452187-1								
10 (1 x 10)	С	Black	1452187-3	-	-	-	-	-	-		
	D	Black	1452187-4								






Unsealed Receptacle Housings 2-Rows with CPA

No. of	Kaulaa	Housing Color	Part Numbers							
No. of Positions	Keying Options		Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical	
	А	Black	1419158-5							
-	В	Black	1418158-6							
6 (2 x 3)	С	Black	1411325-3	-	-	-	_	-	-	
	D	Black	1411325-4							

No. of	Kaulaa	Housing				Part Numbers			
No. of Positions	Keying Options	Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical
	٨	Black	9-1411325-1						
	A	Green	1-1411325-1						
	D	Black	9-1411325-2						
	В	Gray	1-1411325-2						
6 (2 x 3)	С	Black	9-1411325-3		_	_	_	_	_
0 (2 X 3)	0	Brown	1-1411325-3	-	-	_	_	-	-
		Black	9-1411325-4						
	D	Blue	1-1411325-4						
	E	Black	9-1411325-5						






Unsealed Receptacle Housings 2-Rows with CPA

No. of	Keying	Housing	Part Numbers							
No. of Positions	Options	Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical	
	А	Black	3-1419170-4	-	-	-	1411169-1	-	-	
8 (2 x 4)	С	Black	1-1419158-3	-	-	-	1411169-3	-	-	
0 (2 X 4)	D	Black	2-1419170-9	-	-	-	1411169-4	-	-	
	E	Black	3-1419170-0	-	-	-	_	-	-	

No. of	Kashara	Housing	Part Numbers						
No. of Positions	Keying Options	Housing Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical
	^	Black	1-1419158-2	-	-	-	1411169-1	-	-
	A	Black	1411168-1	-	-	-	_	-	-
- 8 (2 x 4)	С	Black	1418158-8	-	-	-	1411169-3	-	-
0 (2 X 4)	U	Black	1411168-3	-	-	-	-	-	-
-	D	Black	1-1419158-0	-	-	-	1411169-4	-	-
-	E	Black	1-1419158-1	-	-	-	_	-	-



Unsealed Low Profile Latch 2-Rows



Unsealed Low Profile Latch 2-Rows with CPA

No. of	Keying Options	Housing	Part Numbers							
Positions		Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical	
	А	Black	1456987-2	-	-	-	1411169-1	-	-	
	В	Black	1456987-4	-	-	-	-	-	-	
8 (2 x 4) ·	С	Black	1456987-6	-	-	-	1411169-3	-	-	
	D	Black	1456987-8	-	-	-	1411169-4	-	-	

Unsealed Low Profile Latch 2-Rows without CPA

No. of	Keying		Part Numbers							
No. of Positions	Options	Housing Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical	
	А	Black	1456987-1	-	-	-	1411169-1	_	-	
0 (0 x 4)	В	Black	1456987-3	-	_	-	-	-	-	
8 (2 x 4) ·	С	Black	1456987-5	-	-	-	1411169-3	-	-	
	D	Black	1456987-7	-	-	-	1411169-4	-	-	






No. of Positions: 10 (2 x 5) Position Assy

Housing Material: PA66 GF35

Wire Size Range: 0.22-0.75 mm²


Product Specification: 114-13060

Application Specifications: 408-8955 408-8600



2.54

5.08




Unsealed Receptacle Housings 2-Rows with CPA

No. of	Kaulaa	Housing	Part Numbers							
No. of Positions	Keying Options	Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical	
10 (2 x 5)	А	Black	5-1419170-8	-	-	-	9-1419157-6	-	-	

10.16

No. of	Kouina	ng Housing		Part Numbers							
Positions	Keying Options	Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical		
10 (2 x 5)	А	Black	1-1419158-4	-	-	-	9-1419157-6	-	-		





Unsealed Receptacle Housings 2-Rows with CPA

No. of	Kauina	Housing		Part Numbers							
No. of Positions	Keying Options	Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical		
12 (2 x 6)	В	Black	1-1452015-2	-	-	-	-	1438107-1	-		
12 (2 × 0)	Н	Black	1-1452015-8	-	-	-	-	-	-		

12.7 -

No. of	Kauina	Housing		Part Numbers							
No. of Positions	Keying Options	Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical		
12 (2 x 6)	В	Black	1452015-2	-	-	-	-	1438107-1	-		
12 (2 X 0)	Н	Black	1452015-8	-	-	-	-	-	-		






No. of Positions: 16 (2 x 8) Position Assy

Housing Material: sPS + PA66 GF30

Wire Size Range: 0.22-0.75 mm²

Product Specification: 114-13060

Application Specifications: 408-8955 408-8600



23.6

>PBT+PC


2.54

-Gi

17.8

XX

tyco




Unsealed Receptacle Housings 2-Rows with CPA

No. of	Keying	Housing	Part Numbers						
Positions	Options	Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical
	А	Black	1419171-9	-	-	-	6-1419167-1	1438107-1	-
	С	Black	1419171-3	-	-	-	5-1419167-5	-	-
16 (2 x 8)	D	Black	1419171-4	-	-	-	5-1419167-6	-	-
	E	Black	1419171-5	-	-	-	5-1419167-7	-	-
	F	Black	1419171-6	-	-	-	5-1419167-8	_	-

No. of	Kovina	Housing		Part Numbers						
No. of Positions	Keying Options	Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical	
	^	Black	9-1419170-1	-	-	-	6-1419167-1	1438107-1	-	
	A	Gray	1411369-1	-	-	-	1411367-1	-	-	
16 (2 x 8)	С	Black	8-1419170-5	-	-	-	5-1419167-5	-	-	
10 (2 x 0)	D	Black	8-1419170-6	-	-	-	5-1419167-6	-	-	
	E	Black	8-1419170-7	-	-	-	5-1419167-7	-	-	
	F	Black	8-1419170-8	-	-	-	5-1419167-8	-	-	



Unsealed Low Profile Latch 2-Rows



Unsealed Low Profile Latch 2-Rows

No. of Positions	Kauina	Ususing	Part Numbers							
	Keying Options	Housing Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical	
16 (2 x 8)	А	Black	1458573-1	-	-	-	1438170-1	1438107-1	-	

Unsealed Low Profile Latch 2-Rows with CPA

No. of Positions	Kasian	Usualaa				Part Numbers			
	Keying Options	Housing Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical
16 (2 x 8)	А	Black	1456989-2	-	-	-	1438170-1	1438107-1	-

Unsealed Low Profile Latch 2-Rows without CPA

No. of	Keying		Part Numbers							
No. of Positions	Options	Housing Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical	
	٨	Black	1456989-1	_	_	-	6-1419167-1	-	_	
	A	Gray	1456985-3	-	-	-	1411367-1	-	-	
16 (0 v 0)	С	Black	1456985-4	-	-	-	5-1419167-5	-	-	
16 (2 x 8)	D	Black	1456985-5	-	_	-	5-1419167-6	-	-	
	E	Black	1456985-6	-	-	-	5-1419167-7	-	-	
	F	Black	1456989-7	-	_	-	5-1419167-8	-	-	






No. of Positions: 22 (2 x 11) Position Assy

Housing Material: PA66 GF30

Wire Size Range: 0.22-0.75 mm²


Product Specification: 114-13060

Application Specifications: 408-8955 408-8600



25040-99Vd<

31.2




Unsealed Receptacle Housings 2-Rows with CPA

No. of	Keying	Housing	Part Numbers								
Positions	Options	Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical		
	А	Black	1-1419158-7	-	-	-	2-1419158-8	-	-		
22 (2 x 11)	В	Black	3-1419158-0	-	-	-	2-1419158-7	-	-		
	С	Black	2-1419158-9	-	-	-	2-1419158-6	-	-		


No. of	Kauina	Keying Housing	Part Numbers							
Positions	Options	Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PCI Right-Angle	B Header Vertical	
	А	Black	1420011-1	-	-	-	2-1419158-8	-	-	
22 (2 x 11)	В	Black	1420011-2	-	-	-	2-1419158-7	-	-	
	С	Black	1420011-3	-	-	-	2-1419158-6	-	-	






No. of Positions	Keying Options	Housing Color	Part Numbers							
			Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical	
00	22 A	Black	1452842-1	_	-	-	-	-	_	
22		Gray	1-1452842-1	-					-	






No. of Positions	Keying Options		Part Numbers								
		Housing Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PCI Right-Angle	B Header Vertical		
	А	Black	2-1419158-1								
	В	Green	2-1419158-0								
23	С	Gray	1-1419158-9	-	-	-	-	6-1419138-9	-		
	D	Brown	1-1419158-8								
	E	Blue	2-1419158-2								






No. of Positions	Keying Options	Housing Color	Part Numbers							
			Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical	
$24(2 \times 12)$	^	Black	1452839-1	_	-	-	-			
24 (2 x 12)	A	Gray	1-1452839-1	-				_	-	






No. of Positions	Kauina	Housing Color	Part Numbers						
	Keying Options		Pin Housing	Cover	Locking Device	Cover and Lever	Mating Receptacle Housing		
2 (1 x 2)	А	Black	1452601-1	-	-	-	1452598-1		






No. of	Keying Options	Housing Color					
Positions			Pin Housing	Cover	Locking Device	Cover and Lever	Mating Receptacle Housing
							6-1419169-8
	А	Black	6-1419166-1	-	-	_	3-1419158-2
							1438122-1
4 (1 × 4)	_			_		-	6-1419169-9
	В	Black	6-1419166-2		-		5-1419169-2
			5 4 4 1 0 1 0 0 0				6-1419169-3
	D	Black	5-1419166-6	-	-	-	4-1419169-7






No. of Positions	Kavina	Housing Color	Part Numbers						
	Keying Options		Pin Housing	Cover	Locking Device	Cover and Lever	Mating Receptacle Housing		
6 (1 x 6)	~	Yellow	1564004-1				1564003-1		
	~	Orange	1564004-2		-	_	1504003-1		






No. of	Keying Options	Housing Color	Part Numbers						
Positions			Pin Housing	Cover	Locking Device	Cover and Lever	Mating Receptacle Housing		
							2-1419170-1		
	С	Black	9-1419166-0	_	-	_	9-1419169-1		
8 (1 x 8)							1488903-1		
		51					2-1419170-2		
	D	Black	9-1419166-1	-	-	-	9-1419169-2		






No. of	Keying Options	Housing Color	Part Numbers						
Positions			Pin Housing	Cover	Locking Device	Cover and Lever	Mating Receptacle Housing		
	A			-	_	_	1-1419158-2		
		Black	1411169-1				3-1419170-4		
	С	Black	1411169-3	_	_	_	1419158-8		
8 (2 x 4)							1-1419158-3		
0 (2 X 4)		Black	1 411100 4	-		-	1-1419158-0		
	D		1411169-4		-		2-1419170-9		
		Black	1411100 0	_	_	_	1-1419158-1		
	E		1411169-0				3-1419170-0		





No. of Positions	Kowing	Housing Color	Part Numbers						
	Keying Options		Pin Housing	Cover	Locking Device	Cover and Lever	Mating Receptacle Housing		
10 (2 x 5)	А	Disala	0 1 1 1 0 1 5 7 0	_	_	_	5-1419170-8		
		Black	9-1419157-6				1-1419158-4		






No. of	Kavina	Heusing			Part Numbers		
Positions	Keying Options	Housing Color	Pin Housing	Cover	Locking Device	Cover and Lever	Mating Receptacle Housing
		Black	0.1410107.1			_	1419171-9
	A		6-1419167-1	-	-		9-1419170-1
		Gray	1411367-1	-	-	-	1411369-1
	С	Black	5-1419167-5	_	-	_	1419171-3
							8-1419170-5
16 (2 x 8)	_	D 1 1		-		-	1419171-4
	D	Black	5-1419167-6		-		8-1419170-6
		Disala	E 1410107 7				1419171-5
	E	Black	5-1419167-7	-	-	_	8-1419170-7
	F		5 1410167 0				1419171-6
	F	Black	5-1419167-8	_	-	_	8-1419170-8



GET.64 Interconnection System Housings and Connectors

Unsealed Pin Housings 2-Rows



Unsealed Pin Housings 2-Rows

No. of	Kauina	Heusing	Part Numbers							
No. of Positions	Keying Housing s Options Color Pin Housing		Cover	Locking Device	Cover and Lever	Mating Receptacle Housing				
16 (2 x 8)	А	Black	1438170-1	_	-	-	1488573-1			



Unsealed Pin Housings 2-Rowss

Technical Features


No. of Positions: 22 (2 x 11) Positions

Housing Material: PA66 GF35


Wire Size Range: 0.22-0.75 mm²

Product Specification: 114-13060

Application Specifications: 408-8955 408-8600



33.78




Unsealed Pin Housings 2-Rows

No. of	Kaving	Housing Color		Part Numbers							
Positions	Keying Options		Pin Housing	Cover	Locking Device	Cover and Lever	Mating Receptacle Housing				
			0.4440450.0				1-1419158-7				
	A	Black	2-1419158-8	-	-	_	1420011-1				
00 (0 11)			0.4440450.7				3-1419158-0				
22 (2 x 11)	В	Black	2-1419158-7	-	-	_	1420011-2				
-			0.4440450.0				2-1419158-9				
	С	Black	2-1419158-6	-	-	_	1420011-3				
	U	Diack	2-1419130-0	_	_		1420011-3				



Unsealed Pin Housings (Special Hybrid)



Unsealed Pin Housings (Special Hybrid)

No. of Keyin	Kaving	(oving Housing	Part Numbers						
Positions	Options	Housing Color	Pin Housing	Cover	Locking Device	Cover and Lever	Mating Receptacle Housing		
60	А	Black	1452458-1	1452462-3	-	_	1452454-1		




Unsealed Printed Circuit Board Headers 1-Row


Technical Features

No. of Positions: 2 (1 x 2) Positions Housing Material: PA66 GF35

Wire Size Range: Brass with Tin Finish Product Specification:

Application Specification:






Unsealed Printed Circuit Board Headers 1-Row

No. of	Hausian	Part Numbers							
No. of Positions	Housing Color	PCB H Right-Angle	eader Vertical	Cover	Cover and Lever	Retainer Housing	Mating Receptacle Housing		
2 (1 x 2)	Black	1452625-1	1452623-1	-	-	-	1452598-1		



Unsealed Printed Circuit Board Headers 1-Row – Surface Mount Technology



Unsealed Printed Circuit Board Headers 1-Row - Surface Mount Technology

No. of	Housing	Part Numbers							
No. of Positions	Housing Color	PCB He Right-Angle	PCB Header Right-Angle Vertical		Cover and Lever	Retainer Housing	Mating Receptacle Housing		
6 (1 x 6)	Black	1927688-3	-	-	-	-	1488752-3		



Technical Features


No. of Positions: 4 (1 x 4) Positions


Housing Material: PA66 GF35


Wire Size Range: 0.22-0.75 mm²


Product Specifications: 114-13150 114-13060

Application Specification: 408-8598









Sealed Receptacle Housings 1-Row with CPA

No. of	Keying Options	Housing	Part Numbers						
Positions		Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical
	А	Gray	9-1419167-8	-	-	-	_	_	-
	В	Gray	9-1419167-9	-	-	-	-	-	-
4 (1 x 4)	B	Gray	1719256-1						
	A with 2 blocked	Gray	1438188-1	-	_	_	_	_	-


Sealed Receptacle Housings 1-Row without CPA

No. of	K an size as		Part Numbers							
No. of Positions	Keying Options	Housing Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical	
	А	Gray	9-1419167-0	-	-	-	-	-		
- 4 (1 × 4) - v	В	Gray	9-1419167-1						-	
	A with 1 blocked	Gray	9-1419167-5	-	_	_	_	-	_	



GET.64 Interconnection System Housings and Connectors

Sealed Receptacle Housings 1-Row



Sealed Receptacle Housings 1-Row with CPA

No. of	Kaving	Housing				Part Numbers			
No. of Positions	Keying Options	Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical
	А	Black	1-1419168-1			-	-	_	
	В	Black	1-1419168-2						_
-	С	Black	1-1419168-3	_	-				
	D	Black	1-1419168-4						
	A with 1 blocked with 2 blocked	Black	1438153-4 1438153-1	-	-	-	-	-	_
	B with 1 blocked with 2 blocked with 3 blocked	Black	1438153-6 1438153-5 1438153-2	_	_	_	-	_	_

Sealed Receptacle Housings 1-Row without CPA

			Part Numbers						
No. of Positions	Keying Options	Housing Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical
	А	Black	1419168-7	-			_		
	В	Black	1419168-8		-	_		_	-
	С	Black	1419168-9						
6 (1 x 6)	D	Black	1-1419168-0						
	A with 1 blocked	Black	1438153-3	_	-	_	-	-	_
	B with 2 blocked	Black	1438153-7	-	-	_	-	-	-



Technical Features


No. of Positions: 8 (2 x 4) Position Assy

Housing Material: PA66 GF35

Wire Size Range: 0.22-0.75 mm²

Product Specifications: 114-13150 114-13060

Application Specification: 408-8598




19.4

मन् मन

目光目

自い



Sealed Receptacle Housings 2-Row with CPA

No. of	Kaulaa	Housing Color	Part Numbers							
No. of Positions	Keying Options		Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical	
	А	Black	3-1419168-4							
8 (2 x 4)	В	Black	3-1419168-5							
0 (2 X 4)	С	Black	3-1419168-6	-	-	-	_	-	-	
	D	Black	3-1419168-7							

2.54

A

23.8

Sealed Receptacle Housings 2-Row without CPA

No. of	Koving	Housing Color				Part Numbers			
Positions	Keying Options		Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical
	А	Black	2-1419168-1						
	В	Black	1411001-1	_		_	-	-	-
8 (2 x 4)	С	Black	2-1419168-3		-				
0 (2 X 4)	D	Black	2-1419168-4						
v	B with 2 blocked	Black	1411001-2	-	_	_	_	-	-






No. of Positions: 16 (2 x 8) Position Assy


Housing Material: PA66 GF35


Wire Size Range: 0.22-0.75 mm²


Product Specifications: 114-13150 114-13060

Application Specification: 408-8598









Sealed Receptacle Housings 2-Row with CPA

NI 4	Keying	Housing Color	Part Numbers							
No. of Positions	Options		Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical	
	А	Black	5-1419168-8	_	-	-	-	-		
	В	Black	5-1419168-9						-	
	A with 7 blocked with 8 blocked	Black	1438031-5 1438031-6	_	_	_	_	_	-	


Sealed Receptacle Housings 2-Row without CPA

No. of	Kaulaa	Housing	Part Numbers								
No. of Positions	Keying Options	Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical		
	А	Black	1438031-1								
10 (0 + 0)	В	Black	1438031-2								
16 (2 x 8)	С	Black	1438031-3	-	-	-	-	-	-		
	D	Black	1438031-4								



GET.64 Interconnection System Housings and Connectors

Sealed Receptacle Housings 2-Rows




Sealed Receptacle Housings 2-Row

No. of	Keying H	Heusing		Part Numbers							
Positions	Options	Housing Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical		
	А	Black	1488533-5								
	В	Black	1488533-6			_	_				
	С	Black	1488533-7	-	—	—	_	-	-		
	D	Black	1488533-8								
18 (2 x 9)	A with 2 blocked with 3 blocked with 5 blocked with 8 blocked with 9 blocked with 13 blocked	Black	1-1438533-3 1-1438533-4 1-1438533-7 1438533-9 1-1488533-9 2-1438533-9	_	-	-	-	_	_		



Sealed Receptacle Housings 4-Rows with CPA




Sealed Receptacle Housings 4-Rows with CPA

No. of	Kaulina	Housing -	Part Numbers							
Positions	Keying Options	Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PCI Right-Angle	B Header Vertical	
			1924672-1 / -9							
	A	see Customer Drawing	1-1924672-0 / -9		-		_	8-1419157-9		
			2-1924672-0 / -7	_		-			-	
20			2-1924672-9							
			3-1924672-2 / -7							
	в	see Customer	2-1924672-8	_	_	_	_	1438322-3	_	
	В		3-1924672-0	-	-	-	-	1430322-3	-	




Sealed Receptacle Housings 4-Rows without CPA



Sealed Receptacle Housings 4-Rows without CPA

No. of	Keying	Housing -	Part Numbers							
Positions	Options	Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical	
			1924670-1 / -9							
			1-1924670-0 / -9							
		see Customer	2-1924670-0 / -9			_			_	
	А	see Customer Drawing	3-1924670-0 / -9	-	-		-	8-1419157-9		
		Drawing	4-1924670-0 / -9	-						
			5-1924670-0 / -9							
20			6-1924670-0 / -6							
	В	see Customer Drawing	1924671-1 / -8	-	_	_	_	1438322-3	-	
	С	see Customer Drawing	1924680-1	-	-	-	-	1438522-1	-	
								1438522-6		
	D	see Customer Drawing	1924681-1	-	-	-	_	1438522-7	-	
		Drawing						1438522-8		





Sealed Receptacle Housings 4-Rows with CPA

No. of	Kauling	Housing				Part Numbers					
Positions	Keying Options	Housing Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PCE Right-Angle	3 Header Vertical		
24	А	see Customer Drawing	1924675-1 / -9	-	-	-	-	1456777-1 / -2	-		

Sealed Receptacle Housings 4-Rows without CPA

No. of	Kasima					Part Numbers				
No. of Positions	Keying Options	Housing Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PCI Right-Angle	3 Header Vertical	
24	Α	see Customer	1924674-1 / -9	_	_	_	_	1456777-1 / -2	_	
21	7.	Drawing	1-1924674-0 / -2					1100111 17 2		






No. of Positions: 24 Position Assy without Shorting Bars without CPA

Housing Material: PA66 GF35

Wire Size Range: 0.22-0.75 mm²

Product Specifications: 114-13150 114-13060


Application Specification: 408-8598



Sealed Receptacle Housings 4-Rows without CPA

No. of	Keying	Housing				Part Numbers	;		
Positions	Options	Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PCI Right-Angle	3 Header Vertical
			3-1417171-9						
	А	see Customer	7-1419157-9				_	1456777-1 / -2	
	A	Drawing	1438103-1 / -9	-	-	_	_	1430777-17-2	-
			1-1438103-0 / -7						
			4-1419171-0						
	В	see Customer	1438095-2 / -9				_		
	D	Drawing	1-1438095-0 / -9		-	_	—	-	-
			2-1438095-0 / -3						
		see Customer Drawing	4-1419171-1			-	_	_	
24	С		1438096-2 / -9	-	-				-
		Diamig	1-1438096-0 / -4						
	D	see Customer	1438356-1 / -9						
	D	Drawing	1-1438356-0 / -2	-	-	—	—	-	-
		_	1438582-1						
	Ε	see Customer Drawing	1438582-2	-	-	-	-	-	-
		Drawing	1438582-3						
			1438583-1						
	F	see Customer Drawing	1438583-2	-	-	-	-	-	-
		Diaming	1438583-3						






Sealed Receptacle Housings - Multiple Rows

No. of	Kauina	Ususing		Part Numbers							
No. of Positions	Keying Options	Housing Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical		
30	A	Black	1438083-1	-	-	-	-	-	1438087-1		






Sealed Receptacle Housings 4-Rows with Standard Lever

No. of	Kauling	Ususing		Part Numbers						
Positions	Keying Options	Housing Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical	
			7-1419157-9							
			8-1419157-0 / -6	-	-	-	-	-	-	
			1438090-1 / -9							
			1-1438090-0 / -9							
			2-1438090-0 / -9							
		_	3-1438090-0 / -9							
	G	see Customer Drawing	4-1438090-0 / -9	-	-	-	-	8-1419157-9	-	
38		Drawing	5-1438090-0 / -9							
30			6-1438090-0 / -9							
			7-1438090-0 / -9							
			8-1438090-0 / -9							
			9-1438090-0 / -9							
			1456897-1 / -9							
	Н	Black	1488339-1	-	-	-	-	1438322-3	-	
	J	Black	1438485-1	-	_	_	_	1438522-6	_	
	K	Black	1438486-1	-	-	-	-	1438522-7	-	






Sealed Receptacle Housings 4-Rows with Low Profile Lever

No. of	Keying	Housing Color		Part Numbers								
Positions	Options		Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PCI Right-Angle	B Header Vertical			
	G	see Customer	1438397-1 / -9		_	_	_	8-1419157-9	_			
38	G	Drawing	1-1438397-0 / -3	-	-	-	-	0-1419137-9	-			
		see Customer Drawing	1438982-1 / -9									
	Н		1-1438982-0 / -9	-	-	-	-	1438322-3	-			
			2-1438982-0 / -2									






Sealed Receptacle Housings 4-Row with Standard Lever

No. of	Kasima	Housing -				Part Numbers			
Positions	Keying Options	Color	Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical
	G	Black	1438617-1	-	-	-	-	-	-
		_	1438098-1 / -9						
	Н	see Customer Drawing	1-1438098-0 / -9	-	-	-	-	1456777-2	-
_		Drawing	2-1438098-0 / -5						
			1438099-1 / -9						
40		_	1-1438099-0 / -9						
	J	see Customer Drawing	2-1438099-0 / -9	-	-	_	_	1456777-1	-
		Drawing	3-1438099-0						
			3-1438099-1						
	К	Black	1438679-1	-	-	-	_	-	-
	L	see Customer Drawing	1438435-1 / -9	-	-	-	_	-	-






Sealed Receptacle Housings 4-Row with Low Profile Lever

No. of	Kaulina	Housing Color		Part Numbers							
Positions	Keying Options		Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical		
	Н	see Customer Drawing	2098034-1	-	-	_	_	1456777-2	-		
			1924513-1 / -9								
40		see Customer	1-1924513-0 / -9	-	-	-	-	1456777-1	-		
	J	Drawing	2-1924513-0 / -9								
			3-1924513-0 / -5								






Sealed Receptacle Housings - Multiple Rows

No. of	Keying Options	Housing Color	Part Numbers							
No. of Positions			Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical	
10	А	Black	1438082-1	-	-	-	-	-	1438086-1	
46	В	Black	1438082-2						1438088-1	
	В	BIACK	1438082-2	-	-	_	_	-	1438087-2	






Sealed Receptacle Housings - Multiple Rows

No. of	Keying Options	Housing Color	Part Numbers							
No. of Positions			Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical	
	А	Black	1438129-1	-	-	-	-	1438139-1	-	
50	В	Black	1438129-2	-	-	-	-	-	1438063-1	
	С	Black	1438129-3	-	-	-	-	-	-	






Sealed Receptacle Housings - Multiple Rows with Shorting Bars

No. of Positions	Keying Options	Housing Color	Part Numbers							
			Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical	
	Key 1	Yellow	638595-1	_	_	-	_	638623-1	_	
	Key 2	Yellow	638595-2	-	-	-	-	638623-2	-	
60	Key 3	Yellow	638595-3	-	-	-	-	638623-3	-	
-	Key 4	Yellow	638595-4	-	-	-	-	638623-4	-	
	Key 5	Yellow	638595-5	-	-	-	-	638623-5	-	

Sealed Receptacle Housings - Multiple Rows without Shorting Bars

No. of	Keying Options	Housing Color	Part Numbers							
Positions			Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical	
60	Key 1	Black	1438521-1	-	-	-	-	-	-	






Sealed Receptacle Housings - Multiple Rows

No. of	Keying Options	Housing Color	Part Numbers							
Positions			Receptacle Housing	Cover	Locking Device	Cover and Lever	Mating Pin Housing	Mating PC Right-Angle	B Header Vertical	
	А	Black	1438136-1	-	-	-	1438726-1	_	1438063-1	
70	В	Black	1438136-2	-	-	-	-	_	1438698-1	
70	С	Black	1438136-3	-	-	-	-	_	-	
·	D	Black	1438136-4	-	-	-	-	-	-	





Sealed Printed Circuit Board Headers

No. of	Kauling	Hausian		Part Numbers						
Positions	Keying Options	Housing Color	PCB H Right-Angle	eader Vertical	Cover	Cover and Lever	Retainer Housing	Mating Receptacle Housing		
								1924672-1 / -9 & 1-1924672-0 / -9		
								2-1924672-0 / -7 & 2-1924672-9		
						_		3-1924672-2 / -7		
	A	Black	8-1419157-9	-	-		-	1924670-1 / -9 & 1-1924670-0 / -9		
								2-1924670-0 / -9 & 3-1924670-0 / -9		
								4-1924670-0 / -9 & 5-1924670-0 / -9		
								6-1924670-0 / -6		
		Black		_	_			7-1419157-9 & 8-1419157-0 / -6		
			8-1419157-9				_	1438090-1/-9 & 1-1438090-0/-9		
58						_		2-1438090-0 / -9 & 3-1438090-0 / -9		
50	G							4-1438090-0 / -9 & 5-1438090-0 / -9		
	G		0-1419107-9					6-1438090-0 / -9 & 7-1438090-0 / -9		
								8-1438090-0 / -9 & 9-1438090-0 / -9		
								1456897-1 / -9		
								1438397-1 / -9 & 1-1438397-0 / -3		
	В	Black	1438322-3					2-1924672-8 & 3-1924672-0		
	D	DIACK	1430322-3	-	-	-	-	1924671-1 / -8		
								1438982-1 / -9 & 1-1438982-0 / -9		
	Н	Black	1438322-3	-	-	-	-	2-1438982-0 / -2		
								1438484-1		



Sealed Printed Circuit Board Headers (continued)

Sealed Printed Circuit Board Headers

N (<i>K</i> .	Housing Color		Part Numbers							
No. of Positions	Keying Options		PCB H Right-Angle	eader Vertical	Cover	Cover and Lever	Retainer Housing	Mating Receptacle Housing			
								1924680-1			
	0	Black	1400500 5					1438484-1			
	C + H	Black	1438522-5	-	-	-	-	1438982-1 / -9 & 1-1438982-0 / -9			
								2-1438982-0 / -2			
								1924681-1			
								7-1419157-9 & 8-1419157-0 / -6			
								1438090-1 / -9 & 1-1438090-0 / -9			
								2-1438090-0 / -9 & 3-1438090-0 / -9			
58	D + G	Black	1438522-8	-	-	-	-	4-1438090-0 / -9 & 5-1438090-0 / -9			
								6-1438090-0 / -9 & 7-1438090-0 / -9			
								8-1438090-0 / -9 & 9-1438090-0 / -9			
								1456897-1 / -9			
								1438397-1 / -9 & 1-1438397-0 / -3			
	D. I	Disale	1400500.6					1924681-1			
	D + J	Black	1438522-6	-	_	_	_	1438485-1			
	D + K	Black	1438522-7					1924681-1			
	D+K	DIACK	1436522-7	-	_	_	_	1438486-1			
								3-1417171-9 & 7-1419157-9			
								1438103-1 / -9 & 1-1438103-0 / -7			
								1924674-1 / -9 & 1-1924674-0 / -2			
	A + H	Black	1456777-2	-	-	-	-	1924675-1 / -9 & 1-1924675-0 / -4			
								1438098-1 / -9 & 1-1438098-0 / -9			
								2-1438098-0 / -5			
64								2098034-1			
								3-1417171-9 & 7-1419157-9			
								1438103-1 / -9 & 1-1438103-0 / -7			
	A . I	Plaak	1456777 1					1924674-1 / -9 & 1-1924674-0 / -2			
	A + J	Black	1456777-1	_	_	-	-	1924675-1 / -9 & 1-1924675-0 / -4			
								1924513-1 / -9 & 1-1924513-0 / -9			
								2-1924513-0 / -9 & 3-1924513-0 / -5			






No. of Positions: 92 Position Vertical Assy 3 Pocket (__+ 46 + 46) 122 Position Vertical Assy 3 Pocket (30 + 46 + 46)

Housing Material: PBT GF30

Material and Finish: Brass Pins with tin/gold finish

Product Specification:

Application Specification:



Sealed Printed Circuit Board Headers

	<i></i>	Housing Color	Part Numbers							
No. of Keying Positions Options			PCB H Right-Angle	eader Vertical	Cover	Cover and Lever	Retainer Housing	Mating Receptacle Housing		
00		0		1 400000 0				1438082-1		
92	+ A + B	Gray	-	1438088-2	-	_	-	1438082-2		
122	A + A + B	Black		1438087-2				1438083-1		
122	A + A + D	DIACK	-	1430007-2	-	-	-	1438082-2		



Technical Features


No. of Positions: 150 Position Vertical Assy 3 Pocket (50 + 50 + 50)

Housing Material: PBT GF30

Material and Finish: Brass Pins with tin/gold finish

Product Specification:

Application Specification:



Sealed Printed Circuit Board Headers

No. of	Kassing	Housing	Part Numbers							
Positions	No. of Keying Positions Options		PCB H Right-Angle	leader Vertical	Cover	Cover and Lever	Retainer Housing	Mating Receptacle Housing		
								1438129-1		
150	A + B + C	Black	-	1438139-1	-	-	-	1438129-2		
								1438129-3		



Technical Features


No. of Positions: 190 Position Vertical Assy 3 Pocket (70 + 70 + 50)

Housing Material: PPA GF33

Material and Finish: Brass Pins with tin/gold finish

Product Specification:

Application Specification:



Sealed Printed Circuit Board Headers

No. of	Kasimu		Part Numbers							
No. of Positions	Keying Options		PCB H Right-Angle	leader Vertical	Cover	Cover and Lever	Retainer Housing	Mating Receptacle Housing		
								1438136-1		
190	B + A + C	Black	_	1438063-1	-	-	-	1438136-2		
								1438129-1		