

Catalog: 1654001 Issue Date: 06.2011

Accessory Outlet Filter

EBF Series




UL Recognized CSA Certified VDE Approved

EBF Series

- Accessory IEC 60320-1 C13 filtered outlet
- Allows connection of accessories while filtering noise between a system and the accessory
- Enhanced performance across the frequency range
- Grounded connection
- Suitable for international usage

Ordering Information





Specifications

Maximum leakage current each Line to Ground:

@ 120 VAC 60 Hz: .25 mA @250 VAC 50 Hz: .50 mA

Hipot rating (one minute):

Line to Ground: 2250 VDC
Line to Line: 1450 VDC

Rated Voltage (max.): 250 VAC


Operating Frequency: 50/60 Hz

Rated Current: 1 to 10A

Operating Ambient Temperature Range

(at rated current I_r): -10°C to +40°C In an ambient temperature (T_a) higher than +40°C the maximum operating current (I_O) is calculated as follows: $I_O = I_r \sqrt{(85-Ta)/45}$

Electrical Schematic



Available Part Numbers

1EBF1	1EBF4
3EBF1	3EBF4
6EBF1	6EBF4
10EBF1	10EBF4

Catalog: 1654001

Issue Date: 06.2011




Accessory Outlet Filter (continued)

EBF Series

Case Styles EBF1





Typical Dimensions:


Mounting holes (2):

Load Outlet (1): Line Terminals (2): Ground Terminal (1): .132 [3.35] Dia. with .236 [5.99] Dia. x 90° countersink for #4 flathead screw

IEC 60320-1 C13

.250 [6.3] with .07 [1.8] Dia. hole .250 [6.3] with .07 x .16 [1.8 x 3.8] slot

EBF4



Typical Dimensions:


Mounting holes (2):

Load Outlet (1): Wire Leads (3): .132 [3.35] Dia. with .236 [5.99] Dia. x 90° countersink for #4 flathead screw IEC 60320-1 C13 10.0 [254.0] min., 18AWG, UL1015

Case Dimensions

Part No.	A (max.)	B (max.)	C (max.)	D ± .01 ± .25	E (max.)
EBF1	2.57	1.33	1.00	1.575	1.99
CDF1	65.3	33.8	25.4	40.01	50.5
FBF4	2.09	1.39	1.16	1.575	1.99
CDF4	53.01	35.31	29.46	40.01	50.5

Recommended Panel Cutout



Front Mount Only
Tolerance + .008 [.203] / - .000 [.000]



Catalog: 1654001 Issue Date: 06.2011

Accessory Outlet Filter (continued)


EBF Series

Performance Data


Typical Insertion Loss

Measured in closed 50 Ohm system











6EBF



10EBF



Common Mode / Asymmetrical (L-G)Differential Mode / Symmetrical (L-L)

Minimum Insertion Loss

Measured in closed 50 Ohm system

Common Mode / Asymmetrical (Line to Ground)

Current			Frequ	iency	– MHz	Z	
Rating	.05	.15	.5	1	5	10	30
1A	23	32	41	47	47	47	40
3A	10	19	30	36	48	50	47
6A	1	10	22	28	42	48	47
10A	1	5	14	20	32	38	47

Differential Mode / Symmetrical (Line to Line)

,	Current	Frequency – MHz						
	Rating	.05	.15	.5	1	5	10	30
	1A	3	14	23	41	47	50	44
	3A	2	11	14	25	38	44	40
	6A	2	10	14	20	33	42	40
	10A	2	10	16	19	19	39	40