

2 POSITION LATCHED WIRE- TO-WIRE BALLAST DISCONNECT

- Help save space with a compact design
- Speed up field installation with a tool-less design



TE Connectivity (TE) introduces the 2 position, latched wire-to-wire ballast disconnect connector. This connector utilizes poke-in termination which supports easy field installation with no tools required. The compact design makes this connector ideal for applications with space constraints. Suitable for indoor lighting applications, this connector comes in four different colors enabling ease of identification and assembly.

BENEFITS

- Help save space with a compact design
- Speed up field installation with tool-less termination
- Ensure a reliable connection with a latched design

MECHANICAL

- Operating Temperature: -40°C to +105°C
- Durability: 10 cycles

APPLICATIONS

- Alarm Lighting
- Security Lighting
- Hospital Lighting
- Indoor Lighting
- LED Lighting
- Display Lighting

STANDARDS & SPECIFICATIONS

- Application Specification: 114-137159
- Product Specification: 108-137159
- UL1977 Approval: In Progress
- UL2459 Approval: In Progress
- Multi-pole Splicing Wire Connectors:

ELECTRICAL

- Current rating:
 - 16AWG: 9 A Max
 - 18AWG: 8 A Max.
 - 22AWG: 3 A Max.
- Voltage rating: 600VAC Max.
- Dielectric strength: 2200VAC

LEARN MORE

[Product Flyer](#)

[Product Selector Page](#)

[2 Position W2W Ballast Disconnect Connector Parts List](#)