

BH-316 Series, Rated up to 50 Amps, 115/200 VAC, 400 Hz or 28 Vdc

Product Facts

- 3PST NO, Double break
- **■** Hermetically sealed
- Auxiliary contacts available
- Meets many requirements of MIL-PRF-6106



Performance Data

Electrical Characteristics

Contact Arrangement — 3PST NO, Double Break

Rated Operating Voltage —

28 Vdc or 115/200 VAC, 400 Hz, 3 phase

 $\textbf{Resistive Rating} - 50 \ \mathrm{Amps}$

Inductive Rating -

115/200 VAC, 400 Hz, 3 phase — 50 Amps At 28 Vdc — 25 Amps

Motor Rating — 50 Amps

General Characteristics

Temperature Range — -55°C to +125°C

Operating Cycles (Life) at Rated Resistive Load, Min. — 100,000 cycles

Operating Cycles (Life)

Mechanical, Min. — 200,000 cycles Dielectric Strength —

All Circuits to Ground — 1,500 Vrms Circuit to Circuit — 1,500 Vrms Coil to Ground and Aux. Contacts — 1,000 Vrms

Insulation Resistance, Initial — 100 megohm min.

Weight, Max. — 1.20 lbs

Impact Shock — $5\,\mathrm{G}$

Close Time @ 28 Vdc and 25°C,

Max. — 25 msec

Release Time @ 28 Vdc and 25°C,

Max. — 10 msec

Coil Characteristics

Duty Cycle — Continuous

Operating Voltage, Nom. — 28 Vdc


Pickup Voltage, Max. — 18 Vdc

Dropout Voltage — 1.5 to 7 Vdc **Coil Current, Holding, Max.** — 0.5 Amp

Coil Type



A — Continuous




B — Continuous w/Suppression


For factory-direct application assistance, phone 419-521-9500 or fax 419-526-2749.


Catalog 5-1773450-5



BH-316 Series, Rated up to 50 Amps, 115/200 VAC, 400 Hz or 28 Vdc (Continued)








For factory-direct application assistance, phone 419-521-9500 or fax 419-526-2749.



BH-316 Series, Rated up to 50 Amps, 115/200 VAC, 400 Hz or 28 Vdc (Continued)

Circuit Configurations (Consult factory for other available circuit configurations)



HARTMAN Part Number	Construction Type	Mounting Style	Coil Type	Circuit Config.	TE Part Number
BH-316	Hermetically Sealed	Α	Continuous	2	1616008-4
BH-316A	Hermetically Sealed	Α	Continuous	1	1616008-5
BH-316D	Hermetically Sealed	Α	Continuous	1	1616008-6
BH-316C	Hermetically Sealed	В	Continuous	3	1-1616520-0

For factory-direct application assistance, phone 419-521-9500 or fax 419-526-2749.