


QR-50 Series Relay, AC Current Indicator, Rated up to 5 Amps, 115 VAC

Product Facts

- SPST NC
- **■** Environmentally sealed
- Meets many requirements of MIL-PRF-6106



Performance Data

Electrical Characteristics Contact Arrangement — SPST NC Resistive Rating @ 28 Vdc -.25 Amp

Lamp Load @ 28 Vdc — .10 Amp Sensing Current Rating — 5 Amp, AC continuous

General Characteristics

Temperature Range --55°C to +85°C

Altitude — 50,000 ft


Weight, Max. — .25 lbs


Operating Voltage, Nom. —

115 Vrms, 325-600 Hz


Pickup Max. -95 MA, AC

Dropout Min. — 47 MA AC





Circuit Configurations (Consult factory for other available circuit configurations)



For factory-direct application assistance, phone 419-521-9500 or fax 419-526-2749.

HARTMAN	Construction	Mounting	Duty	Circuit	TE
Part Number	Type	Style	Cycle	Config.	Part Number
QR-50V	Environmentally Sealed	Α	Continuous	1	1616132-3

For additional support numbers



QR-50 Series Relay, AC Current Indicator, Rated up to 15 Amps, 115 VAC

Product Facts

- SPDT
- **■** Environmentally sealed
- Meets many requirements of MIL-PRF-6106



Performance Data

Electrical Characteristics

Contact Arrangement — SPDT

Resistive Rating @ 28 Vdc —

.25 Amp

Lamp Load @ 28 Vdc — .08 Amp

Operating Voltage, Nom. — 115 VAC, 1 Phase, 400 Hz

Pickup Max. -

6 Amp, AC

Dropout Min. —

2.4 Amp, AC

Sensing Current Rating — 15 Amp, AC Continuous

General Characteristics

Temperature Range —


-55°C to +71°C


Altitude — 50,000 ft

Weight, Max. — .19 lbs

Sinusoidal Vibration —


10 G to 500 Hz





Mounting Style A

Circuit Configurations (Consult factory for other available circuit configurations)



Circuit Configuration 1

For factory-direct application assistance, phone 419-521-9500 or fax 419-526-2749.

HARTMAN	Construction	Mounting	Duty	Circuit	TE
Part Number	Type	Style	Cycle	Config.	Part Number
QR-50H	Environmentally Sealed	Α	Continuous	1	1616132-1

www.te.com

to change.