


H-23/24 Series Make & Break Load Switching — 30 kV Relay

(Not recommended for new designs)

Product Facts

- See K61 or K62 series for latest generation products
- Vacuum dielectric for power switching low current loads



Product Specifications Contact Arrangement — H-23 — SPST-NC H-24 — SPST-NO	0 E C
Contact Form — H-23 — B H-24 — A	0 0 F
Test Voltage, DC or 60 Hz (Peak) — 35 kV	S 2
Rated Operating Voltage (Peak) DC or 60 Hz — 30 kV 2.5 MHz — 24 kV 16 MHz — 18 kV 32 MHz — 7 kV	V F C F
Continuous Carry Current, Max. — DC or 60 Hz — 30 A 2.5 MHz — 20 A 16 MHz — 12 A 32 MHz — 7 A Coil Hi-Pot (Vrms, 60 Hz) — 500 A	N

Contact Capacitance — Between Open Contacts — N/A Open Contacts to Ground — N/A Contact Resistance, Max. — 0.015 ohm Operate Time, Max. — 30 ms Release Time, Max. — 20 ms Shock, 11ms, 1/2 Sine (Peak) — 20 g Vibration — Peak — 10 g (55 to 500 Hz) Operating Ambient Temperature Range — -55°C to +125°C Mechanical Life — 1 million cycles

Mechanical Life — 1 million cycles Weight, Nominal — 198.4 g (7 oz.)

Coil Data


Volts, Nominal DC	12 V	26.5 V	115 V
Pickup, Max.	8 Vdc	16 Vdc	80 Vdc
Dropout	.5-5 Vdc	1-10 Vdc	5-50 Vdc
Coil Resistance (±10%)	24	120 Ω	2000 Ω

Ratings listed are for 25°C, sea level conditions

Ordering Information

/12Vdc = 12Vdc

/115Vdc = 115 Vdc



For factory-direct application assistance, dial 800-253-4560, ext. 2055, or 805-220-2055.

Catalog 5-1773450-5 Revised 3-13

reference purposes only. Specifications subject to change.

Dimensions are shown for reference purposes only. Specifications subject USA: +1 800 522 6752 Asia Pacific: +86 0 400 820 6015 UK: +44 800 267 666 For additional support numbers please visit www.te.com

7–81

www.te.com