



RoHS 2 TECHNICAL FILE

PN: 2073244-1

Form: PC120712-01 Version 7 - 18 December 2012

CONTENT

•This technical file contains following sections :

1. PRODUCT IDENTIFICATION

- description
- list of components
- list of suppliers
- applicable EEE category
- applicable exemptions
- picture (optional)
- 2. RISK ASSESSMENT
 - risk assessment methodology
 - material risk
 - supplier risk
 - part noncompliance risk
 - recommended level of technical documentation

3. EVALUATION

- evaluation of documentation
- evaluation criteria
- compliancy confirmation

4. REFERENCES

- International Standards
- EU documents
- TE Connectivity documents
- 5. OVERVIEW TABLE

1. PRODUCT IDENTIFICATION

DESCRIPTION

product group
typeCCAO Mobile & Consumer Electronicsserial number
batch
part number(s)2073244-1
patchcord 8p4c

LIST OF COMPONENTS

All components are listed in the overview table of this technical file.

LIST OF SUPPLIERS

All suppliers are listed in the overview table of this technical file.

APPLICABLE EEE CATEGORY

3. IT and Telecommunications Equipment

APPLICABLE EXEMPTIONS (if any)

PICTURE (optional)

RISK ASSESSMENT METHODOLOGY

- MATERIAL RISK SUPPLIER RISK
 - PART NONCOMPLIANCE RISK
 - RECOMMENDED LEVEL OF TECHNICAL DOCUMENTATION

MATERIAL RISK

- All TE Connectivity parts are categorized in commodity codes. All these commodity codes were evaluated by an internal material expert team and assigned a LOW-MEDIUM-HIGH material risk.
- This LOW-MEDIUM-HIGH material risk evaluation is documented in the overview table of this technical file.
- Business Units (BU) have the opportunity to override this default material risk, based on :
 - BU specific implementation of TE's corporate compliance validation specification TEC-138-703
 - or BU specific compliance procedures
 - or detailed material knowledge of the evaluated component.
- Requirements for BU override of material risk :
 - although BU specific assessment procedures and scoring systems may differ, in the end all scores are to be transferred to a LOW-MEDIUM-HIGH material risk evaluation that can be documented in the overview table
 - any material risk override needs to be explained by a comment in the overview table.

SUPPLIER RISK

- All TE Connectivity suppliers are assigned a LOW-MEDIUM-HIGH supplier risk, using several measurement criteria as indicators for supplier's capabilities to manage hazardous substance content of their products.
- This LOW-MEDIUM-HIGH supplier risk evaluation is documented in the overview table of this technical file.
- Business Units (BU) have the opportunity to override this default supplier risk, based on :
 - BU specific implementation of TE's corporate compliance validation specification TEC-138-703
 - or BU specific compliance procedures
 - or available supplier audit results
- Requirements for BU override of supplier risk :
 - although BU specific assessment procedures and scoring systems may differ, in the end all scores are to be transferred to a LOW-MEDIUM-HIGH supplier risk evaluation that can be documented in the overview table
 - any supplier risk override needs to be explained by a comment in the overview table.

PART NONCOMPLIANCE RISK

- The PART NONCOMPLIANCE RISK combines the material risk evaluation and the supplier risk evaluation into an overall LOW-MEDIUM-HIGH part noncompliance risk ranking.
- The material risk is the main driving factor for the PART NONCOMPLIANCE RISK, with a beneficial influence for trustworthy suppliers.

PART NONCOMPLIANCE		SUPPLIER RISK						
RIS			LOW	MEDIUM	HIGH			
		1						
	LOW	₽	LOW	LOW	LOW			
MATERIAL								
RISK	MEDIUM	⇒	LOW	MEDIUM	MEDIUM			
	HIGH	⇒	LOW	MEDIUM	HIGH			
				-				

RECOMMENDED LEVEL OF TECHNICAL DOCUMENTATION

- The different levels of the PART NONCOMPLIANCE RISK (low-medium-high) determine the **RECOMMENDED LEVEL of TECHNICAL DOCUMENTATION to be established for** documenting the part's compliance with the RoHS substance restrictions :
 - LOW part noncompliance risk
 - HIGH part noncompliance risk
- : generic supplier Statement of Compliance (SoC)
- MEDIUM part noncompliance risk : part specific supplier Statement of Compliance (SoC) : - supplier Material Declaration (MD)
 - or
 - test report
- The recommended technical documentation for every part is documented in the overview table of this technical file.

RECOMMENDED			SUPPLIER RISK				
MINIM DOCUMEN LEVI	TATION		LOW	MEDIUM	HIGH		
MATERIAL RISK	LOW	₽	Generic Supplier Compliance Response	Generic Supplier Compliance Response	Generic Supplier Compliance Response		
	MEDIUM	Generic Supplier Compliance Response		Part Specific Supplier Response	Part Specific Supplier Response		
	HIGH	Ŷ	Generic Supplier Compliance Response	Part Specific Supplier Response	Supplier Material Declaration or Test Report - supplier - TE internal - 3rd party		

3. EVALUATION

EVALUATION OF DOCUMENTATION

- All technical documentation needs to be evaluated whether :
 - the document is of sufficient quality to be used, and
 - actually confirms the required compliancy with the substance restrictions of RoHS2.

EVALUATION CRITERIA

- Following is a non-exhaustive list of criteria to take into account for the evaluation of supplier answers and/or test reports :
 - clear identification of supplier or test lab / letterhead
 - date of answer/test report
 - location of test lab and name of tester
 - clear product identification
 - applicable legislation stated
 - analytical test method used for the test
 - ISO 17025 certification of test lab
 - description of the conclusion of the testing / confirmation that all results do meet the substance restrictions limits
 - no unacceptable waiver statements
 - contact for further information
 - signature

COMPLIANCY CONFIRMATION

- For each component, the result of this compliancy check is documented, by including the following information in the overview table :
 - result of the quality/compliance check (Compliant or Not OK)
 - name of the evaluator who performed the quality/compliancy check
 - date of the quality/compliancy check

4. REFERENCES

International Standards

- ISO 9001 Quality Management Systems Requirements
- IECQ QC080000 Electrical and Electronic Components and Products Hazardous Substance Process Management System Requirements

EU documents

- Directive 2011/65/EU on the restriction of the use of certain hazardous substances in electrical and electronic equipment
- EN 50581 (2012) : Technical documentation for the assessment of electrical and electronic products with respect to the restriction of hazardous substances

TE Connectivity documents

- TE Quality Policy (TEC-11-01)
- TE Product Environmental Compliance Policy (TEC-16-01)
- TE Global Quality Management System (TEC-1000)
- TE Product Environmental Compliance Processes flowchart
- TE Product Compliance Validation Specification (TEC-138-703)

Accepted Kiwi Lee Kiwi Lee	ABLE			0	2h Ir	_ • • •
t Description ROHS Code Material Risk Supplier Risk Part Risk Min Recommended Documentation					Check	Evaluation by: Kiwi Lee
				Supplier Risk		Min Recommended Documentation
And </td <td>patchcord 8p4c</td> <td>R - ALWAYS EU ROHS/ELV COMPLIANT</td> <td>LOW</td> <td></td> <td></td> <td></td>	patchcord 8p4c	R - ALWAYS EU ROHS/ELV COMPLIANT	LOW			
Image: bot of the set of the						
Image: bit is a set of the s						
AndA						
NoteNo						
NNN <td></td> <td></td> <td></td> <td></td> <td></td> <td></td>						
NoteNo						
III						
NoteNo						
AppendixAppend						
NNN						
NNN						
III						
NoteNo						
NNN						
NNN <td></td> <td></td> <td></td> <td></td> <td></td> <td></td>						
Note </td <td></td> <td></td> <td></td> <td></td> <td></td> <td></td>						
Note </td <td></td> <td></td> <td></td> <td></td> <td></td> <td></td>						
Note </td <td></td> <td></td> <td></td> <td></td> <td></td> <td></td>						
Image: style interpressImage: style interpressIma						
Image: stateImage: state </td <td></td> <td></td> <td></td> <td></td> <td></td> <td></td>						
NoteNot						
III <td></td> <td></td> <td></td> <td></td> <td></td> <td></td>						
NNN <td></td> <td></td> <td></td> <td></td> <td></td> <td></td>						
II <td></td> <td></td> <td></td> <td></td> <td></td> <td></td>						
Image Image Image Image Image Image						
Image: book of the sectorImage: book of the sector <t< td=""><td></td><td></td><td></td><td></td><td></td><td></td></t<>						
NNN						
NoteNo						
Image: state of the state of						
NNN <td></td> <td></td> <td></td> <td></td> <td></td> <td></td>						
Note </td <td></td> <td></td> <td></td> <td></td> <td></td> <td></td>						
Image: book of the set of th						
Note </td <td></td> <td></td> <td></td> <td></td> <td></td> <td></td>						
Note </td <td></td> <td></td> <td></td> <td></td> <td></td> <td></td>						
And <td< td=""><td></td><td></td><td></td><td></td><td></td><td></td></td<>						
Image: style interpresentImage: style interpresent <t< td=""><td></td><td></td><td></td><td></td><td></td><td></td></t<>						
Image: style interpresentImage: style interpresent <t< td=""><td></td><td></td><td></td><td></td><td></td><td></td></t<>						
NoteNo						
Image: style intermed intermImage: style intermImage:						
Note </td <td></td> <td></td> <td></td> <td></td> <td></td> <td></td>						
Note						
NNN <td></td> <td></td> <td></td> <td></td> <td></td> <td></td>						
NoteNo						
Image: style is the style is						
Image: state in the state in						
Image: state of the state of						
Image: style s						
Image: state of the state of						
Image: style s						
						+
Image: style s						
Image: state in the state i						
NoteN						
NN						
Image: state of the state of						
Image: style s						
Image: state of the state of						
Image: state of the state of						
Image: state of the state of						
Image: state of the state of		<u> </u>				+
Image: state of the state of						
Image: state of the state of						
Image: state of the state of						
Image: state of the state of						
Image: sector of the sector						
Image: state						
Image: sector						
Image: sector						
Image: second						+
Image: second						
Image: state of the s						