

PRINTABLE CONTINUOUS TUBING

Heat-shrinkable high-performance tubing for wire and cable identification





Contents

Printable continuous tubing

Overview	4
RPS-CT (Commercial grade)	6
TMS-CT (Military grade)	9
D-CT (Organic fluids, especially oils and diesel fuel resistant)	12
HX-CT (Zero-halogen low fire hazard)	14
ZHD-CT (Zero-halogen low fire hazard and fluid resistant)	16
HT-CT (High temperature and highly flame retardant)	18

Identification solutions

Printable continuous tubing



PRINTABLE CONTINUOUS TUBING (-CT).

Benefit from TE Connectivity experience in identification Polyolefin sleeves with the heat-shrinkable high-performance tubing that can be used with any TE thermal transfer roll printer to create identification sleeves for wire and cable harnesses in harsh environments. Spooled continuous reels are useful when printing identical markers or when the user requires more flexibility on the length of the grades used. The range is available in 6 grade depending on the application requirements: commercial, military, Organic fluids, Zero-halogen low fire hazard, Zero halogen low fire hazard and fluid resistant, High temperature or highly flame retardant.

CONTINUOUS TUBING FEATURES

BENEFIT STATEMENTS

- Create identification labels for wire and cable harnesses in harsh environments with any TE Connectivity thermal transfer roll printers
- User flexibility to design custom length markers from 5 mm to 3 meters using TE WinTotal software
- Optimal reel length to maximize bulk printing and minimize storage space
- Reduce installation time with a more open profile
- Printable Continuous tube can be used as well as insulation and protection from mechanical abuse
- Continuous Tubing is also compatible with Automatic Harness assembly machine

APPLICATIONS

- Rail
- Military
- Space, Aerospace
- Industrial
- Automation
- Electrical
- Panel builders

KEY FEATURES

- High performance thermal transfer printable tubing in a continuous format
- Material, sizes and color to suit both harsh environment and commercial print criteria
- Compatible with all TE roll printers
- Data input with Wintotal
- Open profile to allow easier application
- Large range of colors available with same minimum order quantity
- With black color we propose thermal transfer white ribbon

STANDARDS AND SPECIFICATIONS

- **RPS-CT:** MIL-STD-202, NFPA 130, UL STD 244 - E35586
- **TMS-CT:** EN45545-2, SAE-AMS-23053/5, MIL-STD-202, UL STD 224 - E35586
- **HT-CT:** EN45545-2, SAE-AS4952, MIL-STD-202
- **D-CT:** EN45545-2, NFPA 130, MIL-STD-202 Method 215
- **ZHD-CT:** EN45545-2, NFPA 130
- **HX-CT:** EN45545-2, NF F 16-101, London Underground 1-085

Identification solutions

Printable continuous tubing

Selection guide

PRINTABLE HEAT SHRINK TUBING - CONTINUOUS FORMAT

Product	Grade	Size Range	Shrink Ratio	Temperature Ratings	Color Options	Applications	Datasheet
RPS-CT	Commercial	50 m	3:1	-30°C to +105°C	White, Yellow, Black, Blue, Red, Green	Industrial	TTDS-269
TMS-CT	Military	50 m	3:1 (size 1-1/2 and 2 in. are 2:1)	-55°C to +135°C	White, Yellow, Black, Blue, Red, Green, Pink, Orange, Clear	Aerospace & Defense Industrial	TTDS-268
D-CT	Chemicals Resistant Diesel Resistant	50 m	3:1 (size 38 mm is 3:1)	-75°C to +135°C	White, Yellow	Railway - Aerospace	TTDS-267
ZHD-CT	Halogen free Low Fire Hazard Diesel Resistant	50 m	2:1	-55°C to +125°C	White, Yellow	Railway - Automotive	TTDS-273
HX-CT	Halogen free Low Fire Hazard	40 m 50 m	2:1	-40°C to +105°C	White, Yellow, Black, Blue, Red, Green	Railway - Aerospace	TTDS-270
HT-CT	High Temperature Low Outgassing	50 m	2:1 (size 3/32 is 3:1)	-55°C to +225°C	White, Yellow, Black, Blue, Red, Green, Orange	Harsh environment Aerospace - Spatial Semi-conductor industry	TTDS-271

To select the right ribbon, use our ribbon Tool selector



CONVERSION TABLE (METRIC / IMPERIAL)

Imperial Measurement (Inches)		Metric Measurement (Millimeters)
3/32	0.093"	2.4 mm
1/8	0.125"	3.2 mm
3/16	0.175"	4.8 mm
1/4	0.250"	6.4 mm
3/8	0.375"	9.5 mm
1/2	0.500"	12.7 mm
3/4	0.750"	19.1 mm
1	1.000"	25.4 mm
1 1/2	1.500"	38.1 mm
2	2.000"	50.8 mm

COLOR CODINGS FOR CONTINUOUS TUBING

Color legend	Name	Color
0	Black (BK)	
1	Brown (BN)	
2	Red (RD)	
3	Orange (OG)	
4	Yellow (YE)	
5	Green (GN)	
6	Blue (BU)	
7	Violet (VT)	
8	Gray (GY)	
9	White (WH)	
2L	Pink (PK)	
8A	Silver (SR)	
X	Clear (CL)	

Identification solutions

Printable continuous tubing

RPS-CT (Commercial Grade)

Made from durable, flame retarded, radiation cross linked heat shrinkable polyolefin. TMS-CT is a thin wall, light weight, fast recovery 3:1 shrink ratio sleeve*, allowing the customer to cover a wide range of cable diameters.

Suitable for a wide variety of applications including, commercial, industrial and transport.

- Printed marker sleeves meet the requirements of AS 5942 and MIL 202 Method 215 when used as a complete system, as recommended by TE Connectivity.
- Identification printer product ribbon matrix for the recommended printer/product/ribbon combinations (refer to TE document 411-121005).
- RPS-CT Heat Shrink Identification Marker Sleeving is available as part of a complete identification system.
- The system comprises specific printers, thermal transfer ribbons and WINTOTAL software.

FEATURES

- Self-extinguishing, non-flame propagating.
- Resistant to key Common industrial fluids (defined by RW-2510).
- Commercial grade performance.
- Can be laser marked for superior performance.
- Pre-termination Cable Identification.
- Sleeve diameters from 3.2 mm to 38.1 mm (1/8 to 1-1/2inch).
- More open profile for easier use.
- RPS-CT 3:1 Shrink ratio (*except RPS-CT- 38.1 (1-1/2 inch) which is 2:1 ratio)

BENEFITS

- Create identification labels for wire and cable harnesses in harsh environments with any TE Connectivity thermal transferable printers
- User flexibility to design custom length markers from 5 mm to 3 meters using TE WinTotal software
- Optimal reel length to maximize bulk printing and minimize storage space
- Reduce installation time with a more open profile
- Printable Continuous tube can be used as well as insulation and protection from mechanical abuse.

APPLICATIONS

- Communications
- Wire assemblies
- Electrical Panel
- Oil & Gas Control systems

MATERIAL

- Flame retardant, heat-shrinkable polyolefin cross



Temperature Rating

Operating Temperature range:
-30°C to 105°C

Specifications and Approvals

- NFPA 130 Standard for Fixed Guideway Transit and Passenger Rail Systems, Fire protection requirements, Interior Fire Propagation Resistance
- MIL-STD-202 Method 215
- UL STD 224 - E35586
- Federal Railroad Administration, DOT, Appendix B to Part 238


Recommended Hardware and Software

- Printer: T2212, T3212, T3224, T6112DS
- Ribbon: TMS/4RPSCE Serie
- Software: WinTotal

For More information

- Technical Datasheet: TTDS-269
- Product Specification Sheet: RW-2510
- TT Printer accessories: TTDS-260







PART NUMBERING SYSTEM



Optimal print result on TE identification Continuous Tube products can be achieved by using the WINTOTAL software in conjunction with TE Printers and recommended TE Ribbon.

RPS-CT

ORDERING INFORMATION

Description	Color	Part Number	Supplied diameter		Recommended use range (Min-Max)		Spool length Mt. (ft)
			(mm)	(inches)	(mm)	(inches)	
 RPS-CT-50M-3.2-OUT-9	White	EL7583-000	3.2	0.125	1.2-2.7	0.044-0.105	50 (164)
RPS-CT-50M-4.8-OUT-9		EL7584-000	4.8	0.187	1.7-4.1	0.069-0.160	
RPS-CT-50M-6.4-OUT-9		EL7585-000	6.4	0.250	2.3-5.5	0.091-0.215	
RPS-CT-50M-9.5-OUT-9		EL7586-000	9.5	0.375	3.5-8.1	0.137-0.320	
RPS-CT-50M-12.7-OUT-9		EL7587-000	12.7	0.500	4.6-10.8	0.183-0.425	
RPS-CT-50M-19.0-OUT-9		EL7588-000	19.0	0.750	7.0-16.2	0.275-0.640	
RPS-CT-50M-25.4-OUT-9		EL7589-000	25.4	1.000	9.3-21.6	0.366-0.850	
RPS-CT-50M-38.1-OUT-9		EL7590-000	38.1	1.500	20.9-33.0	0.825-1.300	
 RPS-CT-50M-3.2-OUT-4	Yellow	EL7597-000	3.2	0.125	1.2-2.7	0.044-0.105	50 (164)
RPS-CT-50M-4.8-OUT-4		EL7598-000	4.8	0.187	1.7-4.1	0.069-0.160	
RPS-CT-50M-6.4-OUT-4		EL7599-000	6.4	0.250	2.3-5.5	0.091-0.215	
RPS-CT-50M-9.5-OUT-4		EL7600-000	9.5	0.375	3.5-8.1	0.137-0.320	
RPS-CT-50M-12.7-OUT-4		EL7601-000	12.7	0.500	4.6-10.8	0.183-0.425	
RPS-CT-50M-19.0-OUT-4		EL7602-000	19.0	0.750	7.0-16.2	0.275-0.640	
RPS-CT-50M-25.4-OUT-4		EL7603-000	25.4	1.000	9.3-21.6	0.366-0.850	
RPS-CT-50M-38.1-OUT-4		EL7604-000	38.1	1.500	20.9-33.0	0.825-1.300	
 RPS-CT-50M-3.2-OUT-0	Black	ER2164-000	3.2	0.125	1.2-2.7	0.044-0.105	50 (164)
RPS-CT-50M-4.8-OUT-0		ER2165-000	4.8	0.187	1.7-4.1	0.069-0.160	
RPS-CT-50M-6.4-OUT-0		ER2166-000	6.4	0.250	2.3-5.5	0.091-0.215	
RPS-CT-50M-9.5-OUT-0		ER2167-000	9.5	0.375	3.5-8.1	0.137-0.320	
RPS-CT-50M-12.7-OUT-0		ER2168-000	12.7	0.500	4.6-10.8	0.183-0.425	
RPS-CT-50M-19.0-OUT-0		ER2169-000	19.0	0.750	7.0-16.2	0.275-0.640	
RPS-CT-50M-25.4-OUT-0		ER2170-000	25.4	1.000	9.3-21.6	0.366-0.850	
RPS-CT-50M-38.1-OUT-0		ER2171-000	38.1	1.500	20.9-33.0	0.825-1.300	
 RPS-CT-50M-3.2-OUT-6	Blue	ER9614-000	3.2	0.125	1.2-2.7	0.044-0.105	50 (164)
RPS-CT-50M-4.8-OUT-6		ER9617-000	4.8	0.187	1.7-4.1	0.069-0.160	
RPS-CT-50M-6.4-OUT-6		ER9620-000	6.4	0.250	2.3-5.5	0.091-0.215	
RPS-CT-50M-9.5-OUT-6		ER9623-000	9.5	0.375	3.5-8.1	0.137-0.320	
RPS-CT-50M-12.7-OUT-6		ER9626-000	12.7	0.500	4.6-10.8	0.183-0.425	
RPS-CT-50M-19-OUT-6		ER9629-000	19.0	0.750	7.0-16.2	0.275-0.640	
 RPS-CT-50M-3.2-OUT-5	Green	ER9613-000	3.2	0.125	1.2-2.7	0.044-0.105	50 (164)
RPS-CT-50M-4.8-OUT-5		ER9616-000	4.8	0.187	1.7-4.1	0.069-0.160	
RPS-CT-50M-6.4-OUT-5		ER9619-000	6.4	0.250	2.3-5.5	0.091-0.215	
RPS-CT-50M-9.5-OUT-5		ER9622-000	9.5	0.375	3.5-8.1	0.137-0.320	
RPS-CT-50M-12.7-OUT-5		ER9625-000	12.7	0.500	4.6-10.8	0.183-0.425	
RPS-CT-50M-19-OUT-5		ER9628-000	19.0	0.750	7.0-16.2	0.275-0.640	
 RPS-CT-50M-3.2-OUT-2	Red	ER9612-000	3.2	0.125	1.2-2.7	0.044-0.105	50 (164)
RPS-CT-50M-4.8-OUT-2		ER9615-000	4.8	0.187	1.7-4.1	0.069-0.160	
RPS-CT-50M-6.4-OUT-2		ER9618-000	6.4	0.250	2.3-5.5	0.091-0.215	
RPS-CT-50M-9.5-OUT-2		ER9621-000	9.5	0.375	3.5-8.1	0.137-0.320	
RPS-CT-50M-12.7-OUT-2		ER9624-000	12.7	0.500	4.6-10.8	0.183-0.425	
RPS-CT-50M-19-OUT-2		ER9627-000	19.0	0.750	7.0-16.2	0.275-0.640	

Identification solutions

Printable continuous tubing



Identification solutions

Printable continuous tubing

TMS-CT (Military Grade)

Made from durable, flame retarded, radiation cross linked heat shrinkable polyolefin. TMS-CT is a thin wall, light weight, fast recovery 3:1 shrink ratio sleeve*, allowing the customer to cover a wide range of cable diameters.

Suitable for a wide variety of applications including, aerospace, military, industrial, transport and energy.

- Printed marker sleeves meet the requirements of AS 5942 and MIL 202 Method 215 when used as a complete system, as recommended by TE Connectivity.
- Identification printer product ribbon matrix for the recommended printer/product/ribbon combinations (refer to TE document 411-121005).
- TMS-CT meets the material requirements of SAE-AMS-DTL-23053/5 Class 1.
- TMS-CT Heat Shrink Identification Marker Sleeving is available as part of a complete identification system.

FEATURES

- High performance thermal transfer printable tubing in a continuous format
- Material: irradiated, thermally-stabilised polyolefin compound
- Material, sizes and color to suit both harsh environment and commercial print criteria
- Compatible with all TE Printers
- Open profile to allow easier application
- Shrink Ratio:3:1 (*except 1-1/2 and 2 inch TMS-CT which is 2:1)
- With black color we propose thermal transfer white ribbon.

BENEFITS

- Create identification labels for wire and cable harnesses in harsh environments with any TE Connectivity thermal transferable printers
- User flexibility to design custom length markers from 5 mm to 3 meters using TE WinTotal software
- Optimal reel length to maximize bulk printing and minimize storage space
- Reduce installation time with a more open profile
- Printable Continuous tube can be used as well as insulation and protection from mechanical abuse.

APPLICATIONS

- Aerospace
- Military
- Motor sports
- Oil & Gas

MATERIAL

- Flame retardant, heat-shrinkable polyolefin cross linked



Temperature Rating

Operating Temperature range:
-55°C to 135°C

Specifications and Approvals

- EN45545-2 R24 HL2,
- SAE-AMS-23053/5,
- MIL-STD-202 Method 215
- UL STD 224 - E35586
- Federal Railroad Administration, DOT, Appendix B to Part 238
- SHAZAINENNSHI, Japan Railway Rolling Stock & Machinery Association 2003
- Classification 'Flame Retardant' Serial number 2015-163K


Recommended Hardware and Software

- Printer: T2212, T3212, T3224, T6112DS
- Ribbon: TMS/4RPSCE Serie
- Software: WinTotal

For More information

- Technical Datasheet: TTDS-268
- Product Specification Sheet: RW-2511
- TT Printer accessories: TTDS-260

PART NUMBERING SYSTEM









Optimal print result on TE identification Continuous Tube products can be achieved by using the WINTOTAL software in conjunction with TE Printers and recommended TE Ribbon.

Identification solutions

Printable continuous tubing

TMS-CT

ORDERING INFORMATION



Description	Color	Part Number	Supplied diameter		Recommended use range (Min-Max)		Spool length Mt. (ft)		
			(mm)	(inches)	(mm)	(inches)			
 TMS-CT-50M-3/32-OUT-9	White	EL7660-000	2.4	0.093	0.8-1.9	0.032-0.075	50 (164)		
TMS-CT-50M-1/8-OUT-9		EL7661-000	3.2	0.125	1.1-2.6	0.044-0.105			
TMS-CT-50M-3/16-OUT-9		EL7662-000	4.8	0.187	1.7-4.0	0.069-0.160			
TMS-CT-50M-1/4-OUT-9		EL7663-000	6.4	0.250	2.3-5.4	0.091-0.215			
TMS-CT-50M-3/8-OUT-9		EL7664-000	9.5	0.375	3.4-8.1	0.137-0.320			
TMS-CT-50M-1/2-OUT-9		EL7665-000	12.7	0.500	4.6-10.7	0.183-0.425			
TMS-CT-50M-3/4-OUT-9		EL7666-000	19.0	0.750	6.9-16.2	0.275-0.640			
TMS-CT-50M-1-OUT-9		EL7667-000	25.4	1.000	9.2-21.5	0.366-0.850			
TMS-CT-50M-1-1/2-OUT-9		EL7668-000	38.1	1.500	20.9-33.0	0.825-1.300			
TMS-CT-50M-2-OUT-9		EL7669-000	50.8	2.000	27.9-44.9	1.100-1.750			
 TMS-CT-50M-3/32-OUT-4	Yellow	EL7643-000	2.4	0.093	0.8-1.9	0.032-0.075	50 (164)		
TMS-CT-50M-1/8-OUT-4		EL7644-000	3.2	0.125	1.1-2.6	0.044-0.105			
TMS-CT-50M-3/16-OUT-4		EL7645-000	4.8	0.187	1.7-4.0	0.069-0.160			
TMS-CT-50M-1/4-OUT-4		EL7646-000	6.4	0.250	2.3-5.4	0.091-0.215			
TMS-CT-50M-3/8-OUT-4		EL7647-000	9.5	0.375	3.4-8.1	0.137-0.320			
TMS-CT-50M-1/2-OUT-4		EL7648-000	12.7	0.500	4.6-10.7	0.183-0.425			
TMS-CT-50M-3/4-OUT-4		EL7649-000	19.0	0.750	6.9-16.2	0.275-0.640			
TMS-CT-50M-1-OUT-4		EL7650-000	25.4	1.000	9.2-21.5	0.366-0.850			
TMS-CT-50M-1-1/2-OUT-4		EL7651-000	38.1	1.500	20.9-33.0	0.825-1.300			
TMS-CT-50M-2-OUT-4		EL7652-000	50.8	2.000	27.9-44.9	1.100-1.750			
 TMS-CT-50M-3/32-OUT-0	Black	ER2148-000	2.4	0.093	0.8-1.9	0.032-0.075	50 (164)		
TMS-CT-50M-1/8-OUT-0		ER2149-000	3.2	0.125	1.1-2.6	0.044-0.105			
TMS-CT-50M-3/16-OUT-0		ER2150-000	4.8	0.187	1.7-4.0	0.069-0.160			
TMS-CT-50M-1/4-OUT-0		ER2151-000	6.4	0.250	2.3-5.4	0.091-0.215			
TMS-CT-50M-3/8-OUT-0		ER2152-000	9.5	0.375	3.4-8.1	0.137-0.320			
TMS-CT-50M-1/2-OUT-0		ER2153-000	12.7	0.500	4.6-10.7	0.183-0.425			
TMS-CT-50M-3/4-OUT-0		ER2154-000	19.0	0.750	6.9-16.2	0.275-0.640			
TMS-CT-50M-1-OUT-0		ER2155-000	25.4	1.000	9.2-21.5	0.366-0.850			
TMS-CT-50M-1-1/2-OUT-0		ER2156-000	38.1	1.500	20.9-33.0	0.825-1.300			
TMS-CT-50M-2-OUT-0		ER2157-000	50.8	2.000	27.9-44.9	1.100-1.750			
 TMS-CT-50M-3/32-OUT-3	Orange	ER9633-000	2.4	0.093	0.8-1.9	0.032-0.075	50 (164)		
TMS-CT-50M-1/8-OUT-3		ER9638-000	3.2	0.125	1.1-2.6	0.044-0.105			
TMS-CT-50M-3/16-OUT-3		ER9643-000	4.8	0.187	1.7-4.0	0.069-0.160			
TMS-CT-50M-1/4-OUT-3		ER9648-000	6.4	0.250	2.3-5.4	0.091-0.215			
TMS-CT-50M-3/8-OUT-3		ER9653-000	9.5	0.375	3.4-8.1	0.137-0.320			
TMS-CT-50M-1/2-OUT-3		ER9658-000	12.7	0.500	4.6-10.7	0.183-0.425			
TMS-CT-50M-3/4-OUT-3		ER9663-000	19.0	0.750	6.9-16.2	0.275-0.640			
TMS-CT-50M-1-OUT-3		ER9668-000	25.4	1.000	9.2-21.5	0.366-0.850			
 TMS-CT-50M-3/32-OUT-6		Blue	ER9635-000	2.4	0.093	0.8-1.9		0.032-0.075	50 (164)
TMS-CT-50M-1/8-OUT-6			ER9640-000	3.2	0.125	1.1-2.6		0.044-0.105	
TMS-CT-50M-3/16-OUT-6	ER9645-000		4.8	0.187	1.7-4.0	0.069-0.160			
TMS-CT-50M-1/4-OUT-6	ER9650-000		6.4	0.250	2.3-5.4	0.091-0.215			
TMS-CT-50M-3/8-OUT-6	ER9655-000		9.5	0.375	3.4-8.1	0.137-0.320			
TMS-CT-50M-1/2-OUT-6	ER9660-000		12.7	0.500	4.6-10.7	0.183-0.425			
TMS-CT-50M-3/4-OUT-6	ER9665-000		19.0	0.750	6.9-16.2	0.275-0.640			
TMS-CT-50M-1-OUT-6	ER9670-000		25.4	1.000	9.2-21.5	0.366-0.850			
 TMS-CT-50M-3/32-OUT-5	Green		ER9634-000	2.4	0.093	0.8-1.9	0.032-0.075	50 (164)	
TMS-CT-50M-1/8-OUT-5			ER9639-000	3.2	0.125	1.1-2.6	0.044-0.105		
TMS-CT-50M-3/16-OUT-5		ER9644-000	4.8	0.187	1.7-4.0	0.069-0.160			
TMS-CT-50M-1/4-OUT-5		ER9649-000	6.4	0.250	2.3-5.4	0.091-0.215			
TMS-CT-50M-3/8-OUT-5		ER9654-000	9.5	0.375	3.4-8.1	0.137-0.320			
TMS-CT-50M-1/2-OUT-5		ER9659-000	12.7	0.500	4.6-10.7	0.183-0.425			
TMS-CT-50M-3/4-OUT-5		ER9664-000	19.0	0.750	6.9-16.2	0.275-0.640			
TMS-CT-50M-1-OUT-5		ER9669-000	25.4	1.000	9.2-21.5	0.366-0.850			

Identification solutions

Printable continuous tubing

TMS-CT

ORDERING INFORMATION

Description	Color	Part Number	Supplied diameter		Recommended use range (Min-Max)		Spool length Mt. (ft)
			(mm)	(inches)	(mm)	(inches)	
 TMS-CT-50M-3/32-OUT-2	Red	ER9630-000	2.4	0.093	0.8-1.9	0.032-0.075	50 (164)
TMS-CT-50M-1/8-OUT-2		ER9636-000	3.2	0.125	1.1-2.6	0.044-0.105	
TMS-CT-50M-3/16-OUT-2		ER9641-000	4.8	0.187	1.7-4.0	0.069-0.160	
TMS-CT-50M-1/4-OUT-2		ER9646-000	6.4	0.250	2.3-5.4	0.091-0.215	
TMS-CT-50M-3/8-OUT-2		ER9651-000	9.5	0.375	3.4-8.1	0.137-0.320	
TMS-CT-50M-1/2-OUT-2		ER9656-000	12.7	0.500	4.6-10.7	0.183-0.425	
TMS-CT-50M-3/4-OUT-2		ER9661-000	19.0	0.750	6.9-16.2	0.275-0.640	
TMS-CT-50M-1-OUT-2		ER9666-000	25.4	1.000	9.2-21.5	0.366-0.850	
 TMS-CT-50M-3/32-OUT-2L	Pink	ER9631-000	2.4	0.093	0.8-1.9	0.032-0.075	50 (164)
TMS-CT-50M-1/8-OUT-2L		ER9637-000	3.2	0.125	1.1-2.6	0.044-0.105	
TMS-CT-50M-3/16-OUT-2L		ER9642-000	4.8	0.187	1.7-4.0	0.069-0.160	
TMS-CT-50M-1/4-OUT-2L		ER9647-000	6.4	0.250	2.3-5.4	0.091-0.215	
TMS-CT-50M-3/8-OUT-2L		ER9652-000	9.5	0.375	3.4-8.1	0.137-0.320	
TMS-CT-50M-1/2-OUT-2L		ER9657-000	12.7	0.500	4.6-10.7	0.183-0.425	
TMS-CT-50M-3/4-OUT-2L		ER9662-000	19.0	0.750	6.9-16.2	0.275-0.640	
TMS-CT-50M-1-OUT-2L		ER9667-000	25.4	1.000	9.2-21.5	0.366-0.850	

Identification solutions

Printable continuous tubing

D-CT (Organic fluids, especially oils and diesel fuel resistant)

D-CT is the foremost fluid resistant product used in applications where exposure to lubricant and fuel spray is possible.

D-CT is a thin wall, heat shrink tube, manufactured with e-beam technology that gives users the ability to shrink the supplied tube with no damage to material or printed text. Shrinking the tube will ensure the printed mark has a firm hold on the wire.

D-CT gives market leading print performance when used as a complete system, as recommended by TE Connectivity.

- Identification printer product ribbon matrix for the recommended printer/product/ribbon combinations (refer to TE document 411-121005).
- Printed D-CT meets the rail specifications NF F 00608 Categories A & H and BS EN50343. The sleeve also meets the material requirements of SAE-AMSDTL- 23053/6 Class 1.
- D-CT Heat Shrink Identification Marker Sleeveing is available as part of a complete identification system. The system comprises specific printers, thermal transfer ribbons and WINTOTAL software.

FEATURES

- Self-extinguishing, non-flame propagating.
- Resistant to key rail, industrial and military fluids (defined by TE specifications RW-2519).
- Designed for rugged environments
- More open profile for easier use
- Military grade performance
- Pre-termination Cable Identification
- Sleeve diameters from 2.4 mm to 38.1 mm
- Shrink ratio 3:1 (except 38.1 which is 2:1)

BENEFITS

- Create identification labels for wire and cable harnesses in harsh environments with any TE Connectivity thermal transferable printers
- User flexibility to design custom length markers from 5 mm to 3 meters using TE WinTotal software
- Optimal reel length to maximize bulk printing and minimize storage space
- Reduce installation time with a more open profile
- Printable Continuous tube can be used as well as insulation and protection from mechanical abuse.

APPLICATIONS

- Railways
- Aerospace
- Marine

MATERIAL

- Irradiated, thermally stabilized, modified polyolefin compound



Temperature Rating

Operating Temperature range:
-75°C to 135°C

Specifications and Approvals

- EN45545-2 R23 HL1
- EN45545-2 R24 HL3
- NF F 00608 CAT A&H
- NFPA 130


Recommended Hardware and Software

- Printer: T2212, T3212, T3224, T6112DS
- Ribbon: 1966 Serie
- Software: WinTotal

For More information

- Technical Datasheet: TTDS-267
- Product Specification Sheet: RW-2519
- TT Printer accessories: TTDS-260

PART NUMBERING SYSTEM





Optimal print result on TE identification Continuous Tube products can be achieved by using the WINTOTAL software in conjunction with TE Printers and recommended TE Ribbon.

Identification solutions

Printable continuous tubing

D-CT

ORDERING INFORMATION

Description	Color	Part Number	Supplied diameter		Recommended use range (Min-Max)		Spool length Mt. (ft)	
			(mm)	(inches)	(mm)	(inches)		
 D-CT-50M-2.4-OUT-9	White <input type="checkbox"/>	EL8082-000	2.4	0.093	0.9-1.9	0.035-0.075	50 (164)	
D-CT-50M-3.2-OUT-9		EL8083-000	3.2	0.125	1.2-2.56	0.047-0.101		
D-CT-50M-4.8-OUT-9		EL8084-000	4.8	0.187	1.70-3.84	0.067-0.151		
D-CT-50M-6.4-OUT-9		EL8085-000	6.4	0.250	2.20-5.10	0.087-0.201		
D-CT-50M-9.5-OUT-9		EL8086-000	9.5	0.375	3.30-7.6	0.130-0.299		
D-CT-50M-12-OUT-9		EL8087-000	12.7	0.500	4.30-10.16	0.169-0.402		
D-CT-50M-18-OUT-9		EL8088-000	19.0	0.750	6.50-15.3	0.256-0.614		
D-CT-50M-25-OUT-9		EL8089-000	25.4	1.000	8.50-20.30	0.335-0.799		
D-CT-40M-38-OUT-9		EL8090-000	38.1	1.500	19.00-30.48	0.750-1.200		40 (131)
 D-CT-50M-2.4-OUT-4		Yellow <input type="checkbox"/>	EL8091-000	2.4	0.093	0.9-1.9		0.035-0.075
D-CT-50M-3.2-OUT-4	EL8092-000		3.2	0.125	1.2-2.56	0.047-0.101		
D-CT-50M-4.8-OUT-4	EL8093-000		4.8	0.187	1.70-3.84	0.067-0.151		
D-CT-50M-6.4-OUT-4	EL8094-000		6.4	0.250	2.20-5.10	0.087-0.201		
D-CT-50M-9.5-OUT-4	EL8095-000		9.5	0.375	3.30-7.6	0.130-0.299		
D-CT-50M-12-OUT-4	EL8096-000		12.7	0.500	4.30-10.16	0.169-0.402		
D-CT-50M-18-OUT-4	EL8105-000		19.0	0.750	6.50-15.3	0.256-0.614		
D-CT-50M-25-OUT-4	EL8106-000		25.4	1.000	8.50-20.30	0.335-0.799		
D-CT-40M-38-OUT-4	EL8097-000		38.1	1.500	19.00-30.48	0.750-1.200	40 (131)	

Identification solutions

Printable continuous tubing

HX-CT (Zero-halogen low fire hazard)

HX-CT is manufactured using a specially developed radiation cross-linked material. Formulated to give Low Fire Hazard properties, which allow this product to be used in locations where fire may pose a risk to human life and property.

HX-CT heat shrink tube, manufactured with e-beam technology that gives users the ability to shrink the supplied tube with no damage to material or printed text. Shrinking the tube will ensure the printed mark has a firm hold on the wire.

HX-CT gives market leading print performance when used as a complete system, as recommended by TE Connectivity.

- Identification printer product ribbon matrix for the recommended printer/product/ribbon combinations (refer to TE document 411-121005).
- Printed HX-CT meets the rail specifications EN45545-2 Fire Hazard Classification 3, in accordance with requirement set R22/R23—Unlimited use for rail car design.
- HX-CT Heat Shrink Identification Marker Sleeving is available as part of a complete identification system. The system comprises specific printers, thermal transfer ribbons and WINTOTAL software.

FEATURES

- Zero Halogen, Low Toxic Fumes and Low Smoke
- Self Extinguishing, non-flame propagating
- Excellent resistance to burning—Typical LOI 39%
- Resistant to key rail and industrial fluids (defined by TE specification RW-2072)
- Sleeve diameters from 2.4 mm to 38.1 mm (3/32 to 1-1/2inch)
- More open profile for easier use
- Shrink ratio 2:1

BENEFITS

- Create identification labels for wire and cable harnesses in harsh environments with any TE Connectivity thermal transferable printers
- User flexibility to design custom length markers from 5 mm to 3 meters using TE WinTotal software
- Optimal reel length to maximize bulk printing and minimize storage space
- Reduce installation time with a more open profile
- Printable Continuous tube can be used as well as insulation and protection from mechanical abuse
- Recommended for Automatic Harness assembly machine.

APPLICATIONS

- Mass transit
- Marine
- Aerospace
- Military
- Marine
- Industrial applications

MATERIAL

- low fire hazard (LFH), irradiated, thermally stabilized modified polyolefin compound



Temperature Rating

Operating Temperature range:
-55°C to 105°C

Specifications and Approvals

- EN45545-2 R22/R23/R24 HL3
- BS 6853 Vehicule CAT 1A,
- London underground 1-085,
- NF F 16-101 Classification A1,


Recommended Hardware and Software

- Printer: T2212, T3212, T3224, T6112DS
- Ribbon: 1966 Serie
- Software: WinTotal

For More information

- Technical Datasheet: TTDS-270
- Product Specification Sheet: RW-2072
- TT Printer accessories: TTDS-260


PART NUMBERING SYSTEM



Optimal print result on TE identification Continuous Tube products can be achieved by using the WINTOTAL software in conjunction with TE Printers and recommended TE Ribbon.

HX-CT

ORDERING INFORMATION

Description	Color	Part Number	Supplied diameter		Recommended use range (Min-Max)		Spool length Mt. (ft)	
			(mm)	(inches)	(mm)	(inches)		
 HX-CT-50M-2.4-OUT-9	White	EL8194-000	2.4	0.093	1.2-1.9	0.032-0.075	50 (164)	
HX-CT-50M-3.2-OUT-9		EL8195-000	3.2	0.125	1.7-2.6	0.069-0.105		
HX-CT-50M-4.8-OUT-9		EL8196-000	4.8	0.187	1.5-4.0	0.100-0.160		
HX-CT-50M-6.4-OUT-9		EL8197-000	6.4	0.250	3.8-5.4	0.150-0.215		
HX-CT-50M-9.5-OUT-9		EL8198-000	9.5	0.375	5.5-8.1	0.220-0.320		
HX-CT-50M-12.7-OUT-9		EL8199-000	12.7	0.500	6.9-10.7	0.260-0.449		
HX-CT-50M-19.0-OUT-9		EL8200-000	19.0	0.750	10.1-16.2	0.400-0.640		
HX-CT-40M-25.4-OUT-9		EL8201-000	25.4	1.000	14.2-21.5	0.563-0.850		40 (131)
HX-CT-40M-38.1-OUT-9		EL8202-000	38.1	1.500	20.9-33.0	0.825-1.300		
 HX-CT-50M-2.4-OUT-4	Yellow	EL8203-000	2.4	0.093	1.2-1.9	0.032-0.075	50 (164)	
HX-CT-50M-3.2-OUT-4		EL8204-000	3.2	0.125	1.7-2.6	0.069-0.105		
HX-CT-50M-4.8-OUT-4		EL8205-000	4.8	0.187	1.5-4.0	0.100-0.160		
HX-CT-50M-6.4-OUT-4		EL8206-000	6.4	0.250	3.8-5.4	0.150-0.215		
HX-CT-50M-9.5-OUT-4		EL8207-000	9.5	0.375	5.5-8.1	0.220-0.320		
HX-CT-50M-12.7-OUT-4		EL8208-000	12.7	0.500	6.9-10.7	0.260-0.449		
HX-CT-50M-19.0-OUT-4		EL8209-000	19.0	0.750	10.1-16.2	0.400-0.640		
HX-CT-40M-25.4-OUT-4		EL8210-000	25.4	1.000	14.2-21.5	0.563-0.850		40 (131)
HX-CT-40M-38.1-OUT-4		EL8211-000	38.1	1.500	20.9-33.0	0.825-1.300		
 HX-CT-50M-2.4-OUT-0	Black	ER4003-000	2.4	0.093	1.2-1.9	0.032-0.075	50 (164)	
HX-CT-50M-3.2-OUT-0		ER4004-000	3.2	0.125	1.7-2.6	0.069-0.105		
HX-CT-50M-4.8-OUT-0		ER4005-000	4.8	0.187	1.5-4.0	0.100-0.160		
HX-CT-50M-6.4-OUT-0		ER4006-000	6.4	0.250	3.8-5.4	0.150-0.215		
HX-CT-50M-9.5-OUT-0		ER4009-000	9.5	0.375	5.5-8.1	0.220-0.320		
HX-CT-50M-12.7-OUT-0		ER4010-000	12.7	0.500	6.9-10.7	0.260-0.449		
HX-CT-50M-19.0-OUT-0		ER4014-000	19.0	0.750	10.1-16.2	0.400-0.640		
HX-CT-40M-25.4-OUT-0		ER4015-000	25.4	1.000	14.2-21.5	0.563-0.850		40 (131)
HX-CT-40M-38.1-OUT-0		ER4016-000	38.1	1.500	20.9-33.0	0.825-1.300		
 HX-CT-50M-2.4-OUT-6	Blue	ES0265-000	2.4	0.093	1.2-1.9	0.032-0.075	50 (164)	
HX-CT-50M-3.2-OUT-6		ES0268-000	3.2	0.125	1.7-2.6	0.069-0.105		
HX-CT-50M-4.8-OUT-6		ES0271-000	4.8	0.187	1.5-4.0	0.100-0.160		
HX-CT-50M-6.4-OUT-6		ES0274-000	6.4	0.250	3.8-5.4	0.150-0.215		
HX-CT-50M-9.5-OUT-6		ES0277-000	9.5	0.375	5.5-8.1	0.220-0.320		
HX-CT-50M-12.7-OUT-6		ES0280-000	12.7	0.500	6.9-10.7	0.260-0.449		
HX-CT-50M-19.0-OUT-6		ES0283-000	19.0	0.750	10.1-16.2	0.400-0.640		
HX-CT-40M-25.4-OUT-6		ES0286-000	25.4	1.000	14.2-21.5	0.563-0.850		40 (131)
HX-CT-50M-2.4-OUT-5		ES0264-000	2.4	0.093	1.2-1.9	0.032-0.075		
 HX-CT-50M-3.2-OUT-5	Green	ES0267-000	3.2	0.125	1.7-2.6	0.069-0.105	50 (164)	
HX-CT-50M-4.8-OUT-5		ES0270-000	4.8	0.187	1.5-4.0	0.100-0.160		
HX-CT-50M-6.4-OUT-5		ES0273-000	6.4	0.250	3.8-5.4	0.150-0.215		
HX-CT-50M-9.5-OUT-5		ES0276-000	9.5	0.375	5.5-8.1	0.220-0.320		
HX-CT-50M-12.7-OUT-5		ES0279-000	12.7	0.500	6.9-10.7	0.260-0.449		
HX-CT-50M-19.0-OUT-5		ES0282-000	19.0	0.750	10.1-16.2	0.400-0.640		
HX-CT-40M-25.4-OUT-5		ES0285-000	25.4	1.000	14.2-21.5	0.563-0.850		40 (131)
HX-CT-50M-2.4-OUT-2		ES0263-000	2.4	0.093	1.2-1.9	0.032-0.075		
 HX-CT-50M-3.2-OUT-2		Red	ES0266-000	3.2	0.125	1.7-2.6		0.069-0.105
HX-CT-50M-4.8-OUT-2	ES0269-000		4.8	0.187	1.5-4.0	0.100-0.160		
HX-CT-50M-6.4-OUT-2	ES0272-000		6.4	0.250	3.8-5.4	0.150-0.215		
HX-CT-50M-9.5-OUT-2	ES0275-000		9.5	0.375	5.5-8.1	0.220-0.320		
HX-CT-50M-12.7-OUT-2	ES0278-000		12.7	0.500	6.9-10.7	0.260-0.449		
HX-CT-50M-19.0-OUT-2	ES0281-000		19.0	0.750	10.1-16.2	0.400-0.640		
HX-CT-40M-25.4-OUT-2	ES0284-000		25.4	1.000	14.2-21.5	0.563-0.850	40 (131)	

Identification solutions

Printable continuous tubing

ZHD-CT (Zero-halogen low fire hazard and fluid resistant)

ZHD-CT Zero Halogen and Diesel resistant marker sleeve for identification of wires and cables, presented as a continuous tube.

ZHD-CT is manufactured using a specially developed radiation cross linked material. Formulated to give Zero Halogen properties with the added benefit of diesel resistance, specifically designed to bridge the gap for installations where the highest performance is demanded from an Identification sleeve, without compromising on safety or capability.

ZHD-CT gives market leading print performance when used as a complete system, as recommended by TE Connectivity.

- Identification printer product ribbon matrix for the recommended printer/product/ribbon combinations (refer to TE document 411-121005).
- Printed ZHD-CT meets the rail specification EN45545-2 Fire Hazard Classification 1 and 2 in accordance with requirements set R22/R23.
- ZHD-CT Heat Shrink Identification Marker Sleeveing is available as part of a complete identification system. The system comprises specific printers, thermal transfer ribbons and WINTOTAL software.

FEATURES

- Zero Halogen, Low Toxic Fumes and Low Smoke
- Self Extinguishing, non-flame propagating
- Resistant to key rail and industrial fluids (defined by TE specification RW-2536)
- Sleeve diameters from 2.4 mm to 38.1 mm
- Shrink ratio 2:1

BENEFITS

- Create identification labels for wire and cable harnesses in harsh environments with any TE Connectivity thermal transferable printers
- User flexibility to design custom length markers from 5 mm to 3 meters using TE WinTotal software
- Optimal reel length to maximize bulk printing and minimize storage space
- Reduce installation time with a more open profile
- Printable Continuous tube can be used as well as insulation and protection from mechanical abuse.

APPLICATIONS

- Rail
- Marine
- Motorsports
- Industrial

MATERIAL

- Low fire hazard (LFH), irradiated, thermally stabilized modified polyolefin compound



Temperature Rating

Operating Temperature range:
-55°C to 125°C

Specifications and Approvals

- EN45545-2 R22 HL2,
- NFPA 130,
- BS 6853 CAT II,
- EN 50343,


Recommended Hardware and Software

- Printer: T2212, T3212, T3224, T6112DS
- Ribbon: 1966 Serie
- Software: WinTotal

For More information

- Technical Datasheet: TTDS-273
- Product Specification Sheet: RW-2536
- TT Printer accessories: TTDS-260

PART NUMBERING SYSTEM





Optimal print result on TE identification Continuous Tube products can be achieved by using the WINTOTAL software in conjunction with TE Printers and recommended TE Ribbon.

Identification solutions

Printable continuous tubing

ZHD-CT

ORDERING INFORMATION

Description	Color	Part Number	Supplied diameter		Recommended use range (Min-Max)		Spool length Mt. (ft)	
			(mm)	(inches)	(mm)	(inches)		
 ZHD-CT-50M-2.4-OUT-9	White <input type="checkbox"/>	EL8111-000	2.4	0.093	1.27-1.9	0.047-0.075	50 (164)	
ZHD-CT-50M-3.2-OUT-9		EL8112-000	3.2	0.125	1.77-2.56	0.067-0.101		
ZHD-CT-50M-4.8-OUT-9		EL8113-000	4.8	0.187	2.54-4.06	0.098-0.151		
ZHD-CT-50M-6.4-OUT-9		EL8114-000	6.4	0.250	3.81-5.46	0.130-0.201		
ZHD-CT-50M-9.5-OUT-9		EL8115-000	9.5	0.375	5.23-8.12	0.193-0.299		
ZHD-CT-50M-12.7-OUT-9		EL8116-000	12.7	0.500	6.99-10.08	0.256-0.402		
ZHD-CT-50M-19.0-OUT-9		EL8117-000	19.0	0.750	10.2-16.3	0.378-0.602		
ZHD-CT-40M-25.4-OUT-9		EL8118-000	25.4	1.000	14.3-21.6	0.504-0.799		40 (131)
ZHD-CT-40M-38.1-OUT-9		EL8119-000	38.1	1.500	21.0-33.0	0.756-1.200		
 ZHD-CT-50M-2.4-OUT-4	Yellow <input type="checkbox"/>	EL8120-000	2.4	0.093	1.27-1.9	0.047-0.075	50 (164)	
ZHD-CT-50M-3.2-OUT-4		EL8121-000	3.2	0.125	1.77-2.56	0.067-0.101		
ZHD-CT-50M-4.8-OUT-4		EL8122-000	4.8	0.187	2.54-4.06	0.098-0.151		
ZHD-CT-50M-6.4-OUT-4		EL8123-000	6.4	0.250	3.81-5.46	0.130-0.201		
ZHD-CT-50M-9.5-OUT-4		EL8124-000	9.5	0.375	5.23-8.12	0.193-0.299		
ZHD-CT-50M-12.7-OUT-4		EL8125-000	12.7	0.500	6.99-10.08	0.256-0.402		
ZHD-CT-50M-19.0-OUT-4		EL8126-000	19.0	0.750	10.2-16.3	0.378-0.602		
ZHD-CT-40M-25.4-OUT-4		EL8127-000	25.4	1.000	14.3-21.6	0.504-0.799		39 (131)
ZHD-CT-40M-38.1-OUT-4		EL8128-000	38.1	1.500	21.0-33.0	0.756-1.200		

Identification solutions

Printable continuous tubing

HT-CT (High temperature and highly flame retardant)

HT-CT is manufactured using a specially developed radiation cross-linked material. Formulated to give high temperature performance and low outgassing; this product has an operating temperature up to 225°C (437°F) suitable for many military and aerospace applications.

Thin walled HT-CT heat shrink tube, manufactured with e-beam technology gives users the ability to shrink the supplied tube with no damage to material or printed text. Shrinking the tube will ensure the printed marker has a firm hold on the wire.

HT-CT gives market leading print performance when used as a complete system, as recommended by TE Connectivity.

- Identification printer product ribbon matrix for the recommended printer/product/ribbon combinations (refer to TE document 411-121005).
- HT-CT Heat Shrink Identification Marker Sleeveing is available as part of a complete identification system. The system comprises specific printers, thermal transfer ribbons and WINTOTAL software.

FEATURES

- High Temperature
- Excellent chemical resistance
- Flame retarded, Self Extinguishing, UL VW-1 rated
- Resistant to key Aerospace, Military, Rail and Industrial fluids (defined by TE specification RW-2512)
- Sleeve diameters from 3/32 to 1-1/2inch (2.4 mm to 38.1 mm)
- Shrink ratio 2:1 (3/32 is 3:1)
- More open profile for easier use

BENEFITS

- Create identification labels for wire and cable harnesses in harsh environments with any TE Connectivity thermal transferable printers
- User flexibility to design custom length markers from 5 mm to 3 meters using TE WinTotal software
- Optimal reel length to maximize bulk printing and minimize storage space
- Reduce installation time with a more open profile
- Printable Continuous tube can be used as well as insulation and protection from mechanical abuse.

APPLICATIONS

High temperature environment

Where extreme resistance to fuels, lubricants and cleaning solvents is require as much as:

- Aerospace
- Military
- Industrial
- Semi-conductors, etc.

MATERIAL

- Heat-shrinkable fluoropolymer tubing polyolefin compound



Temperature Rating

Operating Temperature range:
-55°C to 225°C

Specifications and Approvals

- EN45545-2 R24 HL3,
- SAE-AS4952,
- MIL-STD-202 Method 215,


Recommended Hardware and Software

- Printer: T2212, T3212, T3224, T6112DS
- Ribbon: TMS-RJS Serie
- Software: WinTotal

For More information

- Technical Datasheet: TTDS-271
- Product Specification Sheet: RW-2512
- TT Printer accessories: TTDS-260

PART NUMBERING SYSTEM








Optimal print result on TE identification Continuous Tube products can be achieved by using the WINTOTAL software in conjunction with TE Printers and recommended TE Ribbon.

Identification solutions

Printable continuous tubing

HT-CT

ORDERING INFORMATION



Description	Color	Part Number	Supplied diameter		Recommended use range (Min-Max)		Spool length Mt. (ft)
			(mm)	(inches)	(mm)	(inches)	
 HT-CT-50M-3/32-OUT-9	White	EL7354-000	2.4	0.093	0.8-1.9	0.032-0.075	50 (164)
HT-CT-50M-1/8-OUT-9		EL7355-000	3.2	0.125	1.7-2.6	0.069-0.105	
HT-CT-50M-3/16-OUT-9		EL7356-000	4.8	0.187	2.5-4.0	0.100-0.160	
HT-CT-50M-1/4-OUT-9		EL7357-000	6.4	0.250	3.4-6.0	0.134-0.236	
HT-CT-50M-3/8-OUT-9		EL7358-000	9.5	0.375	5.3-8.1	0.209-0.319	
HT-CT-50M-1/2-OUT-9		EL7359-000	12.7	0.500	6.7-11.4	0.260-0.449	
HT-CT-50M-3/4-OUT-9		EL7360-000	19.0	0.750	9.9-15.3	0.390-0.602	
HT-CT-50M-1-OUT-9		EL8553-000	25.4	1.000	13.3-23	0.524-0.906	
HT-CT-50M-1/2-OUT-9		EL8554-000	38.1	1.500	20.9-34.0	0.825-1.339	
 HT-CT-50M-3/32-OUT-4	Yellow	EL8070-000	2.4	0.093	0.8-1.9	0.032-0.075	50 (164)
HT-CT-50M-1/8-OUT-4		EL8071-000	3.2	0.125	1.7-2.6	0.069-0.105	
HT-CT-50M-3/16-OUT-4		EL8072-000	4.8	0.187	2.5-4.0	0.100-0.160	
HT-CT-50M-1/4-OUT-4		EL8073-000	6.4	0.250	3.4-6.0	0.134-0.236	
HT-CT-50M-3/8-OUT-4		EL8074-000	9.5	0.375	5.3-8.1	0.209-0.319	
HT-CT-50M-1/2-OUT-4		EL8075-000	12.7	0.500	6.7-11.4	0.260-0.449	
HT-CT-50M-3/4-OUT-4		EL8076-000	19.0	0.750	9.9-15.3	0.390-0.602	
HT-CT-50M-1-OUT-4		EL8551-000	25.4	1.000	13.3-23	0.524-0.906	
HT-CT-50M-1/2-OUT-4		EL8555-000	38.1	1.500	20.9-34.0	0.825-1.339	
 HT-CT-50M-3/32-OUT-0	Black	ER2139-000	2.4	0.093	0.8-1.9	0.032-0.075	50 (164)
HT-CT-50M-1/8-OUT-0		ER2140-000	3.2	0.125	1.7-2.6	0.069-0.105	
HT-CT-50M-3/16-OUT-0		ER2141-000	4.8	0.187	2.5-4.0	0.100-0.160	
HT-CT-50M-1/4-OUT-0		ER2142-000	6.4	0.250	3.4-6.0	0.134-0.236	
HT-CT-50M-3/8-OUT-0		ER2143-000	9.5	0.375	5.3-8.1	0.209-0.319	
HT-CT-50M-1/2-OUT-0		ER2144-000	12.7	0.500	6.7-11.4	0.260-0.449	
HT-CT-50M-3/4-OUT-0		ER2145-000	19.0	0.750	9.9-15.3	0.390-0.602	
HT-CT-50M-1-OUT-0		ER2146-000	25.4	1.000	13.3-23	0.524-0.906	
HT-CT-50M-1/2-OUT-0		ER2147-000	38.1	1.500	20.9-34.0	0.825-1.339	
 HT-CT-50M-3/32-OUT-3	Orange	ES3448-000	2.4	0.093	1.2-1.9	0.032-0.075	50 (164)
HT-CT-50M-1/8-OUT-3		ER7299-000	3.2	0.125	1.7-2.6	0.069-0.105	
HT-CT-50M-3/16-OUT-3		ER7544-000	4.8	0.187	1.5-4.0	0.100-0.160	
HT-CT-50M-1/4-OUT-3		ER7543-000	6.4	0.250	3.8-5.4	0.150-0.215	
HT-CT-50M-3/8-OUT-3		ER7542-000	9.5	0.375	5.5-8.1	0.220-0.320	
HT-CT-50M-1/2-OUT-3		ER7541-000	12.7	0.500	6.9-10.7	0.260-0.449	
HT-CT-50M-3/4-OUT-3		ER7304-000	19.0	0.750	10.1-16.2	0.400-0.640	
HT-CT-50M-1-OUT-3		ER7540-000	25.4	1.000	14.2-21.5	0.563-0.850	
 HT-CT-50M-3/32-OUT-6		Blue	ES1485-000	2.4	0.093	0.8-1.9	
HT-CT-50M-1/8-OUT-6	ES1486-000		3.2	0.125	1.7-2.6	0.069-0.105	
HT-CT-50M-3/16-OUT-6	ES1487-000		4.8	0.187	2.5-4.0	0.100-0.160	
HT-CT-50M-1/4-OUT-6	ES1488-000		6.4	0.250	3.4-6.0	0.134-0.236	
HT-CT-50M-3/8-OUT-6	ES1489-000		9.5	0.375	5.3-8.1	0.209-0.319	
HT-CT-50M-1/2-OUT-6	ES1490-000		12.7	0.500	6.7-11.4	0.260-0.449	
HT-CT-50M-3/4-OUT-6	ES1491-000		19.0	0.750	9.9-15.3	0.390-0.602	
HT-CT-50M-1-OUT-6	ES1492-000		25.4	1.000	13.3-23	0.524-0.906	
 HT-CT-50M-3/32-OUT-5	Green		ES1477-000	2.4	0.093	1.2-1.9	0.032-0.075
HT-CT-50M-1/8-OUT-5		ES1478-000	3.2	0.125	1.7-2.6	0.069-0.105	
HT-CT-50M-3/16-OUT-5		ES1479-000	4.8	0.187	1.5-4.0	0.100-0.160	
HT-CT-50M-1/4-OUT-5		ES1480-000	6.4	0.250	3.8-5.4	0.150-0.215	
HT-CT-50M-3/8-OUT-5		ES1481-000	9.5	0.375	5.5-8.1	0.220-0.320	
HT-CT-50M-1/2-OUT-5		ES1482-000	12.7	0.500	6.9-10.7	0.260-0.449	
HT-CT-50M-3/4-OUT-5		ES1483-000	19.0	0.750	10.1-16.2	0.400-0.640	
HT-CT-50M-1-OUT-5		ES1484-000	25.4	1.000	14.2-21.5	0.563-0.850	

Identification solutions

Printable continuous tubing

HT-CT

ORDERING INFORMATION

Description	Color	Part Number	Supplied diameter		Recommended use range (Min-Max)		Spool length Mt. (ft)
			(mm)	(inches)	(mm)	(inches)	
 HT-CT-50M-3/32-OUT-2	Red	ES1457-000	2.4	0.093	1.2-1.9	0.032-0.075	50 (164)
HT-CT-50M-1/8-OUT-2		ES1459-000	3.2	0.125	1.7-2.6	0.069-0.105	
HT-CT-50M-3/16-OUT-2		ES1461-000	4.8	0.187	1.5-4.0	0.100-0.160	
HT-CT-50M-1/4-OUT-2		ES1463-000	6.4	0.250	3.8-5.4	0.150-0.215	
HT-CT-50M-3/8-OUT-2		ES1465-000	9.5	0.375	5.5-8.1	0.220-0.320	
HT-CT-50M-1/2-OUT-2		ES1466-000	12.7	0.500	6.9-10.7	0.260-0.449	
HT-CT-50M-3/4-OUT-2		ES1467-000	19.0	0.750	10.1-16.2	0.400-0.640	
HT-CT-50M-1-OUT-2		ES1468-000	25.4	1.000	14.2-21.5	0.563-0.850	
 HT-CT-50M-3/32-OUT-2L	Pink	ES1469-000	2.4	0.093	1.2-1.9	0.032-0.075	50 (164)
HT-CT-50M-1/8-OUT-2L		ES1470-000	3.2	0.125	1.7-2.6	0.069-0.105	
HT-CT-50M-3/16-OUT-2L		ES1471-000	4.8	0.187	1.5-4.0	0.100-0.160	
HT-CT-50M-1/4-OUT-2L		ES1472-000	6.4	0.250	3.8-5.4	0.150-0.215	
HT-CT-50M-3/8-OUT-2L		ES1473-000	9.5	0.375	5.5-8.1	0.220-0.320	
HT-CT-50M-1/2-OUT-2L		ES1474-000	12.7	0.500	6.9-10.7	0.260-0.449	
HT-CT-50M-3/4-OUT-2L		ES1475-000	19.0	0.750	10.1-16.2	0.400-0.640	
HT-CT-50M-1-OUT-2L		ES1476-000	25.4	1.000	14.2-21.5	0.563-0.850	

Index

Part Number	Page	Part Number	Page	Part Number	Page
EL		EL8086-000	13	ER	
EL7354-000	19	EL8087-000	13	ER2140-000	19
EL7355-000	19	EL8088-000	13	ER2141-000	19
EL7356-000	19	EL8089-000	13	ER2142-000	19
EL7357-000	19	EL8090-000	13	ER2143-000	19
EL7358-000	19	EL8091-000	13	ER2144-000	19
EL7359-000	19	EL8092-000	13	ER2145-000	19
EL7360-000	19	EL8093-000	13	ER2146-000	19
EL7583-000	7	EL8094-000	13	ER2147-000	19
EL7584-000	7	EL8095-000	13	ER2148-000	10
EL7585-000	7	EL8096-000	13	ER2149-000	10
EL7586-000	7	EL8097-000	13	ER2150-000	10
EL7587-000	7	EL8105-000	13	ER2151-000	10
EL7588-000	7	EL8106-000	13	ER2152-000	10
EL7589-000	7	EL8111-000	17	ER2153-000	10
EL7590-000	7	EL8112-000	17	ER2154-000	10
EL7597-000	7	EL8113-000	17	ER2155-000	10
EL7598-000	7	EL8114-000	17	ER2156-000	10
EL7599-000	7	EL8115-000	17	ER2157-000	10
EL7600-000	7	EL8116-000	17	ER2164-000	7
EL7601-000	7	EL8117-000	17	ER2165-000	7
EL7602-000	7	EL8118-000	17	ER2166-000	7
EL7603-000	7	EL8119-000	17	ER2167-000	7
EL7604-000	7	EL8120-000	17	ER2168-000	7
EL7643-000	10	EL8121-000	17	ER2169-000	7
EL7644-000	10	EL8122-000	17	ER2170-000	7
EL7645-000	10	EL8123-000	17	ER2171-000	7
EL7646-000	10	EL8124-000	17	ER4003-000	15
EL7647-000	10	EL8125-000	17	ER4004-000	15
EL7648-000	10	EL8126-000	17	ER4005-000	15
EL7649-000	10	EL8127-000	17	ER4006-000	15
EL7650-000	10	EL8128-000	17	ER4009-000	15
EL7651-000	10	EL8194-000	15	ER4010-000	15
EL7652-000	10	EL8195-000	15	ER4014-000	15
EL7660-000	10	EL8196-000	15	ER4015-000	15
EL7661-000	10	EL8197-000	15	ER4016-000	15
EL7662-000	10	EL8198-000	15	ER7299-000	19
EL7663-000	10	EL8199-000	15	ER7304-000	19
EL7664-000	10	EL8200-000	15	ER7540-000	19
EL7665-000	10	EL8201-000	15	ER7541-000	19
EL7666-000	10	EL8202-000	15	ER7542-000	19
EL7667-000	10	EL8203-000	15	ER7543-000	19
EL7668-000	10	EL8204-000	15	ER7544-000	19
EL7669-000	10	EL8205-000	15	ER9612-000	7
EL8070-000	19	EL8206-000	15	ER9613-000	7
EL8071-000	19	EL8207-000	15	ER9614-000	7
EL8072-000	19	EL8208-000	15	ER9615-000	7
EL8073-000	19	EL8209-000	15	ER9616-000	7
EL8074-000	19	EL8210-000	15	ER9617-000	7
EL8075-000	19	EL8211-000	15	ER9618-000	7
EL8076-000	19	EL8551-000	19	ER9619-000	7
EL8082-000	13	EL8553-000	19	ER9620-000	7
EL8083-000	13	EL8554-000	19	ER9621-000	7
EL8084-000	13	EL8555-000	19	ER9622-000	7
EL8085-000	13	ER2139-000	19	ER9623-000	7

Index

Part Number	Page	Part Number	Page	Part Number	Page
ER9624-000	7	ES		ES1491-000	19
ER9625-000	7	ES0263-000	15	ES1492-000	19
ER9626-000	7	ES0264-000	15	ES3448-000	19
ER9627-000	7	ES0265-000	15		
ER9628-000	7	ES0266-000	15		
ER9629-000	7	ES0267-000	15		
ER9630-000	11	ES0268-000	15		
ER9631-000	11	ES0269-000	15		
ER9633-000	10	ES0270-000	15		
ER9634-000	10	ES0271-000	15		
ER9635-000	10	ES0272-000	15		
ER9636-000	11	ES0273-000	15		
ER9637-000	11	ES0274-000	15		
ER9638-000	10	ES0275-000	15		
ER9639-000	10	ES0276-000	15		
ER9640-000	10	ES0277-000	15		
ER9641-000	11	ES0278-000	15		
ER9642-000	11	ES0279-000	15		
ER9643-000	10	ES0280-000	15		
ER9644-000	10	ES0281-000	15		
ER9645-000	10	ES0282-000	15		
ER9646-000	11	ES0283-000	15		
ER9647-000	11	ES0284-000	15		
ER9648-000	10	ES0285-000	15		
ER9649-000	10	ES0286-000	15		
ER9650-000	10	ES1457-000	20		
ER9651-000	11	ES1459-000	20		
ER9652-000	11	ES1461-000	20		
ER9653-000	10	ES1463-000	20		
ER9654-000	10	ES1465-000	20		
ER9655-000	10	ES1466-000	20		
ER9656-000	11	ES1467-000	20		
ER9657-000	11	ES1468-000	20		
ER9658-000	10	ES1469-000	20		
ER9659-000	10	ES1470-000	20		
ER9660-000	10	ES1471-000	20		
ER9661-000	11	ES1472-000	20		
ER9662-000	11	ES1473-000	20		
ER9663-000	10	ES1474-000	20		
ER9664-000	10	ES1475-000	20		
ER9665-000	10	ES1476-000	20		
ER9666-000	11	ES1477-000	19		
ER9667-000	11	ES1478-000	19		
ER9668-000	10	ES1479-000	19		
ER9669-000	10	ES1480-000	19		
ER9670-000	10	ES1481-000	19		
		ES1482-000	19		
		ES1483-000	19		
		ES1484-000	19		
		ES1485-000	19		
		ES1486-000	19		
		ES1487-000	19		
		ES1488-000	19		
		ES1489-000	19		
		ES1490-000	19		

CONNECT WITH US

We make it easy to connect with our experts and are ready to provide all the support you need.

Visit www.te.com/support to chat with a Product Information Specialist.

Asia: +86 400-820-6015 - Europe, Middle East, & Africa: +49 6251-133-0 - North America: +1-888-441-9982

te.com

© 2023 TE Connectivity. All Rights Reserved.

TE Connectivity, TE connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

INDUSTRIAL / PRINTABLE CONTINUOUS TUBING / CATALOG / EN

04/23

CATALOG

TE Connectivity

3, rue Jean Perrin
69687 Chassieu cedex
France

Tel: +33 481923100