# CERTIFICATE OF COMPLIANCE

Certificate Number UL-US-L28476-1125-51709002-3

**Report Reference** E28476-20090715

**Date** 6-Mar-2023

Issued to: TYCO Electronics Corp

2901 Fulling Mill Rd Middletown, PA 17057

**United States** 

This is to certify that representative samples of

ECBT2 - Connectors for Use in Data, Signal, Control and

Power Applications - Component

See Addendum Page for Product Designation(s).

Have been evaluated by UL in accordance with the component requirements in the Standard(s) indicated on this Certificate. UL Recognized components are incomplete

in certain constructional features or restricted in

performance capabilities and are intended for installation in complete equipment submitted for investigation to UL LLC.

Standard(s) for Safety: UL 1977, Edition 4, Issue Date 2022-12-07

Additional Information: See the UL Online Certifications Directory at

https://iq.ulprospector.com for additional information

This Certificate of Compliance indicates that representative samples of the product described in the certification report have met the requirements for UL certification. It does not provide authorization to apply the UL Recognized Component Mark. Only the Authorization Page that references the Follow-Up Services Procedure for ongoing surveillance provides authorization to apply the UL Mark.

Only those products bearing the UL Recognized Component Mark should be considered as being UL Certified and covered under UL's Follow-Up Services.

Look for the UL Recognized Component Mark on the product.

Deborah Jennings-Conner, VP Regulatory Services

UL LLC



# CERTIFICATE OF COMPLIANCE

Certificate Number UL-US-L28476-1125-51709002-3

**Report Reference** E28476-20090715

**Date** 6-Mar-2023

This is to certify that representative samples of the product as specified on this certificate were tested according to the current UL requirements

Model	Category Description		
DRC10-24PX-XXXX	Connectors		
DRC10-40P-XXXX	Connectors		
DRC12-24PXZ-XXXX	Connectors		
DRC12-40PXZ-XXXX	Connectors		
DRC12-70PXZ-XXXX	Connectors		
DRC13-24PX-XXXX	Connectors		
DRC13-40PX-XXXX	Connectors		
DRC14-24PXZ-XXXX	Connectors		
DRC14-40PXZ-XXXX	Connectors		
DRC14-70PXZ-XXXX	Connectors		
DRC16-24SXZ-XXXX	Connectors		
DRC16-40SZ-XXXX	Connectors		
DRC16-70SXZ-XXXX	Connectors		
DRC18-40SXZ-XXXX	Connectors		
DRC20-50PX-XXXX	Connectors		
DRC20-60PX-XXXX	Connectors		
DRC20-75PXX-XXXX	Connectors		
DRC22-40PX-XXXX	Connectors		
DRC22-50PX-XXXX	Connectors		
DRC23-24PX-XXXX	Connectors		
DRC23-40PX-XXXX	Connectors		
DRC23-64PX-XXXX	Connectors		
DRC23-80P	Connectors		
DRC26-24SX-XXXX	Connectors		
DRC26-38SX-XXXX	Connectors		
DRC26-40SX-XXXX	Connectors		
DRC26-50SX-XXXX	Connectors		
DRC26-60SX-XXXX	Connectors		

Webrah Jennings-Corner, VP Regulatory Services



File E28476 Service Request: 1181364

July 15, 2009

REPORT

on

COMPONENT - Connectors for Use in Data, Signal, Control and Power Applications

TYCO ELECTRONICS CORP MIDDLETOWN, PA

Copyright © 2009 Underwriters Laboratories Inc.

Underwriters Laboratories Inc. authorizes the above named company to reproduce this Report provided it is in its entirety.

Underwriters Laboratories Inc. authorizes the above named company to reproduce the latest pages of that portion of this Report consisting of this Cover Page through Page 5.

File E28476 Vol. 125 Sec. 3 Page 1 Issued: 2009-07-15 and Report Revised: 2023-02-27

DESCRIPTION

PRODUCT COVERED:

USR Component Connectors, Series DRC1, DRC18, DRC26.

\* Cat Nos. DRC10-24PX-XXXX, DRC10-40P-XXXX, DRC12-24PXZ-XXXX, DRC12-40PXZ-XXXX, DRC12-70PXZ-XXXX, DRC13-24PX-XXXX, DRC13-40PX-XXXX, DRC14-24PXZ-XXXX, DRC14-40PXZ-XXXX, DRC14-70PXZ-XXXX, DRC16-24SXZ-XXXX, DRC16-40SZ-XXXX, DRC16-70SXZ-XXXX, DRC18-40SXZ-XXXX, DRC20-50PX-XXXX, DRC20-60PX-XXXX, DRC20-75PXX-XXXX, DRC22-40PX-XXXX, DRC22-50PX-XXXX, DRC23-24PX-XXXX \*DRC23-40PX-XXXX, DRC23-64PX-XXXX, DRC23-80P, DRC26-24SX-XXXX, DRC26-38SX-XXXX, DRC26-40SX-XXXX, DRC26-50SX-XXXX, DRC26-60SX-XXXX.

Refer to Nomenclature portion of report for Cat. Nos. GENERAL:

These devices are multi-pole connectors intended for factory assembly on stranded copper conductors where the acceptability of combinations is determined by Underwriters Laboratories Inc. The devices are identified as follows:

\* USR indicates investigation to United States Standards referenced in the Test Records.

RATING:

No current or voltage

Flammability -

Disconnecting Use - see Sec Gen for required marking

File E28476 Vol. 125 Sec. 3 Page 2 Issued: 2009-07-15 and Report Revised: 2023-02-27

#### NOMENCLATURE:

\* DRC 1 4 - 40 P **X Z** - XXXX I II III IV V VI VII VIII

- I. Designates Deutsch Rectangular Connector Bulk Packaged without Contacts or Accessories.
- II. Indicates Contact Type
  - 1 = Accepts Size 16 Terminals
  - 2 = Accepts Size 20 Terminals
- III. Indicates Connector Style
- \* 0 = 180° Receptacle PCB Termination
  - 2 = Receptacle Flange Mount
- \* 3 = 90° Receptacle PCB Termination
  - 4 = Receptacle Inline

\*

- 6 = Plug
- 8 = Keyed Plug 40 Pin Size 16 Only
- IV. Indicates Shell Size and Insert Layout
  - 24 = 24 pole
  - 38 = 38 poles
  - 40 = 40 pole
  - 50 = 50 poles
  - 60 = 60 poles
  - 70 = 70 pole
  - 75 = 75 poles
  - 76 = 76 poles
  - 80 = 80 poles
  - V. Indicates Contact Style
- \* S = Socket (Plug)
- \* P = Pin (Receptacle)
- \* VI. Keying Position

Blank = No Key

A, B, C, D or 01 through 10

\*

VII. Wire Seals

- \* Blank = **Normal** Wire Insulation Seal
- \* T = Thin Wall Wire Insulation Seal
- \* E = Extra Thin Wire Insulation Wall Seal

VIII. Special Modifications

File E28476 Vol. 125 Sec. 3 Page 3 Issued: 2009-07-15 and Report Revised: 2010-12-09

### TECHNICAL CONSIDERATIONS (NOT FOR FIELD REPRESENTATIVE'S USE):

Use - For use only in or with complete equipment where the acceptability of the combination is determined by Underwriters Laboratories Inc.

Conditions of Acceptability - The following are among the considerations to be made when evaluating the device in the end-use product.

# Interruption of Current

1. These devices are not suitable for interrupting the flow of current by connecting or disconnecting the mating connector.

### Current-Carrying Capability and Current Ratings

2. These devices have not been subjected to the Temperature test and as a result do not have an assigned current rating. The device's current carrying capability is to be reviewed in the end-use by measuring temperatures on the connector housing and/or terminals when current is flowing through the connector under conditions of normal use.

## Insulating Materials

\*

\*3. These devices employ insulating materials with properties as tabulated below at the minimum thickness employed in the connector housing, the suitability of the insulating materials based on the documented values shall be determined in the end-use application. Please note the values specified in the table when multiple materials are indicated represent the minimum values for the group of materials.

File E28476 Vol. 125 Sec. 3 Page 4 Issued: 2009-07-15 and Report Revised: 2023-02-27

Part	TE RM # Insulating Material #	Manufacture	Min Thicknes s (mm)	Flam e Clas s	HWI	HA I	RTI Elec	Max Operating Temp °C
Plug/Rcp t Housing Size 16	TE Proprietary	TE Proprietary	1.78	v-0	4	1	130	125
	TE Proprietary	TE Proprietary	1.78	V-0	-	-	130	125
Plug/Rcp t Housing Size 20	TE Proprietary	TE Proprietary	1.40	v-0	4	1	130	125
	TE Proprietary	TE Proprietary	1.40	v-0	0	0	140	125
	TE Proprietary	TE Proprietary	1.40	v-0	-	-	130	125
Header Housing Size 16	TE Proprietary	TE Proprietary	1.27	v-0	4	1	130	125
	TE Proprietary	TE Proprietary	1.27	V-0	-	-	130	125
Header Housing Size 20	TE Proprietary	TE Proprietary	1.02	v-0	4	1	130	125
	TE Proprietary	TE Proprietary	1.02	v-0	0	0	140	125
	TE Proprietary	TE Proprietary	1.02	v-0	-	-	130	125
Retainer Size 16	TE Proprietary	TE Proprietary	1.14	v-0	2	4	170	125
	TE Proprietary	TE Proprietary	1.14	НВ	3	0		65
	TE Proprietary	TE Proprietary	1.14	v-0	0	0	140	125
Retainer Size 20	TE Proprietary	TE Proprietary	0.98	V-0	2	4	170	125

File E28476 Vol. 125 Sec. 3 Page 4A Issued: 2009-07-15 and Report Revised: 2023-02-27

Note:

(#) - Code for Insulating Body Material.

A. TE RM No. TE Proprietary

Color: Black

- 1. Dielectric strength (kV/mm): 17
- 2. CTI: 4
- B. TE RM No. TE Proprietary

Color: Black

- 1. Dielectric strength (kV/mm): 32
- 2. CTI: 4
- C. TE RM No. TE Proprietary
  - 1. Dielectric strength (kV/mm):--
  - 2. CTI: --
- D. TE RM No. TE Proprietary

Color: Black

- 1. Dielectric strength (kV/mm): 23
- 2. CTI: 2
- \*E. TE RM No. TE Proprietary

Color: Black

- 1. Dielectric Strength (kV/mm): -
- 2. CTI: 4
- 4. The Maximum Operating Temperature of these devices should not exceed the temperature ratings of the insulating materials. These materials may be used interchangeably at a maximum temperature of  $65^{\circ}$ C for the Size 16 Connectors and  $125^{\circ}$ C for the Size 20 Connectors.
- 5. These devices have been evaluated for a 20 mm Flame Test per applicant request. The suitability of the insulating materials shall be determined in the end-use application. Devices employing housings molded from Stanyl TE250F6 have not been subjected to the 20 mm Flame Test.

File E28476 Vol. 125 Sec. 3 Page 5 Issued: 2009-07-15 and Report Revised: 2023-02-27

# Terminations

7. The following crimp contacts have been evaluated for the wire sizes as tabulated below:

Stamped and Formed Type -

Pin/Contact	Contact Size	Wire Size, AWG	Force, lbf
1060-12-0166 / 1062-12-0166	12	12, 14	20
1000 12 0100 / 1002 12 0100		12, 11	20
1060-12-0222 / 1062-12-0222	12	10	20
1060-14-0122 / 1062-14-0122	16	14 - 18	20
1060-16-0122 / 1062-16-0122	16	14 - 18	20
1000 10 0000 / 1000 10 0000	1.0	1.6 1.0	20
1060-16-0622 / 1062-16-0622 1060-16-0622 / 1062-16-0622	16 16	16, 18	20 8
1000 10 0022 / 1002 10 0022	10	20	
1060-16-1222 / 1062-16-1222	16	12, 16	20
1062-16-14xx	16	12 - 16	20
1060-20-0122 / 1062-20-0122	20	1.6 1.0	20
1060-20-0122 / 1062-20-0122	20	16 <b>,</b> 18	8
1060-20-01xx / 1062-20-01xx	20	22	<u></u>
	20		-
1060-20-0222 / 1062-20-0222	20	16, 18	20
1060-20-0222 / 1062-20-0222	20	20	8
1060-20-02xx / 1062-20-02xx	20	22	8
1060-20-0144	20	16	20
	20	18	20
	20	20	8
1062-20-03xx	20	16 18	20
1062-20-03xx	20	20	8
1062-20-03xx	20	22	8

Solid Type -

Pin/Contact	Contact Size	Wire Size, AWG	Force, lbf
0460-202-20141	20	20	8
0462-201-20141	20	20	8
0460-202-20XXX / 0462 201 20XXX	16	22	8
0460-215-16141 / 0462-209-16141	16	14	20
0460-204-12141 / 0462-203-12141	12	12, 14	20
0460-202-16141 / 0462-201-16141	16	16, 18	20
0460-202-16141 / 0462-201-16141	16	20	8