В

CHEMINAX

.020

.047

.111

135

(nominal)

.145

(maximum)

100 OHM, AWG 26, 19 STRANDS OF AWG 38, RADIO FREQUENCY, TWIN CONDUCTOR CABLE

3-27-02 Date: Revision:

THIS SPECIFICATION SHEET FORMS A PART OF THE LATEST ISSUE OF RAYCHEM SPECIFICATION 1200

CONSTRUCTION DETAILS

ELECTRICAL CHARACTERISTICS

DIMENSIONS ARE NOMINAL VALUES IN INCHES UNLESS OTHERWISE DESIGNATED.

CHARACTERISTIC IMPEDANCE

100 ± 7 ohms, Method C at 1 MHz

CAPACITANCE - MUTUAL

14.5 pF/ft. (nominal)

VELOCITY OF PROPAGATION

73% (nominal)

AWG 26,

CONDUCTORS

19 Strands of AWG 38, Silver-Coated High-Strength Copper Alloy

ADDITIONAL REQUIREMENTS

DIELECTRICS

SHIELD

JACKET

Modified FEP

AWG 38

Silver-Coated Copper

Rayfoam® H Colors - White/Light Blue

ELECTRICAL

CONDUCTOR RESISTANCE INSULATION RESISTANCE

42.0 ohms/1000 ft. (nominal) 10,000 megohms (minimum)

for 1000 ft.

JACKET FLAWS

SPARK TEST **IMPULSE TEST**

1.0 kV (rms) 6.0 kV (peak)

VOLTAGE WITHSTAND

1000 volts (rms) (minimum)

(DIELECTRIC)

ENVIRONMENTAL

FLAMMABILITY HEAT SHOCK

Method B 225°C

LOW TEMPERATURE-

-55°C/3.75 inch mandrel

COLD BEND

VOLTAGE WITHSTAND

(POST ENVIRONMENTAL)

1000 volts (rms), 1 minute

PHYSICAL

INSULATION (DIELECTRIC)

(Prior to Cabling)

ELONGATION

50% (minimum) 600 lbf/in2 (minimum)

TENSILE STRENGTH

JACKET

200% (minimum)

TENSILE STRENGTH JACKET THICKNESS

2000 lbf/in2 (minimum) .012 inch (nominal)

SHIELD COVERAGE

90% (minimum)

BRAID ANGLE

ELONGATION

25° (maximum)

Outer jacket will be translucent white (designated by a "-9X" appended to the part number, e.g., 0026C0024-9X), unless otherwise specified.

WEIGHT

13.7 lbs/1000 ft. (nominal)

Designate outer jacket color with a dash number in accordance with MIL-STD-681.

Ravchem

300 Constitution Drive Menlo Park, California 94025 1-800-2-Raychem Fax: 1-650-361-6297

THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN. REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.