



**SPECIFICATIONS**


INPUT VOLTAGE : 3.0 V rms (NOM)  
 INPUT FREQUENCY : 2.5 kHz (NOM)  
 ELECTRICAL STROKE : +/- 0.500 INCH  
 SENSITIVITY : 1.6 mV/VOLT/.001 INCH  
                   : 63 mV/VOLT/mm  
 LINEARITY ERROR : ± 0.25 % OF FULL RANGE (MAX)  
 PHASE SHIFT : +13°  
 IMPEDANCE, PRIMARY : 125 OHMS (NOM)  
 IMPEDANCE, SECONDARY : 325 OHMS (NOM)  
 OPERATING TEMPERATURE : -65° TO 300° F  
 SHOCK SURVIVAL : 1000 g's, 11ms  
 VIBRATION (20 TO 2000 Hz) : 20 g's rms

**REVISIONS**

REV.	DESCRIPTION	DATE:	APPR.
A	REDRAWN WITH NO CHANGES	14 JUL 20	



[ ] DENOTES MILLIMETER

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE IN INCHES  TOLERANCES ARE: ANGLES: +/- 0.5 DEG. FRACTIONS: +/- 1/64  DECIMAL: XX= +/- .01 .XXX= +/- .005	DRAFTSMAN: R.E.A.	DATE: 06 OCT 06	 EVERY CONNECTION COUNTS	
	CHECKER:	DATE:		
This Drawing and Specifications are the property of Macro Sensors, Div. of Howard A. Schaevitz Technologies, Inc. DO NOT COPY without the written approval of Macro Sensors.	APPROVED:	DATE:	TITLE <b>CDM 375 500          OUTLINE</b>	
	APPROVED:	DATE:	<b>A</b> C.A.G.E. No. <b>06WW0</b>	DRAWING No. <b>010912160000</b>
FINISH:	APPROVED:	DATE:	SCALE: NONE	SHEET No. 1 of 1

MATERIAL: