## File E28476 Project 2900062.7421762

August 28, 2015

REPORT

on

COMPONENT - Connectors for Use in Data, Signal, Control and Power Applications

TYCO ELECTRONICS CORP MIDDLETOWN PA 17057-3170

Copyright © 2015 UL LLC

UL LLC authorizes the above named company to reproduce this Report only for purposes as described in the Conclusion. The Report should be reproduced in its entirety; however to protect confidential product information, the Construction Details Descriptive pages may be excluded.

File E28476 Vol. 129 Sec. 3 Page 1 Issued: 2015-08-28 and Report Revised: 2018-07-25

#### DESCRIPTION

#### PRODUCT COVERED:

USR, CNR Component Connector,

Cat. No. HDC, followed by -HA, followed by -003, -004, -010, -016 or -032, followed by M, F.

Cat. No. HDC, followed by -HA, followed by -003, -004, followed by MS, FS.

Cat. No. HDC, followed by -HA, followed by -010, -016 or -032, followed by MC, FC.

Cat. No. HDC, followed by -HA, followed by -016, followed by M, F, MC, FC, followed by 17-32.

Cat. No. HDC, followed by -HD, followed by -007, -008, followed by M, F.

Cat. NO. HDC, followed by -HD, followed by -007, followed by M1.

Cat. No. HDC, followed by -HQ, followed by -005, -007, -008, -012, -017, followed by M or F.

Cat. No. HDC, followed by -HQ, followed by 4/2, followed by -M or -F.

USR Component Connector,

Cat. No. HDC, followed by -HD, followed by -015, -025, -040, -050, -064, -080 or -128, followed by M, F or FJ; Cat. Nos. HDC-HD-025M/Z, HDC-HD-025F/Z.

Cat. No. HDC, followed by -HD, followed by -025, followed by M, F, followed by 26-50.

Cat. No. HDC, followed by -HD, followed by -040, followed by M, F or FJ, followed by 41-80.

Cat. No. HDC, followed by -HD, followed by -064, followed by M, F or FJ, followed by 65-128.

Cat. No. HDC, followed by -HDD, followed by -016, -072, -108, -144 or -216, followed by M, F.

Cat. No. HDC, followed by -HDD, followed by -072, followed by M, F, followed by 73-144

Cat. No. HDC, followed by -HDD, followed by -108, followed by M, F, followed by 109-216.

Cat. No. HDC, followed by  $-\mathrm{HDD}$ , followed by -024, -042, followed by M, F, FJ.

File E28476 Vol. 129 Sec. 3 Page 1A Issued: 2015-08-28 and Report Revised: 2022-01-10

# USR, CNR Component Connector,

Cat. No. HDC-HQ, followed by -002, followed by M or F.

Cat. No. HDC-HQ, followed by -002, followed by PM or PF.

Cat. No. HDC-HQ, followed by -003, followed by M or F.

Cat. No. HDC-HQ, followed by -003, followed by PM or PF.

Cat. No. HDC-HQ, followed by -021, followed by M or F.

Cat. Nos. HQ-D-032-M, HQ-D-032-F.

File E28476 Vol. 129 Sec. 3 Page 2 Issued: 2015-08-28 and Report Revised: 2022-08-18

### GENERAL:

These devices are multi-pole connectors intended for factory assembly on copper wire sizes as indicated in Ratings table below where the acceptability of combinations is determined by UL LLC. The devices are identified as follows:

 $\,$  \*USR indicates investigation to United States Standards as noted in the Test Record.

 $\,\,^*\text{CNR}$  indicates investigation to Canadian National Standards as noted in the Test Record.

### RATINGS:

Cat. Nos.	Voltage Vac/Vdc	USR Ampere (A)	CNR Ampere (A)	
HDC-HA-003M HDC-HA-003F	250	1	1	
HDC-HA-004M HDC-HA-004F	250	10	10	
HDC-HA-003MS HDC-HA-003FS	400	1		
HDC-HA-004MS HDC-HA-004FS	400	10	10	
HDC-HA-010M	600	1	1	
HDC-HA-010F	600	16	16	
HDC-HA-016M HDC-HA-016F	600	1	1	
HDC-HA-032M HDC-HA-032F	600	16	16	

File E28476 Vol. 129 Sec. 3 Page 2A Issued: 2015-08-28 and Report Revised: 2022-08-18

Cat. Nos.	Voltage Vac/Vdc	USR Ampere (A)	CNR Ampere (A)	Conductor Sizes, AWG Str
HDC-HA-010MC	600	1	1	24, 20-12
HDC-HA-010FC	600	16	16	14-12
HDC-HA-016MC HDC-HA-016FC	600	1	1	24, 20-12
HDC-HA-032MC HDC-HA-032FC	600	16	16	14-12
HDC-HD-007M	250	1	1	24, 20-14
HDC-HD-007F HDC-HD-007M1	250	10	10	14
HDC-HD-008M	50	1	1	24, 20-14
HDC-HD-008F	50	10	10	14
HDC-HD-015M HDC-HD-015F HDC-HD-015FJ	250	10	-	14
HDC-HD-025M HDC-HD-025F HDC-HD-025FJ HDC-HD-050M HDC-HD-050F	250	10	_	14

File E28476 Vol. 129 Sec. 3 Page 3 Issued: 2015-08-28 and Report Revised: 2022-08-18

Cat. Nos.	Voltage Vac/Vdc	USR Ampere (A)	CNR Ampere (A)	Conductor Sizes, AWG Str	
HDC-HD-025M/Z	250	10	_	14	
HDC-HD-025F/Z	230	10	_	14	
HDC-HD-040M					
HDC-HD-040F					
HDC-HD-040FJ	250	10	-	14	
HDC-HD-080M	250	10			
HDC-HD-080F					
HDC-HD-080FJ					
HDC-HD-064M					
HDC-HD-064F					
HDC-HD-064FJ					
HDC-HD-128M	250	10	-	14	
HDC-HD-128F					
HDC-HD-128FJ					
HDC-HDD-024FJ					
HDC-HDD-042FJ					
HDC-HDD-016M	600	10	_	14	
HDC-HDD-016F					
*HDC-HDD-024M	600	10	-	14	
HDC-HDD-024F					
*HDC-HDD-042M	600	10	-	14	
HDC-HDD-042F					
HDC-HDD-072M					
HDC-HDD-072F	600	10	_	14	
HDC-HDD-144M					
HDC-HDD-144F HDC-HDD-108M					
HDC-HDD-108F					
HDC-HDD-216M	600	10	_	14	
HDC-HDD-216F					
HDC-HQ-005M	400	1	1	24, 20-12	
HDC-HQ-005F	400	16	16	14-12	
HDC-HQ-007M	400	1	1	24, 20-14	
HDC-HQ-007F	400	10	10	14	
HDC-HQ-008M	600	1	1	24, 20-12	
HDC-HQ-008F	600	16	16	14-12	
HDC-HQ-012M	400	1	1	24, 20-14	
HDC-HQ-012F	400	10	10	14	
HDC-HQ-017M	250	1	1	24, 20-14	
HDC-HQ-017F	250	10	10	14	
		Power: 10	Power: 10	Power: 16-8	
HDC-HQ4/2-M	Power: 600	Signal: 1	Signal: 1	Signal: 24, 20-14	
HDC-HQ4/2-F	Signal:	Power: 40	Signar, i	Power: 10-8	
1120 1121/21	250	Signal: 10	_	Signal: 14	

File E28476 Vol. 129 Sec. 3 Page 3A Issued: 2015-08-28 and Report Revised: 2022-01-10

Cat. Nos.	Voltage Vac/Vdc	USR Ampere (A)	CNR Ampere (A)	Conductor Sizes, AWG Str
	400	40	-	10-8
HDC-HQ-002M	400	40	-	10-8
HDC-HQ-002F	400	10	10	18-12
	400	10	10	18-12
	830	40	-	10-8
HDC-HQ-002PM	0.50	40	-	10-8
HDC-HQ-002PF	0.2.0	10	10	18-12
	830	10	10	18-12
HDC-HQ-003M HDC-HQ-003F	400	40	35	8 AWG, 10 mm <sup>2</sup>
HDC-HQ-003PM HDC-HQ-003PF	830	40	35	8 AWG, 10 mm <sup>2</sup>
HDC-HQ-021M HDC-HQ-021F	50V AC, 120V DC	6.5	5	20 AWG
HDC-HQ-021M HDC-HQ-021F	50V AC, 120V DC	6.5	-	0.5 mm <sup>2</sup>
HQ-D-032-M HQ-D-032-F	32	2.2	2.2	22
HQ-D-032-M HQ-D-032-F	-	-	-	24-30

Disconnecting Use - see Sec Gen for required marking

TECHNICAL CONSIDERATIONS (NOT FOR FIELD REPRESENTATIVE'S USE):

Use - For use only in or with complete equipment where the acceptability of the combination is determined by UL LLC.

Conditions of Acceptability - The following are among the considerations to be made when evaluating the device in the end-use product.

Interruption of Current

1. These devices are not suitable for interrupting the flow of current by connecting or disconnecting the mating connector.

Current-Carrying Capability and Current Ratings

2. These devices have been subjected to the Temperature test with the rated currents and maximum temperature rise and recorded temperature (adjusted to 25°C ambient) values tabulated below:

		Wire		Maximum Temperature, °C		
Cat Nos.	Contac t	size AWG	Curren t, A	Rise	Recorded Temperature	Represent
HDC-HA-004MS	Pin	24	1	2.3	27.3	
mating with HDC-	Socket			1.9	26.9	HDC-HA-003
HA-004F5	Pin	14	10	17.7	42.7	HDC-HA-004
	Socket			15.6	40.6	
HDC-HA-016MC	Pin	24	1	3.9	28.9	
mating with HDC-	Socket			4.3	29.3	HDC-HA-010
HA-UIOFC	Pin	14	16	29.6	55	HDC-HA-016
	Socket			28.0	55.8	
HDC-HD-008M	Pin	24	1	3.2	28.2	
mating with HDC-	Socket			2.7	27.7	HDC-HD
HD-008F	Pin	14	10	14.7	39.7	IIDC IID
	Socket			14.2	39.2	
HDC-HDD-108M	Pin	14	10	-	70.5	HDC-HD
mating with HDC- HDD-108F	Socket			1	71.4	HDC-HDD
	Pin	24	1	2.2	27.2	
HDC-HQ-008M	Socket			2.1	27.1	HDC-HQ-005
mating with HDC- HQ-008F	Pin	14	16	25.2	50.2	HDC-HQ-008
112 0001	Socket			24.3	49.3	
	Pin	24	1	4.1	29.1	
HDC-HQ-017M	Socket			4.1	29.1	HDC-HQ-007 HDC-HO-012
mating with HDC- HQ-017F	Pin	14	10	19.1	44.1	HDC-HQ-017
~	Socket			19.0	44.0	

File E28476 Vol. 129 Sec. 3 Page 4A Issued: 2015-08-28 and Report Revised: 2022-01-10

		Wire		Maximum Temp	perature, °C
		size	Current,		Recorded
Cat Nos.	Contact	AWG	А	Rise	Temperature
HDC-HQ-002M	Male	10	40	-	57.1
HDC-HQ-002F	Female	10	40	-	56.5
HDC-HQ-002M	Male	18	10	11.9	36.9
HDC-HQ-002F	Female	18	10	12.8	37.8
HDC-HQ-002PM	Male	10	40	-	69.4
HDC-HQ-002PF	Female	10	40	-	64.9
HDC-HQ-002PM	Male	18	10	14.0	39.0
HDC-HQ-002PF	Female	18	10	14.0	39.0
HQ-D-032-M	Male	22	2.2	14.7	39.7
HQ-D-032-F	Female	22	2.2	15.3	40.3

				Maximum Temperature, °C		
Cat Nos.	Contact	Wire size	Current,	Rise	Recorded Temperature	Represent
					<u> </u>	Represent
HDC-HQ-003PM	Pin	8 AWG	USR: 40	30.7	55.7	
mating with	Socket	8 AWG	USR: 40	30.9	55.9	
HDC-HQ-003PF	Pin	10 mm <sup>2</sup>	USR: 40	27.6	52.6	
	Socket	10 mm <sup>2</sup>	USR: 40	28.3	53.3	HDC-HQ-003M
	Pin	8 AWG	CNR: 35	21.2	46.2	HDC-HQ-003F
	Socket	8 AWG	CNR: 35	21.9	46.9	
	Pin	10 mm <sup>2</sup>	CNR: 35	19.4	44.4	
	Socket	10 mm <sup>2</sup>	CNR: 35	20.9	45.9	
HDC-HQ-021M mating with HDC-HQ-021F	Pin	20 AWG	USR: 6.5	41.4	66.4	
	Socket	20 AWG	USR: 6.5	41.1	66.1	
	Pin	0.5 mm <sup>2</sup>	USR: 6.5	81.4	106.4	_
	Socket	0.5 mm <sup>2</sup>	USR: 6.5	79.6	104.6	_
	Pin	20 AWG	CNR: 5	22.5	47.5	
	Socket	20 AWG	CNR: 5	22.2	47.2	