File E28476 Project 2900062.7421762

August 29, 2015

REPORT

on

COMPONENT - Connectors for Use in Data, Signal, Control and Power Applications

TYCO ELECTRONICS CORP MIDDLETOWN PA 17057-3170

Copyright © 2015 UL LLC

UL LLC authorizes the above named company to reproduce this Report only for purposes as described in the Conclusion. The Report should be reproduced in its entirety; however to protect confidential product information, the Construction Details Descriptive pages may be excluded.

DESCRIPTION

PRODUCT COVERED:

USR, CNR Component Connector,

Cat. No. HDC, followed by -HE, followed by -006, -010, -016, -024, -032, -048, followed by M, F, MSS or FSS.

Cat. No. HDC, followed by -HE, followed by -016, followed by M, F, MSS or FSS, followed by 17-32.

Cat. No. HDC, followed by -HE, followed by -024, followed by M, F, MSS or FSS, followed by 25-48.

Cat. No. HDC, followed by -HES or -HEC, followed by -006, -010, -016, -024, -032 or -048, followed by M or F.

Cat. No. HDC, followed by -HE, followed by -006, 010, 016, 024, followed by MS, FS, MC, FC.

Cat. No. HDC, followed by -HE, followed by -016, followed by MS, FS, MC, FC, followed by 17-32.

Cat. No. HDC, followed by -HE, followed by -024, followed by MS, FS, MC, FC, followed by 25-48.

Cat. No. HDC, followed by -HVE, -HVES or -HVEC, followed by -003, -006, -010, followed by M or F.

Cat. No. HDC, followed by -HEE, followed by -010, -015, -018, -032, -046, -064, -092, followed by M or F.

Cat. No. HDC, followed by -HEE, followed by -032, followed by M or F, followed by 33-64.

Cat. No. HDC, followed by -HEE, followed by -046, followed by M or F, followed by 47-92.

Cat. No. HEEE, followed by -020, -032, -040, -048, -064, -072, -080, -096, -128, -144, followed by -M or -F.

Cat. No. HEEE, followed by -040, followed by -M or -F, followed by 41-80.

Cat. No. HEEE, followed by -048, followed by -M or -F, followed by 49-96.

Cat. No. HEEE, followed by -064, followed by -M or -F, followed by 65-128.

Cat. No. HEEE, followed by -072, followed by -M or -F, followed by 73-144.

Cat. No. HDC, followed by -HEAV, followed by -006, -010, -016, -024, followed by M, F, MS, FS.

File E28476 Vol. 129 Sec. 4 Page 2 Issued: 2015-08-29 and Report

GENERAL:

These devices are multi-pole connectors intended for factory assembly on copper wire sizes as indicated in Ratings table below where the acceptability of combinations is determined by UL LLC. The devices are identified as follows:

USR indicates investigation to United States Standards, UL 1977.

CNR indicates investigation to Canadian National Standards, ${\tt C22.2\ No.\ 182.3.}$

RATINGS:

Cat. Nos.	Voltage Vac/Vdc	USR Ampere (A)	CNR Ampere (A)
HDC-HE-006M HDC-HE-006F HDC-HES-006M	500	1	1
HDC-HES-006F HDC-HE-006MSS HDC-HE-006FSS	500	16	-
HDC-HE-010M HDC-HE-010F HDC-HES-010M	500	1	1
HDC-HES-010F HDC-HE-010MSS HDC-HE-010FSS	500	16	-
HDC-HE-016M HDC-HE-016F HDC-HE-032M HDC-HE-032F HDC-HES-016M	500	1	1
HDC-HES-016F HDC-HES-032M HDC-HES-032F HDC-HE-016MSS HDC-HE-032MSS HDC-HE-032MSS HDC-HE-032FSS	500	16	-
HDC-HE-024M HDC-HE-024F HDC-HE-048M HDC-HE-048F HDC-HES-024M	500	1	1
HDC-HES-024F HDC-HES-048M HDC-HES-048F HDC-HE-024MSS HDC-HE-024FSS HDC-HE-048MSS HDC-HE-048FSS	500	16	-

File E28476 Vol. 129 Sec. 4 Page 3 Issued: 2015-08-29 and Report

Cat. Nos.	Voltage Vac/Vdc	USR Ampere (A)	CNR Ampere (A)
HDC-HVES-003M HDC-HVES-003F	830	1	1
HDC-HVE-003M HDC-HVE-003F	830	16	16
HDC-HVES-006M HDC-HVES-006F	830	1	1
HDC-HVE-006M HDC-HVE-006F	830	16	16
HDC-HVES-010M HDC-HVES-010F	830	1	1
HDC-HVE-010M HDC-HVE-010F	830	16	16
HDC-HEAV-006M HDC-HEAV-006F	500	1	1
HDC-HEAV-006MS HDC-HEAV-006FS	500	16	_
HDC-HEAV-010M HDC-HEAV-010F	500	1	1
HDC-HEAV-010MS HDC-HEAV-010FS	500	16	
HDC-HEAV-016M HDC-HEAV-016F	500	1	1
HDC-HEAV-016MS HDC-HEAV-016FS	500	16	
HDC-HEAV-024M HDC-HEAV-024F HDC-HEAV-024MS HDC-HEAV-024FS	500	1	1

Cat. Nos.	Voltage Vac/Vdc	USR Ampere (A)	CNR Ampere	Conductor Sizes, AWG Str
HDC-HEC-006M	500	1	1	24, 20-12
HDC-HEC-006F	500	16	-	14-12
HDC-HEC-010M	500	1	1	24, 20-12
HDC-HEC-010F	500	16	-	14-12
HDC-HEC-016M	500	1	1	24, 20-12
HDC-HEC-016F				, -
HDC-HEC-032M	500	16	_	14-12
HDC-HEC-032F				
HDC-HEC-024M	500	1	1	24, 20-12
HDC-HEC-024F		_	_	
HDC-HEC-048M	500	16	_	14-12
HDC-HEC-048F				

File E28476 Vol. 129 Sec. 4 Page 4 Issued: 2015-08-29 and Report

	Ţ	1	1	1
Cat. Nos.	Voltage Vac/Vdc	USR Ampere (A)	CNR Ampere (A)	Conductor Sizes, AWG Str
HDC-HVEC-003M	830	1	1	24, 20-12
HDC-HVEC-003F	830	16	16	14-12
HDC-HVEC-006M	830	1	1	24, 20-12
HDC-HVEC-006F	830	16	16	14-12
HDC-HVEC-010M	830	1	1	24, 20-12
HDC-HVEC-010F	830	16	16	14-12
HDC-HEE-010M	500	1	1	24, 20-12
HDC-HEE-010F	500	16	-	14-12
HDC-HEE-018M	500	1	1	24, 20-12
HDC-HEE-018F	500	16	-	14-12
HDC-HEE-032M HDC-HEE-032F	500	1	1	24, 20-12
HDC-HEE-064M HDC-HEE-064F	500	16	-	14-12
HDC-HEE-046M HDC-HEE-046F	500	1	1	24, 20-12
HDC-HEE-092M HDC-HEE-092F	500	16	-	14-12
HEEE-020-M	400	1	1	24, 20-12
HEEE-020-F	400	16	-	14-12
HEEE-032-M	400	1	1	24, 20-12
HEEE-032-F	400	16	-	14-12
HEEE-040-M HEEE-040-F	500	1	1	24, 20-12
HEEE-080-M HEEE-080-F	500	16	_	14-12
HEEE-048-M HEEE-048-F	400	1	1	24, 20-12
HEEE-096-M HEEE-096-F	400	16	-	14-12
HEEE-064-M HEEE-064-F	500	1	1	24, 20-12
HEEE-128-M HEEE-128-F	500	16	_	14-12
HEEE-072-M HEEE-072-F	400	1	1	24, 20-12
HEEE-144-M HEEE-144-F	400	16	_	14-12

Disconnecting Use - see Sec Gen for required marking

TECHNICAL CONSIDERATIONS (NOT FOR FIELD REPRESENTATIVE'S USE):

Use - For use only in or with complete equipment where the acceptability of the combination is determined by UL LLC.

Conditions of Acceptability - The following are among the considerations to be made when evaluating the device in the end-use product.

Interruption of Current

1. These devices are not suitable for interrupting the flow of current by connecting or disconnecting the mating connector.

Current-Carrying Capability and Current Ratings

2. These devices have been subjected to the Temperature test with the rated currents and maximum temperature rise and recorded temperature (adjusted to 25°C ambient) values tabulated below:

		Wire	Maximum Temperature, °C			
Cat Nos.	Contact	size AWG	Curren t, A	Rise	Recorded Temperature	Represent
HDC-HEC-024M mating with	Pin Socket	14	16	-	66.4	HDC-HE
HDC-HEC-024F	Socket			_	02.0	
HDC-HVEC-	Pin	24	1	2.2	27.2	HDC-HVE
010M mating	Socket			2.0	27.0	HDC-HVES
with HDC-	Pin	14	16	22.3	47.3	HDC-HVEC
HVEC-010F	Socket			22.2	47.2	
HDC-HEE-046M	Pin	14	16	-	72.2	HDC-HE
mating with HDC-HEE-046F	Socket			_	71.2	HDC-HEE
	Pin	24	1	7.9	32.9	HDG HE
HEEE-072-M	Socket			7.7	32.7	HDC-HE
mating with HEEE-072-F	Pin	14	16	-	111.1	HDC-HEEE HDC-HEEE
	Socket			-	109.6	HDC-HEEE
HDC-HEAV-	Pin	14	16	-	69.9	
016MS mating with HDC- HEAV-016FS	Socket			-	66.5	HDC-HEAV HDC-HEAV-S
HDC-HEAV-	Pin	24	1	1.5	26.5	HDC-HEAV
024MS mating with HDC- HEAV-024FS	Socket			1.6	26.6	HDC-HEAV-S

File E28476 Vol. 129 Sec. 4 Page 6 Issued: 2015-08-29 and Report

Insulating Materials

3. These devices employ insulating materials with properties as tabulated below at the minimum thickness employed in the connector housing, the suitability of the insulating materials based on the documented values shall be determined in the end-use application. Please note the values specified in the table when multiple materials are indicated represent the minimum values for the group of materials.

Cat. No.	Insulating Material (#)	Measured Minimum Thickness	Flame Class	,	HAI(+ +)	RTI Elec	Max Operating Temp, ^O C
HDC-HEC-024M HDC-HEC-024F	B for cover C for body	0.8 mm	HB	ı	-	80	80
HDC-HVEC-010M HDC-HVEC-010F	B for cover C for body	0.8 mm	HB	-	-	80	80
HDC-HEE-046M	B for cover	0.8 mm					
HDC-HEE-046F	C for body	0.5 mm for body 0.8 mm for cover	HB	ı	_	80	80
HEEE-072-M	D	0.7 mm				120	105
HEEE-072-F	В	0.6 mm	(+)	_	_	130	125
HDC-HEAV-024MS HDC-HEAV-024FS	С	0.4 mm	HB	-	-	80	80

Note:

- (#) Code for Insulating Body Material.
- (+): Thickness is less than the minimum Recognized material thickness of B, as such no assigned Flame class. UL 746C (12mm) Flammability test conducted.
- (++): These PLCs are based on the minimum Recognized material thickness.

Mating Connectors

4. These devices have only been assessed for use with specific types of connectors within their product family. They have not been assessed to operate with any other similar devices from any other manufacturer.

File E28476 Vol. 129 Sec. 4 Page 7 Issued: 2015-08-29 and Report

Terminations

5. Crimp contacts of Cat. Nos. as tabulated below are intended for crimp termination on stranded copper conductor using the tooling shown as tabulated below for information purpose only.

Contacts Cat. Nos.	Conductor Sizes, AWG	Crimp tool
CEM, CEF, DEM, DEF	24, 20-12	ILL. 12

Miscellaneous

6. The enclosure of the device has live parts that may be exposed to user contact when the connector is energized. The device is suitable for use only within an acceptable enclosure.