



REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
	A			


SPECIFICATIONS

INPUT VOLTAGE: $\pm 15V$ DC (NOM) $\pm 25MA$
 ELECTRICAL STROKE: $\pm 1.000"$
 SCALE FACTOR: 10 VINCH
 LINEARITY: 0.25% OF FULL RANGE (MAX)
 NULL VOLTAGE: 0V DC
 RIPPLE: $< 25MV$ RMS
 STABILITY: 0.125% FULL SCALE
 OUTPUT IMPEDANCE: < 200 OHMS
 OPERATING TEMPERATURE: 0 TO 150 DEG. F
 REPEATABILITY: 0.00002"
 SOCK SURVIVAL: 1000 G'S, 11MS
 VIBRATION (DC TO 2000 HZ): 30 G'S RMS
 PRE TRAVEL: 0.05" (NOM)
 OVER TRAVEL: 0.03" (NOM)

REVISIONS			
REV.	DESCRIPTION	DATE	APPR
A	REMOVED CABLE BUNDLE FROM EXHAUST HOSE	11/25/91	KEA



PT08-10-65 (SR) or equiv.
 MATING CONNECTOR SUPPLIED



<p>TE CONNECTIVITY 11500 WILLOW CREEK DRIVE FORT WORTH, TEXAS 76154-1099 TEL: 817-435-7000 FAX: 817-435-7001</p>	<p>PROJECT NO: 00000000 DRAWING NO: 032913040000 SHEET: 1 OF 1</p>	<p>Macro Sensors THE OFFSHORE & OILFIELD TECHNOLOGY, INC. CHSDR 750 1000 OUTLINE B 000000 032913040000 SCALE: 1:1</p>
--	--	--

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	-		
DIMENSIONS: INCHES		CHK	-		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	-	NAME: CHSDR 750 1000 OUTLINE	
0 PLC ± -		PRODUCT SPEC	-	SIZE: A2	
1 PLC ± -		APPLICATION SPEC	-	CAGE CODE: 00779	
2 PLC ± -		WEIGHT	-	DRAWING NO: 032913040000	
3 PLC ± -		CUSTOMER DRAWING	-	RESTRICTED TO: -	
4 PLC ± -		SCALE: NTS	-	SHEET: 1 OF 1	
ANGLES ± -		SHEET	1 OF 1	REV: A	
FINISH					