




Mounting Detail

with locking ring

without locking ring



Third Angle Projection







	Date	Name	mm —→	Scale	Drawing No:
Drawn	15.08.2005	Braun		1:1	KISSLING
Check	05.12.2005	Braun		General Tolerances DIN ISO 2768 mK	Elektrotechnik - GmbH & Co KG D - 72218 Wildberg

08-2-1-14 F

NSN.:

Circuit Diagram

	Circuitry made with toggle at keyway	opposite keyway
Pole 1		
Pole 2		

Actuation

momentary keyway side
locking opposite keyway side

Locking Configuration

locked out in keyway side
locked in opposite keyway side

Construction

Material, Casing Duroplast GF
 Material, Cover GD-ZnAl4Cu1
 Connections Screws M3,5x6 ISO 1580
 Protection Interior IP 6K7 DIN 40 050 Part 9
 Connections IP 00 DIN 40 050 Part 9

Mechanical Data

Current carrying parts CuZn-Alloy
 Contacts Ag
 Ambient Temperature Range -55°C to +85°C
 Storage Temperature Range -65°C to +85°C
 Life Cycle iaw VG 95 210 Part 21, grade H 100.000 operations

Electrical Data

Voltage 28 V DC ohmic Load 18A
 28 V DC inductive Load at L/R = 5 ms 10A
 28 V DC lamp Load 5A
 115 V AC ohmic Load 11A
 115 V AC inductive Load cos. φ = 0,75, 8A
 115 V AC lamp Load 2A
 Motor Load utilisation category AC3 (see DIN VDE 0660 Part 107) 5A

Min. Rating 12 V DC, 20 mA

It is recommended to use gold-plated contacts
for lower currents or voltages.

Date	Name		Scale 1:1		Drawing No:
Drawn	15.08.2005	Braun	General Tolerances	Elektrotechnik - GmbH & Co KG D - 72218 Wildberg	08-2-1-14 F
Check	15.08.2005	Braun			NSN: