




LOC	DIST	REVISIONS			
P	LTR REV	DESCRIPTION MODIFICATIONS	DATE	DWN DESS.	APVD APP.
FH	2	1	CREATION	21MAR2007	FB AG



Capacity / Klemmbereich : 16-70 mm² AL
 6-50 mm² CU
 16/2.5-70/12 mm² AL/St
 Tightening torque / Anzugsmoment : 22 N.m

TOLERANCES UNLESS OTHERWISE SPECIFIED	-
TOLERANCES NON SPECIFIEES:	-
FINISH	-
FINITION	-

DIMENSIONS: mm	DWN/DESSINE F. BOARD	21MAR2007	MATERIAL MATIERE	-	FINISH FINITION	-						
	CHK/VERIFIE G. NEDELLEC	-	Tyco Electronics SIMEL PRODUCTS									
TOLERANCES UNLESS OTHERWISE SPECIFIED, TOLERANCES NON SPECIFIEES (SUIV. NR DE DECIMALES): 0 PLC / DEC: ±0 1 PLC / DEC: ±0 2 PLC / DEC: ±0 3 PLC / DEC: ±0 4 PLC / DEC: ±0 ANGLES ±		APVD/APPROUVE A. GUICHARD				NAME TITRE	HEL-3919					
PRODUCT SPEC SPEC. PRODUIT		-	SIZE FORMAT	A4	CAGE CODE	-	DRAWING NO No PLAN	C=1-1199006-5	RESTRICTED TO RESERVE A	-		
APPLICATION SPEC SPEC. APPLICATION		-	WEIGHT MASSE APPROX.	- g	CUSTOMER DRAWING /PLAN CLIENT		UNIQUEMENT POUR REFERENCE	SCALE ECHELLE	:	SHEET FEUILLE	OF DE	REV