

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL REVISION	25MAY04	CW	CW
	A1	ECR-09-026519	04DEC09	LS	CW
	B	ECR-19-015407	28JAN20	CW	CW

STRIPPING HAND TOOL



SPECIAL HAND TOOL WITH LENGTH STOP FOR HIGH QUALITY STRIPPING AND DISMANTLING OF SINGLE AND MULTI WIRE CABLES

APPLICABLE FOR A GREAT VARIETY OF INSULATIONS DIFFERING IN HARDNESS

CUSTOMER MANUAL: 411-18506

NO PINCHING OR DEFORMING OF CABLE ENDS BY A SPECIAL CUTTING MODE INTERCHANGEABLE BLADES FOR DIFFERENT WIRE RANGES. AUTOMATIC RELEASE AFTER OPERATION SOLID CONSTRUCTION, EASY TO HANDLE CHROME PLATED BODY, PLASTIC HANDLES

WIRE SIZES:
Drahtquerschnitten:
0.14mm² - 0.25mm², 0.75mm², 1.5mm², 2.5mm², 4mm², 6mm²

REPLACEMENT BLADES:
Ersatzmesser:

TE- P/N: 3-1579005-7

© 2020 TE Connectivity. All Rights Reserved.

DIMENSIONS: mm	DWN C.W itt	25MAY2004	MATERIAL	-	FINISH	-
	CHK C.W itt	25MAY2004	STE TE Connectivity			
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD C.W itt	25MAY2004				
	0 PLC ±	PRODUCT SPEC	NAME STRIPPING TOOL Abisolierwerkzeug			
1 PLC ±	-					
2 PLC ±	APPLICATION SPEC	-	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
3 PLC ±	-	-	A 4	00779	©-1-1579002-2	
4 PLC ±	WEIGHT	0,43 kg	CUSTOMER DRAWING			
ANGLES ±	-	-				
		SCALE		-	SHEET	1 OF 1
		REV		B		