


Double Pole, Electrically Held, 1 Amp and Less (Continued)

HM, HMD, HS, HSD



HM, HS Standard / Sensitive TO-5 Commercial Relay



Terminal View

Product Facts

- Hermetically sealed
- Spreader Pads
- Excellent RF switching

Electrical Characteristics

Gold/platinum/palladium/silver alloy

Gold/platinum/palladium/silver alloy

Before Life — 100 milliohms max.

(measured @ 10 mA @ 6 Vdc)

(measured @ 1 A @ 28 Vdc)

Åfter Life — 200 milliohms max.

Mechanical Life Expectancy —

Contact Arrangement -

Contact Material -


Contact Resistance —


2 Form C (DPDT)


Stationary

(gold plated) Moveable —

(gold plated)







Product Facts

- Suppression Diode
- Hermetically sealed
- Spreader Pads
- Excellent RF switching

Electrical Characteristics

Coil Voltage — 5 to 30 Vdc (HM/HMD) 5 to 48 Vdc (HS/HSD) Coil Power — HM/HMD — 675 mW max. @ 25°C HS/HSD — 565 mW max. @ 25°C

Duty Cycle — Continuous Pick-up Voltage — Approximately

70% of nominal coil voltage **Pick-up Sensitivity** — HM/HMD — 180 mW max. @ 25°C HS/HSD — 90 mW max. @ 25°C

← .370 (9.40)DIA MAX → .031 ± .003 (0.79) → .035±.010 (0.89) ↓ Ø Ø Ô 0 Ò Ó Ø \odot .200 DIA 36⁰ (5.08)GROUND PIN (OPTIONAL)

Header

Contact Ratings

1 million operations

Contact Load	Туре	Operations Min.	
1.0 A @ 28 Vdc	Resistive	100,000	
250 mA @ 115 Vac, 60 Hz & 400 Hz	Resistive (Case not grounded)	100,000	
100 mA @ 115 Vac, 60 Hz & 400 Hz	Resistive	100,000	
0.2 A @ 28 Vdc	Inductive (0.32 Henry)	100,000	
0.1 A @ 28 Vdc	Lamp	100,000	
30 µA @ 50 mVdc	Low Level	1,000,000	

1-14

Catalog 5-1773450-5 D Revised 3-13 re S

Dimensions are shown for reference purposes only. Specifications subject to change. Dimensions are in millimeters unless otherwise specified.

USA: +1 800 522 6752 Asia Pacific: +86 0 400 820 6015 UK: +44 800 267 666 For additional support numbers please visit www.te.com



Double Pole, Electrically Held, 1 Amp and Less (Continued)

HM, HMD, HS, HSD

Standard Coil Data

(Continued)

Operating Characteristics

Timing -Operate Time -HM/HMD — 4.0 ms max. HS/HSD — 6.0 ms max. Release Time -HM — 3.0 ms max. HS — 3.0 ms max. HMD — 6.0 ms max. (suppression diode) HSD — 7.5 ms max. (suppression diode)

Dielectric Withstanding Voltage —

Between Open Contacts —
350 Vrms 60 Hz
Between Adjacent Contacts —
350 Vrms 60 Hz
Between Contacts & Coil —
350 Vrms 60 Hz

Insulation Resistance -

1,000 megohms @ 500 Vdc

Environmental Characteristics

Temperature Range --55°C to +85°C

Weight -

HM/HMD — 0.09 oz. (2.55 gms) 0.099 oz. (2.80 gms) w/ spreader pad HS/HSD 0.12 oz. (3.40 gms) 0.129 oz. (3.45 gms) w/ spreader pad

Vibration Resistance -


10 G's, 10 to 500 Hz

Shock Resistance — 30 G's. 6 ±1 ms


Semiconductor Characteristics Diode


100 Vdc peak inverse voltage (PIV) 1.0 Vdc max. transient voltage

	Nom. Coil Voltage (Vdc)	Coil Resistance in Ohms ±20% @ 25°C	Pickup Voltage Vdc (max.) @ 25°C	Nom. Coil Power (mW) @ 25°C	Max. Coil Voltage	Coil Desig
HM/HMD	5.0	50	3.6	500	5.8	5
	6.0	98	4.2	367	8.0	6
	9.0	220	6.5	368	12.0	9
	12.0	390	8.4	369	16.0	12
	18.0	880	13.0	368	24.0	18
	26.5	1,560	17.0	450	32.0	26
	30.0	2,500	22.0	360	36.0	30
HS/HSD	5.0	100	3.5	250	7.5	5
	6.0	200	4.5	180	10.0	6
	9.0	400	6.8	203	15.0	9
	12.0	850	9.0	169	20.0	12
	18.0	1,600	13.5	203	30.0	18
	26.5	3,300	18.0	213	40.0	26
	36.0	6,500	24.0	199	57.0	36
	48.0	11,000	32.0	209	75.0	48



HM/HMD Enclosure





Spreader and Mounting Pads



Ordering Instructions Catalog-selected Relays: The catalog number is derived by choosing the proper CODE for each of the relay characteristics in the order in which the codes are listed.

Specifying a Part Number Example:		Туре	<u>Diodes</u>	<u>odes Ground Pin</u> Spreader/I		/Mounting Pa	<u> Pads Coils Terminals</u>		als
		HM	D	Х		3	-26	В	1_1
Catalog 5-1773450-5	Dimensions are shown for	Dimens	sions are in mil	limeters	USA: +1 800 522 675	2 1	or additional su	pport numbers	

www.te.com

reference purposes only. Specifications subject to change.

unless otherwise specified.

USA: +1 800 522 6752 Asia Pacific: +86 0 400 820 6015 UK: +44 800 267 666

For additional support numbers please visit www.te.com

·15