



P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	INITIAL RELEASE	08JUL2020	SB	LI



TYPICAL INSERTION LOSS
COMMON MODE 50/50Ω; DIFFERENTIAL MODE 50/50Ω

MHz	0.01	0.05	0.15	0.5	1	3	5	10	30
CM	70	71	75	86	81	63	54	40	38
DM	51	53	64	82	84	63	48	19	22



SAFETY ORGANIZATIONS
THIS FILTER WILL BE FORMALLY RECOGNIZED, CERTIFIED OR APPROVED BY THE LISTED AGENCY. THEREFORE, ALL TEST/REQUIREMENTS SPECIFIED IN THE LATEST REVISION OF THE FOLLOWING AGENCY STANDARDS WILL BE MET:

UL RECOGNIZED* 10A 440V 50Hz/60Hz 40°C
CSA CERTIFIED** 10A 440V 50Hz/60Hz 40°C

*31 JULY 2020 ; **31 AUGUST 2020

OPERATING SPECIFICATION
LINE CURRENT/VOLTAGE: 10A, 440VAC
LINE FREQUENCY: 50/60Hz

MAXIMUM LEAKAGE CURRENT: 5mA @ 230VAC, 50Hz

OPERATING AMBIENT TEMPERATURE RANGE @ RATED CURRENT: -25°C TO +40°C

IN AN AMBIENT, T_a, HIGHER THAN 40°C, THE MAXIMUM OPERATING CURRENT, I_o, IS AS FOLLOWS:

$$I_o = I_r \sqrt{\frac{85 - T_a}{45}}$$

RELIABILITY SPECIFICATIONS
STORAGE TEMPERATURE: -40°C TO +85°C
HUMIDITY: 21 DAYS @ 40°C AND 95% RH

TEST SPECIFICATIONS
INDUCTANCE, NOMINAL: 16mH

CAPACITANCE @ 1kHz
LINE TO GROUND, NOMINAL: 0.365μF
LINE TO LINE, NOMINAL: 3.75μF

DISCHARGE RESISTOR
L/L I.R. 2MΩ 1W
L/N I.R. XXX
L/G I.R. 1MΩ 1W
N/G I.R. XXX
IR (NO DISCHARGE RESISTOR) 20°C, 50% RH AND 100VDC, MIN: 6MΩ

RECOMMENDED RECEIVING INSPECITON HIPOT
LINE TO GROUND FOR 1 MINUTE: 2632VDC
LINE TO LINE FOR 1 MINUTE: 1892VDC

FILTER APPROVAL
THE BEST WAY TO SELECT AND QUALIFY A FILTER IS FOR YOUR ENGINEERING TO TEST THE UNIT IN YOUR EQUIPMENT.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SHRICARANA B 27FEB2020	TE Connectivity		
DIMENSIONS: mm		CHK LEO IRUDHAYARAJ 27FEB2020			
		APVD LEO IRUDHAYARAJ 27FEB2020			
		PRODUCT SPEC			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	NAME POWER LINE FILTER 10KEHD10AFPD		
0 PLC ±-		-	SIZE		
1 PLC ±0.5		-	CAGE CODE		
2 PLC ±0.40		-	DRAWING NO		
3 PLC ±0.130		-	RESTRICTED TO		
4 PLC ±0.0500		-	A300779C-1-1609969-0		
ANGLES ±-		WEIGHT	SCALE		
MATERIAL		-	2:5		
FINISH		-	SHEET 1 OF 2		
CUSTOMER DRAWING		-	REV B		





© 2020 TE Connectivity. All Rights Reserved.


NOTE 1 GROUND CONNECTION:
DO NOT LOOSEN INNER GROUND NUTS.
TORQUE OUTER TERMINAL SCREWS: 0.5Nm / 4.5 in.lbs
TORQUE GROUND NUTS: 2Nm

NOTE 2 INPUT OUTPUT CONNECTION TERMINAL
AWG SIZE: 26-12 AWG
WIRE SECTION: 4 mm²
THREADED BOLT SIZE FOR GROUND: M5

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SHRICHARANA B 27FEB2020	 TE Connectivity		
DIMENSIONS: mm		CHK LEO IRUDHAYARAJ 27FEB2020			
		APVD LEO IRUDHAYARAJ 27FEB2020	NAME POWER LINE FILTER 10KEHD10AFPD		
		PRODUCT SPEC -	-		
MATERIAL -		APPLICATION SPEC -	SIZE A3		
		WEIGHT -	CAGE CODE 00779		
FINISH -		CUSTOMER DRAWING	DRAWING NO C-1-1609969-0		
			RESTRICTED TO -		
			SCALE 1:2		
			SHEET 2 OF 2		
			REV B		