


## A-1077 Series, Rated up to 100 Amps, 28 Vdc

#### **Product Facts**

- SPST NO, Double Break or SPDT Double Break
- **■** Gasket Sealed
- Auxiliary contacts available
- Meets many requirements of MIL-PRF-6106



#### **Performance Data**

#### **Electrical Characteristics**

Main Contact Configuration — A-1077DD — SPST NO A-1077S — SPDT

Rated Operating Voltage — 28 Vdc

Main Contact Rating —
Resistive Rating — 100 Amps
Inductive Rating — 100 Amps

Motor Rating — 100 Amps Interrupt Rating — 1,200 Amps Auxiliary Contacts —

**Resistive Rating** — 5 Amp, 28 VAC/115 VAC

## **General Characteristics**

**Temperature Range** — -55°C to +71°C

Operating Cycles (Life) at Rated Resistive Load, Min. — 50,000 cycles

Operating Cycles (Life)
Mechanical, Min. — 100,000 cycles

Dielectric Strength —

All Circuits to Ground — 1,250 Vrms Circuit to Circuit — 1,250 Vrms Coil to Ground and Aux. Contacts — 1.000 Vrms

**Altitude, Max.** — 50,000 ft. **Weight, Max.** — 1.5 to 2 lbs

#### **Coil Characteristics**

## **Coil Characteristics**

**Duty Cycle** — Continuous

Operating Voltage, Max. — 32 Vdc Operating Voltage, Min. — 24 Vdc

Pickup Voltage @ 25°C, Max. — 16.5 Vdc


**Dropout Voltage** — 1 to 7 Vdc


For factory-direct application assistance, phone 419-521-9500 or fax 419-526-2749.

www.te.com




# A-1077 Series, Rated up to 100 Amps, 28 Vdc (Continued)





#### Circuit Configurations (Consult factory for other available circuit configurations)



HARTMAN Part Number	Construction Type	Mounting Style	Coil Type	Circuit Config.	TE Part Number
A-1077DD	Gasket Sealed	Α	Continuous	1	1616055-3
A-1077S	Gasket Sealed	В	Continuous, w/ Suppression	2	1616081-3

For factory-direct application assistance, phone 419-521-9500 or fax 419-526-2749.

For additional support numbers

please visit www.te.com